# SN54LVTH540, SN74LVTH540 3.3-V ABT OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCBS681G - MARCH 1997 - REVISED OCTOBER 2003


- Support Mixed-Mode Signal Operation (5-V Input and Output Voltages With 3.3-V V<sub>CC</sub>)
- Typical V<sub>OLP</sub> (Output Ground Bounce)
   <0.8 V at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C
- Support Unregulated Battery Operation Down to 2.7 V
- I<sub>off</sub> and Power-Up 3-State Support Hot Insertion
- Bus Hold on Data Inputs Eliminates the Need for External Pullup/Pulldown Resistors
- Latch-Up Performance Exceeds 500 mA Per JESD 17
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)

#### description/ordering information


These octal buffers/drivers are designed specifically for low-voltage (3.3-V)  $V_{CC}$  operation, but with the capability to provide a TTL interface to a 5-V system environment.

The 'LVTH540 devices are ideal for driving bus lines or buffer-memory address registers. These devices feature inputs and outputs on opposite sides of the package that facilitate printed circuit board layout.

#### SN54LVTH540 . . . J OR W PACKAGE SN74LVTH540 . . . DB, DW, NS, OR PW PACKAGE (TOP VIEW)



# SN54LVTH540 . . . FK PACKAGE (TOP VIEW)



#### ORDERING INFORMATION

TA	PACK	AGET	ORDERABLE PART NUMBER	TOP-SIDE MARKING
	COIC DW	Tube	SN74LVTH540DW	1.//***********************************
−40°C to 85°C	SOIC - DW	Tape and reel	SN74LVTH540DWR	LVTH540
	SOP - NS	Tape and reel	SN74LVTH540NSR	LVTH540
	SSOP – DB	Tape and reel	SN74LVTH540DBR	LXH540
		Tube	SN74LVTH540PW	1.7/1540
	TSSOP – PW	Tape and reel	SN74LVTH540PWR	LXH540
	CDIP – J	Tube	SNJ54LVTH540J	SNJ54LVTH540J
−55°C to 125°C	CFP – W	Tube	SNJ54LVTH540W	SNJ54LVTH540W
	LCCC - FK	Tube	SNJ54LVTH540FK	SNJ54LVTH540FK

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



### SN54LVTH540, SN74LVTH540 3.3-V ABT OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCBS681G - MARCH 1997 - REVISED OCTOBER 2003

#### description/ordering information (continued)

The 3-state control gate is a 2-input AND gate with active-low inputs so that, if either output-enable (OE1 or OE2) input is high, all outputs are in the high-impedance state.

Active bus-hold circuitry holds unused or undriven inputs at a valid logic state. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.


When  $V_{CC}$  is between 0 and 1.5 V, the devices are in the high-impedance state during power up or power down. However, to ensure the high-impedance state above 1.5 V,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

These devices are fully specified for hot-insertion applications using  $I_{off}$  and power-up 3-state. The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the devices when they are powered down. The power-up 3-state circuitry places the outputs in the high-impedance state during power up and power down, which prevents driver conflict.

#### **FUNCTION TABLE**

	INPUTS							
OE1	OE2	Α	Y					
L	L	L	Н					
L	L	Н	L					
Н	X	Χ	Z					
Х	Н	Χ	Z					

#### logic diagram (positive logic)



SCBS681G - MARCH 1997 - REVISED OCTOBER 2003

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage range, $V_{CC}$
or power-off state, V <sub>O</sub> (see Note 1)
Voltage range applied to any output in the high state, $V_O$ (see Note 1)0.5 V to $V_{CC}$ + 0.5 V
Current into any output in the low state, IO: SN54LVTH540
SN74LVTH540 128 mA
Current into any output in the high state, I <sub>O</sub> (see Note 2): SN54LVTH540
SN74LVTH540 64 mA
Input clamp current, $I_{IK}$ ( $V_I < 0$ )
Output clamp current, $I_{OK}$ ( $V_O < 0$ )
Package thermal impedance, θ <sub>JA</sub> (see Note 3): DB package
DW package 58°C/W
NS package 60°C/W
PW package 83°C/W
Storage temperature range, T <sub>stg</sub> –65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
  - 2. This current flows only when the output is in the high state and  $V_O > V_{CC}$ .
  - 3. The package thermal impedance is calculated in accordance with JESD 51-7.

#### recommended operating conditions (see Note 4)

		SN54LVTH540		SN74LV	TH540	UNIT
		MIN	MAX	MIN	MAX	UNII
Vcc	Supply voltage	2.7	3.6	2.7	3.6	V
V <sub>IH</sub>	High-level input voltage	2	Z.	2		V
V <sub>IL</sub>	Low-level input voltage		0.8		8.0	V
VI	Input voltage	ć	5.5		5.5	V
IOH	High-level output current	4	-24		-32	mA
loL	Low-level output current	<sup>1</sup> / <sub>1</sub> C	48		64	mA
Δt/Δν	Input transition rise or fall rate	06	10		10	ns/V
Δt/ΔV <sub>CC</sub>	Power-up ramp rate	200		200		μs/V
T <sub>A</sub>	Operating free-air temperature	-55	125	-40	85	°C

NOTE 4: All unused control inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

## SN54LVTH540, SN74LVTH540 3.3-V ABT OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCBS681G - MARCH 1997 - REVISED OCTOBER 2003

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

				SN	54LVTH	540	SN	74LVTH	540		
PAI	RAMETER	TEST CO	ONDITIONS	MIN	TYP†	MAX	MIN	TYP†	MAX	UNIT	
$V_{IK}$		$V_{CC} = 2.7 \text{ V},$	I <sub>I</sub> = -18 mA			-1.2			-1.2	V	
		$V_{CC} = 2.7 \text{ V to } 3.6 \text{ V},$	I <sub>OH</sub> = -100 μA	V <sub>CC</sub> -0	-0.2 V <sub>CC</sub> -0.2						
.,		$V_{CC} = 2.7 \text{ V},$	$I_{OH} = -8 \text{ mA}$	2.4			2.4			.,	
VOH		V 2 V	$I_{OH} = -24 \text{ mA}$	2						V	
		V <sub>CC</sub> = 3 V	$I_{OH} = -32 \text{ mA}$				2	2			
		\/ 27\/	$I_{OL} = 100  \mu A$			0.2			0.2		
		V <sub>CC</sub> = 2.7 V	$I_{OL} = 24 \text{ mA}$			0.5			0.5		
\/-·			$I_{OL} = 16 \text{ mA}$			0.4			0.4	V	
$V_{OL}$		\\\\-\-\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	$I_{OL} = 32 \text{ mA}$			0.5			0.5	V	
		VCC = 3 V	$I_{OL} = 48 \text{ mA}$			0.55				]	
			$I_{OL} = 64 \text{ mA}$						0.55		
		$V_{CC} = 0 \text{ or } 3.6 \text{ V},$	V <sub>I</sub> = 5.5 V			\$ 10			10		
1.	Control inputs	$V_{CC} = 3.6 \text{ V},$	$V_I = V_{CC}$ or GND		Š	±1			±1		
I <sub>I</sub>		V <sub>CC</sub> = 3.6 V	VI = VCC		Q.	1			1	μΑ	
	Data inputs		V <sub>I</sub> = 0		1	-5			-5		
l <sub>off</sub>		$V_{CC} = 0$ ,	$V_I$ or $V_O = 0$ to 4.5 $V$		3				±100	μΑ	
		V <sub>CC</sub> = 3 V	V <sub>I</sub> = 0.8 V	75	5		75				
l <sub>l</sub> (hold)	Data inputs		V <sub>I</sub> = 2 V	-75	<b>−75</b>		-75			μА	
		$V_{CC} = 3.6 V^{\ddagger}$ ,	$V_{I} = 0 \text{ to } 3.6 \text{ V}$					±500			
lozh		$V_{CC} = 3.6 \text{ V},$	V <sub>O</sub> = 3 V			5			5	μΑ	
l <sub>OZL</sub>		$V_{CC} = 3.6 \text{ V},$	V <sub>O</sub> = 0.5 V			-5			-5	μΑ	
I <sub>OZPU</sub>		$\frac{\text{VCC}}{\text{OE}} = 0 \text{ to } 1.5 \text{ V}, \text{ VO} = 0$	0.5 V to 3 V,			±100*			±100	μΑ	
IOZPD		$\frac{\text{V}_{\text{C}}\text{C}}{\text{OE}} = 1.5 \text{ V to } 0, \text{ V}_{\text{O}} = 0$	0.5 V to 3 V,			±100*			±100	μΑ	
		V <sub>CC</sub> = 3.6 V,	Outputs high			0.19			0.19		
ICC		$I_{O} = 0$ ,	Outputs low		5		5			mA	
		$V_I = V_{CC}$ or GND	Outputs disabled		0.19 0.				0.19		
		V <sub>CC</sub> = 3 V to 3.6 V, One Other inputs at V <sub>CC</sub> or G			0.2			0.2	mA		
Ci		V <sub>I</sub> = 3 V or 0			3			3		pF	
Со		$V_0 = 3 \text{ V or } 0$			7			7		pF	

<sup>\*</sup> On products compliant to MIL-PRF-38535, this parameter is not production tested.



<sup>&</sup>lt;sup>†</sup> All typical values are at  $V_{CC}$  = 3.3 V,  $T_A$  = 25°C.

<sup>‡</sup> This is the bus-hold maximum dynamic current. It is the minimum overdrive current required to switch the input from one state to another.

<sup>§</sup> This is the increase in supply current for each input that is at the specified TTL voltage level, rather than VCC or GND.


SCBS681G - MARCH 1997 - REVISED OCTOBER 2003

# switching characteristics over recommended ranges of supply voltage and operating free-air temperature, $C_L = 50$ pF (unless otherwise noted) (see Figure 1)

				SN54L\	/TH540			SN7	4LVTH5	540			
PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 3.3 V ± 0.3 V		V <sub>CC</sub> = 2.7 V		V <sub>CC</sub> = 3.3 V ± 0.3 V			V <sub>CC</sub> = 2.7 V		UNIT	
			MIN	MAX	MIN	MAX	MIN	TYP†	MAX	MIN	MAX		
tPLH .	•	V	1	3.9	NA.	4.7	1.1	2.4	3.8		4.6	20	
<sup>t</sup> PHL	А	Y	1	3.9	N. P.	4.7	1.1	2.7	3.8		4.6	ns	
<sup>t</sup> PZH	<u> </u>	V	1.4	5.3	1,	6.3	1.5	3.4	5.2		6.2	20	
t <sub>PZL</sub>	OE1 or OE2	Y	1.4	5.5		6.1	1.5	3.7	5.3		5.9	ns	
<sup>t</sup> PHZ	OE1 or OE2	<u> </u>	<b>V</b>	1.4	5.9		6.2	1.5	3.9	5.6		5.9	
t <sub>PLZ</sub>	OE1 or OE2	Y	1.4	5.5		5.8	1.5	3.5	5		5.3	5.3 ns	

<sup>&</sup>lt;sup>†</sup> All typical values are at  $V_{CC}$  = 3.3 V,  $T_A$  = 25°C.

#### PARAMETER MEASUREMENT INFORMATION



NOTES: A.  $C_L$  includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_Q = 50 \ \Omega$ ,  $t_f \leq 2.5 \ ns$ .
- D. The outputs are measured one at a time with one transition per measurement.
- E. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms







10-Dec-2020

#### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
SN74LVTH540DBR	ACTIVE	SSOP	DB	20	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LXH540	Samples
SN74LVTH540DW	ACTIVE	SOIC	DW	20	25	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LVTH540	Samples
SN74LVTH540DWR	ACTIVE	SOIC	DW	20	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LVTH540	Samples
SN74LVTH540PW	ACTIVE	TSSOP	PW	20	70	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LXH540	Samples
SN74LVTH540PWR	ACTIVE	TSSOP	PW	20	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LXH540	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



### **PACKAGE OPTION ADDENDUM**

10-Dec-2020

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 3-Jun-2022

#### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LVTH540DBR	SSOP	DB	20	2000	330.0	16.4	8.2	7.5	2.5	12.0	16.0	Q1
SN74LVTH540DWR	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1
SN74LVTH540PWR	TSSOP	PW	20	2000	330.0	16.4	6.95	7.1	1.6	8.0	16.0	Q1

**PACKAGE MATERIALS INFORMATION** 

www.ti.com 3-Jun-2022




#### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74LVTH540DBR	SSOP	DB	20	2000	356.0	356.0	35.0
SN74LVTH540DWR	SOIC	DW	20	2000	367.0	367.0	45.0
SN74LVTH540PWR	TSSOP	PW	20	2000	356.0	356.0	35.0

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 3-Jun-2022

#### **TUBE**



#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
SN74LVTH540DW	DW	SOIC	20	25	507	12.83	5080	6.6
SN74LVTH540PW	PW	TSSOP	20	70	530	10.2	3600	3.5





#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-150.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





SOIC



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
- 5. Reference JEDEC registration MS-013.



SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated