

ESD752 and ESD762 24V、2チャンネル、5.7A、8/20 μ s サージ保護と ESD 保護、SOT-23 および SOT-323 / SC-70 パッケージ

1 特長

- 強力なサージ保護:
 - IEC 61000-4-5 (8/20 μ s): 5.7A~2.5A
- IEC 61000-4-2 レベル 4 ESD 保護:
 - ± 30 kV または ± 20 kV の接触放電
 - ± 30 kV または ± 20 kV のエアギャップ放電
- 24V の動作電圧
- 双方向 ESD 保護
- 1 つの部品で完全な ESD 保護機能とサージ保護機能を実現できる 2 チャンネル・デバイス
- 下流の部品を保護する低いクランピング電圧
- I/O 容量 = 3pF または 1.7pF (標準値)
- SOT-23 (DBZ): 小型、標準、共通フットプリント
- SOT-323 / SC-70 (DCK): 超小型、標準、省スペース、共通フットプリント
- 自動光学検査 (AOI) に適したリード付きパッケージ

2 アプリケーション

- USB Power Delivery (USB-PD):
 - VBUS 保護
 - IO 保護 (VBUS への短絡に耐える)
- 産業用制御ネットワーク:
 - スマート分配システム (SDS)
 - DeviceNet IEC 62026-3
 - CANopen - CiA 301/302-2、EN 50325-4
 - 4/20mA 回路
 - PLC サージ保護
 - ADC サージ保護

3 概要

ESD752 and ESD762 は、USB Power Delivery (USB-PD) および産業用インターフェイス用の双方向 ESD 保護ダイオードです。ESD752 and ESD762 は、IEC 61000-4-2 レベル 4 で規定されている最大レベル (± 30 kV または ± 20 kV の接触、 ± 30 kV または ± 20 kV のエアギャップ) を満たす、または上回る ESD 耐性を持ちます。低い動的抵抗および低いクランピング電圧により、過渡現象に対してシステム・レベルの保護を実現します。産業用システムは高いレベルの堅牢性と信頼性を要求するため、この保護機能は重要です。


これらのデバイスはチャンネルごとの IO 容量が低く、静電気放電 (ESD) とその他の過渡事象に起因する損傷から保護されるよう、2 つの IO ラインに適合したピン配置を備えています。ESD752 には $I_{pp} = 5.7A$ (8/20 μ s のサージ波形) の性能があり、過渡的なサージ事象から USB VBUS や産業用 I/O ラインを保護するのに適しています。さらに、ESD752 と ESD762 の 3pF または 1.7pF のライン容量は、産業用アプリケーションの USB Power Delivery と IO 信号用の低速な信号を保護するのに適しています。

ESD752 and ESD762 は、フロースルー配線を容易にするため、2 種類のリード付きパッケージで供給されます。

パッケージ情報 (1)

| 部品番号 | パッケージ | 本体サイズ (公称) |
|--------|--------------------------|-----------------|
| ESD752 | DCK (SOT-323 / SC-70, 3) | 2.00mm × 1.25mm |
| | DBZ (SOT-23, 3) | 2.92mm × 1.30mm |
| ESD762 | DBZ (SOT-23, 3) | 2.92mm × 1.30mm |

(1) 利用可能なパッケージについては、このデータシートの末尾にある注文情報を参照してください。



USB Power Delivery Application

USB Power Delivery の標準的なアプリケーション



Table of Contents

| | | | |
|---|----------|---|-----------|
| 1 特長..... | 1 | 7.4 Device Functional Modes..... | 9 |
| 2 アプリケーション..... | 1 | 8 Application and Implementation..... | 10 |
| 3 概要..... | 1 | 8.1 Application Information..... | 10 |
| 4 Revision History..... | 2 | 8.2 Typical Application..... | 10 |
| 5 Pin Configuration and Functions..... | 3 | 9 Power Supply Recommendations..... | 12 |
| 6 Specifications..... | 4 | 10 Layout..... | 13 |
| 6.1 Absolute Maximum Ratings..... | 4 | 10.1 Layout Guidelines..... | 13 |
| 6.2 ESD Ratings—JEDEC Specification..... | 4 | 10.2 Layout Example..... | 13 |
| 6.3 ESD Ratings—IEC Specification..... | 4 | 11 Device and Documentation Support..... | 14 |
| 6.4 Recommended Operating Conditions..... | 4 | 11.1 Documentation Support..... | 14 |
| 6.5 Thermal Information..... | 4 | 11.2 Receiving Notification of Documentation Updates.. | 14 |
| 6.6 Electrical Characteristics..... | 5 | 11.3 サポート・リソース..... | 14 |
| 6.7 Typical Characteristics – ESD752..... | 6 | 11.4 Trademarks..... | 14 |
| 6.8 Typical Characteristics – ESD762..... | 7 | 11.5 Electrostatic Discharge Caution..... | 14 |
| 7 Detailed Description..... | 8 | 11.6 Glossary..... | 14 |
| 7.1 Overview..... | 8 | 12 Mechanical, Packaging, and Orderable Information..... | 14 |
| 7.2 Functional Block Diagram..... | 8 | | |
| 7.3 Feature Description..... | 8 | | |


4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| Changes from Revision A (August 2022) to Revision B (November 2022) | Page |
|---|------|
| • データシートに ESD762 の仕様を追加..... | 1 |
| • Added the <i>Application Curves</i> section..... | 12 |

| Changes from Revision * (May 2022) to Revision A (August 2022) | Page |
|--|------|
| • データシートのステータスを「事前情報」から「量産データ」に変更 | 1 |

5 Pin Configuration and Functions



**图 5-1. DCK and DBZ Package,
 3-Pin SOT-323 / SC-70 and SOT-23
 (Top View)**

表 5-1. Pin Functions

| PIN | | TYPE ⁽¹⁾ | DESCRIPTION |
|------|------|---------------------|--------------------|
| NAME | NO. | | |
| IO | 1, 2 | I/O | ESD protected IO |
| GND | 3 | G | Connect to ground. |

(1) I = Input, O = Output, I/O = Input or Output, G = Ground, P = Power

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| PARAMETER | | DEVICE | MIN | MAX | UNIT |
|------------------|--|--------|-----|-----|------|
| P _{pp} | IEC 61000-4-5 Power (t _p – 8/20 μs) at 25°C | ESD752 | | 210 | W |
| | IEC 61000-4-5 Power (t _p – 8/20 μs) at 25°C | ESD762 | | 90 | W |
| I _{pp} | IEC 61000-4-5 current (t _p – 8/20 μs) at 25°C | ESD752 | | 5.7 | A |
| | IEC 61000-4-5 current (t _p – 8/20 μs) at 25°C | ESD762 | | 2.5 | A |
| T _A | Operating free-air temperature | | -55 | 150 | °C |
| T _J | Junction temperature | | -55 | 150 | °C |
| T _{stg} | Storage temperature | | -65 | 155 | °C |

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

6.2 ESD Ratings—JEDEC Specification

| PARAMETER | | TEST CONDITION | VALUE | UNIT |
|--------------------|-------------------------|---|--------|------|
| V _(ESD) | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ± 2500 | V |
| | | Charged device model (CDM), per JEDEC specification JS-002 ⁽²⁾ | ± 1000 | |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 ESD Ratings—IEC Specification

over T_A = 25°C (unless otherwise noted)

| PARAMETER | | TEST CONDITION | DEVICE | VALUE | UNIT |
|--------------------|-------------------------|---|--------|--------|------|
| V _(ESD) | Electrostatic discharge | IEC 61000-4-2 Contact Discharge, all pins | ESD752 | ±30000 | V |
| | | | ESD762 | ±20000 | V |
| | | IEC 61000-4-2 Air Discharge, all pins | ESD752 | ±30000 | V |
| | | | ESD762 | ±20000 | V |

6.4 Recommended Operating Conditions

| PARAMETER | | MIN | NOM | MAX | UNIT |
|-----------------|--------------------------------|-----|-----|-----|------|
| V _{IN} | Input voltage | -24 | | 24 | V |
| T _A | Operating free-air temperature | -55 | | 150 | °C |

6.5 Thermal Information

| THERMAL METRIC ⁽¹⁾ | | ESD752 | | ESD762 | UNIT |
|-------------------------------|--|--------------|-----------------------|--------------|------|
| | | DBZ (SOT-23) | DCK (SOT-323 / SC-70) | DBZ (SOT-23) | |
| | | 3 PINS | 3 PINS | 3 PINS | |
| R _{θJA} | Junction-to-ambient thermal resistance | 291.5 | 283.0 | 325.3 | °C/W |
| R _{θJC(top)} | Junction-to-case (top) thermal resistance | 147.1 | 164.1 | 178.8 | °C/W |
| R _{θJB} | Junction-to-board thermal resistance | 131.1 | 105.1 | 165.5 | °C/W |
| Ψ _{JT} | Junction-to-top characterization parameter | 32.0 | 67.1 | 52.4 | °C/W |
| Ψ _{JB} | Junction-to-board characterization parameter | 130.2 | 104.4 | 164.4 | °C/W |

6.5 Thermal Information (continued)

| THERMAL METRIC ⁽¹⁾ | | ESD752 | | ESD762 | UNIT |
|-------------------------------|--|--------------|-----------------------|--------------|------|
| | | DBZ (SOT-23) | DCK (SOT-323 / SC-70) | DBZ (SOT-23) | |
| | | 3 PINS | 3 PINS | 3 PINS | |
| $R_{\theta JC(bot)}$ | Junction-to-case (bottom) thermal resistance | N/A | N/A | N/A | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.


6.6 Electrical Characteristics

over $T_A = 25^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

| PARAMETER | | TEST CONDITIONS | DEVICE | MIN | TYP | MAX | UNIT |
|-------------|---|--|--------|-------|------|-------|----------|
| V_{RWM} | Reverse stand-off voltage | | | -24 | | 24 | V |
| V_{BRF} | Forward breakdown voltage ⁽²⁾ | $I_{IO} = 10\text{ mA}$, IO to GND | | 25.5 | | 35.5 | V |
| V_{BRR} | Reverse breakdown voltage ⁽²⁾ | $I_{IO} = -10\text{ mA}$, IO to GND | | -35.5 | | -25.5 | V |
| V_{CLAMP} | Clamping voltage ⁽³⁾ | $I_{PP} = 5.7\text{ A}$, $t_p = 8/20\ \mu\text{s}$, IO to GND | ESD752 | | 37 | | V |
| | | $I_{PP} = 2.5\text{ A}$, $t_p = 8/20\ \mu\text{s}$, from IO to GND | ESD762 | | 36 | | V |
| V_{CLAMP} | Clamping voltage ⁽⁴⁾ | $I_{PP} = 16\text{ A}$, TLP, IO to GND or GND to IO | ESD752 | | 35 | | V |
| | | | ESD762 | | 38 | | V |
| V_{Hold} | Holding voltage after snapback ⁽⁵⁾ | TLP | ESD752 | | 30 | | V |
| | | | ESD762 | | 30 | | V |
| I_{LEAK} | Leakage current | $V_{IO} = \pm 24\text{ V}$, IO to GND | | -50 | 5 | 50 | nA |
| R_{DYN} | Dynamic resistance ⁽⁴⁾ | IO to GND and GND to IO | ESD752 | | 0.35 | | Ω |
| | | | ESD762 | | 0.57 | | Ω |
| C_L | Line capacitance ⁽⁶⁾ | $V_{IO} = 0\text{ V}$, $f = 1\text{ MHz}$, $V_{pp} = 30\text{ mV}$ | ESD752 | | 3 | 5 | pF |
| | | | ESD762 | | 1.7 | 2.8 | pF |


- (1) Measurements made on each IO channel.
- (2) V_{BRF} and V_{BRR} are defined as the voltage when +/- 10 mA is applied in the positive or negative direction respectively, before the device latches into the snapback state.
- (3) Device stressed with 8/20 μs exponential decay waveform according to IEC 61000-4-5.
- (4) Non-repetitive current pulse, Transmission Line Pulse (TLP); square pulse; ANSI / ESD STM5.5.1-2008
- (5) V_{HOLD} is defined as the lowest voltage on the TLP plot once the trigger threshold is reached and the device snapbacks and begins clamping the voltage.
- (6) Measured from IO to GND on each channel.

6.7 Typical Characteristics – ESD752




tp = 100 ns, Transmission Line Pulse (TLP)

6-1. Positive TLP Curve




tp = 100 ns, Transmission Line Pulse (TLP)

6-2. Negative TLP Curve




Vclamp_ESD at 30ns = 28V

6-3. +8-kV Clamped IEC Waveform




Vclamp_ESD at 30ns = -32.9V

6-4. -8-kV Clamped IEC Waveform



Frequency = 1MHz, Vpp = 30 mV


6-5. Capacitance vs. Bias Voltage





TA = 150 °C
ILEAK is less than 1 nA at -55 °C and 25 °C.

6-6. Leakage Current vs. Bias Voltage Across Temperature

6.7 Typical Characteristics – ESD752 (continued)



6.8 Typical Characteristics – ESD762




7 Detailed Description

7.1 Overview

The ESD752 and ESD762 are dual-channel ESD TVS diodes in SOT-23 and SOT-323 (SC-70) leaded packages which are convenient for automatic optical inspection. This product offers IEC 61000-4-2 ± 30 -kV or ± 20 -kV air-gap, ± 30 -kV or ± 20 -kV contact ESD protection respectively, and has a clamp circuit with a back-to-back TVS diode for bidirectional signal support.

A typical application of this product is the ESD protection for USB-PD slower speed signals (CC1, CC2, SBU1, SBU2, D+, and D-). The $I_{PP} = 5.7$ A (8/20 μ s surge waveform) capability of the ESD752 makes it suitable for protecting VBUS. The ESD752 device is also a good fit for protecting industrial IOs requiring 5.7 A or less of surge current protection. The 3 pF or 1.7 pF line capacitance of these ESD protection diodes are suitable for USB-PD slower speed signals and industrial IO applications.

7.2 Functional Block Diagram



7.3 Feature Description

The ESD752 and ESD762 are bidirectional TVS diodes with a high ESD protection level. This device protects the circuit from ESD strikes up to ± 30 -kV or ± 20 -kV contact and ± 30 -kV or ± 20 -kV air-gap respectively as specified in the IEC 61000-4-2 standard. The ESD752 and ESD762 can also handle up to 5.7 A or 2.5 A of surge current (IEC 61000-4-5 8/20 μ s) respectively. The I/O capacitance of 3 pF or 1.7 pF (typical) are suitable for USB power delivery slower speed signals and industrial applications. These clamping devices have a small dynamic resistance, which makes the clamping voltage low when the device is actively protecting other circuits.

For example, the ESD752 clamping voltage is only 37 V when the device is taking 5.7 A transient current. The breakdown is bidirectional so these protection devices are a good fit for applications requiring positive and negative polarity protection. Low leakage allows these diodes to conserve power when working below the V_{RWM} . The temperature range of -55°C to $+150^{\circ}\text{C}$ makes this ESD device work at extensive temperatures in most environments. The leaded SOT-23 and SOT-323 (SC-70) packages are good for applications requiring automatic optical inspection (AOI).

7.3.1 Temperature Range

These devices are qualified to operate from -55°C to $+150^{\circ}\text{C}$.

7.3.2 IEC 61000-4-5 Surge Protection

The IO pins can withstand surge events up to 5.7 A and 2.5 A (8/20 μ s waveform) for the ESD752 and ESD762 respectively. An ESD-surge clamp diverts this current to ground.

7.3.3 IO Capacitance

The capacitance between the I/O pins is 3 pF and 1.7 pF for the ESD752 and ESD762 respectively. These capacitances are suitable for USB power delivery slower speed signals and industrial applications.

7.3.4 Dynamic Resistance

The IO pins feature an ESD clamp that has a low R_{DYN} of 0.35 Ω for the ESD752 device, and 0.57 Ω for the ESD762 device, which prevents system damage during ESD events.

7.3.5 DC Breakdown Voltage

The DC breakdown voltage between the IO pins is a minimum of ± 25.5 V. This protects sensitive equipment is protected from surges above the reverse standoff voltage of ± 24 V.

7.3.6 Ultra Low Leakage Current

The IO pins feature an ultra-low leakage current of 50 nA (maximum) with a bias of ± 24 V.

7.3.7 Clamping Voltage

The IO pins feature an ESD clamp that is capable of clamping the voltage to 37 V ($I_{PP} = 5.7$ A for 8/20 μ s surge waveform), 35 V ($I_{PP} = 16$ A for TLP), 36 V ($I_{PP} = 2.5$ A for 8/20 μ s surge waveform), and 38 V ($I_{PP} = 16$ A for TLP) for the ESD752 and ESD762, respectively.

7.3.8 Industry Standard Leaded Packages

These devices feature industry standard SOT-23 (DBZ) and SC-70 (DCK) leaded packages for automatic optical inspection (AOI).

7.4 Device Functional Modes

The ESD752 and ESD762 are dual channel passive clamp devices that have low leakage during normal operation when the voltage between IO and GND is below V_{RWM} , and activate when the voltage between IO and GND goes above V_{BR} . During IEC 61000-4-2 ESD events, transient voltages as high as ± 30 kV can be clamped on either channel. When the voltages on the protected lines fall below the V_{HOLD} , the device reverts back to the low leakage passive state.

8 Application and Implementation


注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

The ESD752 and ESD762 are dual channel TVS diodes which are used to provide a path to ground for dissipating ESD events on USB-PD or industrial IO signal lines. As the current from the ESD passes through the TVS, only a small voltage drop is present across the diode. This is the voltage presented to the protected IC. The low R_{DYN} of the triggered TVS holds this voltage (V_{CLAMP}) to a safe level for the protected IC.

8.2 Typical Application



USB Power Delivery Application

图 8-1. USB Power Delivery Typical Application

8.2.1 Design Requirements

For this design example, the ESD752 and ESD762 are used to provide ESD protection on a USB-PD connector. 表 8-1 lists the known design parameters for this application.

表 8-1. Design Parameters for the USB Power Delivery Typical Application

| Design Parameter | Value |
|---------------------------------|---------------|
| Diode configuration | Bidirectional |
| VBUS Voltage | + 20 V |
| V_{IO} signal range | + 3.3 V |
| V_{RWM} | ± 24 V |
| Short to VBUS event on V_{IO} | ± 20 V |


表 8-1. Design Parameters for the USB Power Delivery Typical Application (continued)

| Design Parameter | Value |
|------------------|----------------|
| Data rate | Up to 480 Mbps |


8.2.2 Detailed Design Procedure

The ESD752 and ESD762 has a V_{RWM} of ± 24 V to prevent the diode from being damaged during a short event that can occur when one of the USB-PD slower speed lines (CC1, CC2, SBU1, SBU2, D+, and D-) is shorted to VBUS. The bidirectional characteristic protects both positive and negative polarity. The low 1.7 pF capacitance of the ESD762 device enables data rates up to 480 Mbps, which allows the designer to meet the requirements for the D+ and D- signals. The ESD752 has an $I_{PP} = 5.7$ A (8/20 μ s) surge current capability making it suitable for protecting the VBUS power rail.

8.2.3 Application Curves



8-2. +8-kV Clamped IEC Waveform



8-3. -8-kV Clamped IEC Waveform

9 Power Supply Recommendations

These are passive TVS diode-based ESD protection devices; therefore, there is no requirement to power it. Ensure that the maximum voltage specifications for each pin are not violated.


10 Layout

10.1 Layout Guidelines

- The optimum placement of the device is as close to the connector as possible.
 - EMI during an ESD event can couple from the trace being struck to other nearby unprotected traces, resulting in early system failures.
 - The PCB designer must minimize the possibility of EMI coupling by keeping any unprotected traces away from the protected traces which are between the TVS and the connector.
- Route the protected traces as straight as possible.
- Eliminate any sharp corners on the protected traces between the TVS and the connector by using rounded corners with the largest radii possible.
 - Electric fields tend to build up on corners, increasing EMI coupling.
- If pin 3 is connected to ground, use a thick and short trace for this return path.

10.2 Layout Example

This is a typical example of a dual channel IO routing.



10-1. Routing with DBZ and DCK Package

11 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

11.1 Documentation Support

11.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [ESD Layout Guide user's guide](#)
- Texas Instruments, [ESD and Surge Protection for USB Interfaces application note](#)
- Texas Instruments, [ESD Protection Diodes EVM user's guide](#)
- Texas Instruments, [Generic ESD Evaluation Module user's guide](#)
- Texas Instruments, [Reading and Understanding an ESD Protection data sheet](#)

11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.3 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の [使用条件](#) を参照してください。

11.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

11.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|-----------------|--------------------------------------|----------------------|--------------|-------------------------|-------------------------|
| ESD752DBZR | ACTIVE | SOT-23 | DBZ | 3 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 150 | 2RP8 | Samples |
| ESD752DCKR | ACTIVE | SC70 | DCK | 3 | 3000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -55 to 150 | 1MP | Samples |
| ESD762DBZR | ACTIVE | SOT-23 | DBZ | 3 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 150 | 2RK8 | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| ESD752DBZR | SOT-23 | DBZ | 3 | 3000 | 180.0 | 8.4 | 2.9 | 3.35 | 1.35 | 4.0 | 8.0 | Q3 |
| ESD752DCKR | SC70 | DCK | 3 | 3000 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| ESD762DBZR | SOT-23 | DBZ | 3 | 3000 | 180.0 | 8.4 | 2.9 | 3.35 | 1.35 | 4.0 | 8.0 | Q3 |

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal


| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| ESD752DBZR | SOT-23 | DBZ | 3 | 3000 | 210.0 | 185.0 | 35.0 |
| ESD752DCKR | SC70 | DCK | 3 | 3000 | 180.0 | 180.0 | 18.0 |
| ESD762DBZR | SOT-23 | DBZ | 3 | 3000 | 210.0 | 185.0 | 35.0 |

EXAMPLE BOARD LAYOUT

DBZ0003A

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE
SCALE:15X



SOLDER MASK DETAILS

4214838/F 08/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DBZ0003A

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE
BASED ON 0.125 THICK STENCIL
SCALE:15X

4214838/F 08/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.


DCK0003A



PACKAGE OUTLINE

SOT-SC70 - 1.1 max height

SMALL OUTLINE TRANSISTOR SC70



4220745/E 08/2024

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side

EXAMPLE STENCIL DESIGN

DCK0003A

SOT-SC70 - 1.1 max height

SMALL OUTLINE TRANSISTOR SC70



SOLDER PASTE EXAMPLE
BASED ON 0.125 THICK STENCIL
SCALE:18X

4220745/E 08/2024

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
7. Board assembly site may have different recommendations for stencil design.

重要なお知らせと免責事項

TI は、技術データと信頼性データ(データシートを含みます)、設計リソース(リファレンス・デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、または [ti.com](#) やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、TI はそれらに異議を唱え、拒否します。

郵送先住所 : Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated