











SN74AUP1T34

SCES841F - JUNE 2012-REVISED APRIL 2018

# SN74AUP1T34 1-Bit Unidirectional Voltage-Level Translator

#### **Features**

- Wide Operating VCC Range of 0.9 V to 3.6 V
- Balanced Propagation Delays:  $t_{PLH} = t_{PHL}$  (1.8-V to 3.3-V Translation Typical)
- Low Static-Power Consumption: Maximum of 5-µA
- ±6-mA Output Drive at 3 V
- I<sub>off</sub> Supports Partial Power-Down-Mode Operation
- VCC Isolation Feature If V<sub>CCA</sub> Input Is at GND, B Port Is in the High-Impedance state
- Input Hysteresis Allows Slow Input Transition and Better Switching Noise Immunity at Input
- ESD Protection Exceeds JESD 22
- 5000-V Human-Body Model (A114-A)
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II

## Applications

- Enterprise
- Industrial
- Personal Electronics
- **Telecommunications**

## 3 Description

The SN74AUP1T34 device is a 1-bit noninverting translator that uses two separate configurable powersupply rails. It is a uni-directional translator from A to B. The A port is designed to track V<sub>CCA</sub>. V<sub>CCA</sub> accepts supply voltages from 0.9 V to 3.6 V. The B port is designed to track  $V_{\rm CCB}$ .  $V_{\rm CCB}$  accepts supply voltages from 0.9 V to 3.6 V. This allows for low-voltage translation between 1-V, 1.2-V, 1.5-V, 1.8-V, 2.5-V, and 3.3-V voltage nodes. The SN74AUP1T34 is also fully specified for partial-power-down applications using  $I_{\text{off}}$ . The  $I_{\text{off}}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.


The VCC isolation feature ensures that if V<sub>CCA</sub> input is at GND, the B port is in the high-impedance state. If V<sub>CCB</sub> input is at GND, any input to the A side does not cause the leakage current even floating.

## Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
SN74AUP1T34DCK	SC70 (5)	2.00 mm x 1.25 mm
SN74AUP1T34DRY	SON (6)	1.45 mm × 1.00 mm
SN74AUP1T34DSF	SON (6)	1.00 mm × 1.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### **Example Application**



**Page** 

**Page** 



#### **Table of Contents**

1	Features 1		8.3 Feature Description	
2	Applications 1		8.4 Device Functional Modes	12
3	Description 1	9	Application and Implementation	13
4	Revision History2		9.1 Application Information	13
5	Pin Configuration and Functions 4		9.2 Typical Application	1
6	Specifications5	10	Power Supply Recommendations	18
•	6.1 Absolute Maximum Ratings 5	11	Layout	1
	6.2 ESD Ratings		11.1 Layout Guidelines	1
	6.3 Recommended Operating Conditions		11.2 Layout Example	1
	6.4 Thermal Information	12	Device and Documentation Support	16
	6.5 Electrical Characteristics: DC		12.1 Support Resources	10
	6.6 Electrical Characteristics: AC		12.2 Trademarks	10
	6.7 Typical Characteristics		12.3 Electrostatic Discharge Caution	10
7	Parameter Measurement Information 11		12.4 Glossary	10
8	Detailed Description 12	13	Mechanical, Packaging, and Orderable Information	10
	8.1 Overview       12         8.2 Functional Block Diagram       12		13.1 Package Option Addendum	1

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision E (June 2016) to Revision F	Page
•	Added operating junction temperature to Absolute Maximum Ratings table	5
•	Updated Recommended Operating Conditions table	6
•	Updated the V <sub>CCB</sub> value for the parameter 'high-level input voltage' in the Recommended Operating Conditions table	6
•	Updated the $V_{\text{CCB}}$ value for the parameter 'low-level input voltage' in the Recommended Operating Conditions table .	6
•	Added Electrical Characteristics: DC table	<mark>7</mark>
_		_
C	hanges from Revision D (April 2016) to Revision E	Page

# Changes from Revision D (April 2016) to Revision E

Changed pin A number From: 3 To: 2 and GND From: 2 To: 3 for the SC70 package in the Pin Configuration and Functions section 4

#### Changes from Revision C (May 2013) to Revision D

Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and 

#### Changes from Revision B (July 2012) to Revision C

Submit Documentation Feedback

Copyright © 2012-2018, Texas Instruments Incorporated







Cł	anges from Revision A (June 2012) to Revision B	
•	Removed Feature: Output Enable Feature Allows User to Disable Outputs to Reduce Power Consumption.	1



# 5 Pin Configuration and Functions





#### **Pin Functions**

PIN			1/0	DESCRIPTION					
NAME	NAME SC70 SON	SON	1/0	DESCRIPTION					
Α	2	2	1	Input Port					
В	4	4	0	Output Port					
GND	3	3	_	Ground					
V <sub>CCA</sub>	1	1	_	Input Port DC Power Supply					
V <sub>CCB</sub>	5	6	_	Output Port DC Power Supply					
NC	_	5	_	No Connect. Leave floating.					



# 6 Specifications

## 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT	
Supply voltage, V <sub>CCA</sub> and V <sub>CCB</sub>	-0.3	4	V		
	-0.5	4.6			
Input voltage, V <sub>I</sub>		-0.5	4.6	V	
		-0.5	4.6		
Voltage applied to any output in the high impedance or pe	-0.5	4.6	V		
Voltage applied to any output in the high-impedance or po	-0.5	4.6	V		
Voltage applied to any output in the high or law state. V		-0.5	4.6	V	
Voltage applied to any output in the high or low state, $V_{\text{O}}$		-0.5	4.6	V	
Input clamp current, I <sub>IK</sub>	V <sub>I</sub> < 0 V		-50	mA	
Output clamp current, I <sub>OK</sub>	V <sub>O</sub> < 0 V		-50	mA	
Continuous output current, I <sub>O</sub>			±50	mA	
Continuous current through V <sub>CCA</sub> or GND		±100	mA		
Storage temperature, T <sub>stg</sub>		-65	150	°C	
Operating junction temperature, T <sub>J</sub>			150	°C	

6.2 ESD Ratings

			VALUE	UNIT
V	Floatrootatio dioabarga	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	5000	\/
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	750	V

JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

				MIN	NOM	MAX	UNIT
V <sub>CCA</sub>	Supply voltage			0.9		3.6	V
$V_{CCB}$	Supply voltage			0.9		3.6	V
V <sub>IH</sub>		V <sub>CCA</sub> = 0.9 V to 1.95 V	V <sub>CCB</sub> = 0.9 V to 3.6 V	0.65 × V <sub>CCA</sub>			
	High-level input voltage	$V_{CCA} = 2.3 \text{ V to } 2.7 \text{ V}$	$V_{CCB} = 0.9 \text{ V to } 3.6 \text{ V}$	1.6			V
		$V_{CCA} = 3 \text{ V to } 3.6 \text{ V}$	$V_{CCB} = 0.9 \text{ V to } 3.6 \text{ V}$	2			
	Low-level input voltage	V <sub>CCA</sub> = 0.9 V	V <sub>CCB</sub> = 0.9 V to 3.6 V			0.3 <b>x</b> V <sub>CCA</sub>	
$V_{IH}$		V <sub>CCA</sub> = 1 V to 1.95 V	V <sub>CCB</sub> = 0.9 V to 3.6 V		(	0.35 × V <sub>CCA</sub>	V
		$V_{CCA} = 2.3 \text{ V to } 2.7 \text{ V}$	$V_{CCB} = 0.9 \text{ V to } 3.6 \text{ V}$			0.7	
		$V_{CCA} = 3 \text{ V to } 3.6 \text{ V}$	$V_{CCB} = 0.9 \text{ V to } 3.6 \text{ V}$			0.9	
Δt/Δν	Input transition rise or fall rate	V <sub>CCA</sub> = 3 V to 3.6 V	V <sub>CCB</sub> = 0.9 V to 3.6 V			200	ns/V
T <sub>A</sub>	Operating free-air temperature			-40		85	°C

## 6.4 Thermal Information

			SN74AUP1T34				
	THERMAL METRIC <sup>(1)</sup>	DCK (SC70)	DRY (SON)	DSF (SON)	UNIT		
		5 PINS	6 PINS	6 PINS			
$R_{\theta JA}$	Junction-to-ambient thermal resistance	300.8	338.5	367.1	°C/W		
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	141.3	240.4	188.8	°C/W		
$R_{\theta JB}$	Junction-to-board thermal resistance	77.3	224.6	274.6	°C/W		
ΨЈТ	Junction-to-top characterization parameter	12.6	86.8	24.1	°C/W		
ΨЈВ	Junction-to-board characterization parameter	76.5	221.4	273.1	°C/W		

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



# 6.5 Electrical Characteristics: DC

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST	CONDITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN	MAX	UNIT
			$I_{OH} = -100 \mu A$	0.9 V to 3.6 V	0.9 V to 3.6 V	V <sub>CCB</sub> - 0.2		
			$I_{OH} = -0.25 \text{ mA}$	0.9 V to 1 V	0.9 V to 1 V	0.75 × V <sub>CCB</sub>		
	High-level output	., .,	$I_{OH} = -1.5 \text{ mA}$	1.2 V	1.2 V	1		.,
V <sub>OH</sub>	voltage	$V_I = V_{IH}$	$I_{OH} = -2 \text{ mA}$	1.65 V	1.65 V	1.32		V
	$I_{OH} = -3 \text{ mA}$ 2.3 V 2.3 V	1.9						
			$I_{OH} = -6 \text{ mA}$	3 V	3 V	2.72		
			$I_{OL} = 100 \mu A$	0.9 V to 3.6 V	0.9 V to 3.6 V		0.1	
			I <sub>OL</sub> = 0.25 mA	0.9 V to 1 V	0.9 V to 1 V		0.1	
.,	Low-level output	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	I <sub>OL</sub> = 1.5 mA	1.2 V	1.2 V		$0.3 \times V_{CCB}$	V
$V_{OL}$	voltage	$V_I = V_{IL}$	I <sub>OL</sub> = 2 mA	1.65 V	1.65 V		0.31	V
			I <sub>OL</sub> = 3 mA	2.3 V	2.3 V		0.31	
			I <sub>OL</sub> = 6 mA	3 V	3 V		0.31	
I <sub>I</sub>	Input leakage current	V <sub>I</sub> = VCC	A or GND	0.9 V to 3.6 V	0.9 V to 3.6 V		±1	μA
	O# state summent	A or B por	t:	0 V	0 V to 3.6 V		±5	
l <sub>off</sub>	Off-state current	$V_I$ or $V_O =$	0 to 3.6 V	0 V to 3.6 V	0 V		±5	μΑ
		V <sub>I</sub> = VCCI or GND, I <sub>O</sub> = 0 mA		0.9 V to 3.6 V	0.9 V to 3.6 V		5	
	V <sub>CCA</sub> supply			0.9 V to 3.6 V	$V_{CCA}$		2	
I <sub>CCA</sub>	current			0 V	0 V to 3.6 V		1	μΑ
				0 V to 3.6 V	0 V		1	
				0.9 V to 3.6 V	0.9 V to 3.6 V		5	
	V <sub>CCB</sub> supply	V <sub>I</sub> = VCCI	or GND,	0.9 V to 3.6 V	$V_{CCA}$		2	
I <sub>CCB</sub>	current	$I_O = 0 \text{ mA}$		0 V	0 V to 3.6 V		1	μΑ
				0 V to 3.6 V	0 V		1	
I <sub>CCA</sub> +	Combined supply current	$V_I = VCCI$ $I_O = 0 \text{ mA}$		0.9 V to 3.6 V	0.9 V to 3.6 V		5.2	μΑ
Cı	Input capacitance	V <sub>I</sub> = 3.3 V	or GND	3.3 V	3.3 V		4	pF
C <sub>I/O</sub>	Input-to-output internal capacitance	A or B por V <sub>O</sub> = 3.3 V		0 V	3.3 V		7	pF

Copyright © 2012–2018, Texas Instruments Incorporated



## 6.6 Electrical Characteristics: AC

over operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN TY	P MAX	UNIT
			0.9 V	2	25	
			1.2 V	1	8	
	C <sub>L</sub> = 5 pF	0.9 V	1.65 V	16.	2	
			2.3 V	16.	3	
			3 V	16.	8	
			0.9 V		42.5	
			1.2 V		24.9	
	C <sub>L</sub> = 5 pF	1.2 V	1.65 V		23.2	
			2.3 V		22.6	
			3 V		22.5	
			0.9 V		40	
			1.2 V		10.7	
Propagation delay time low-to-high output / high-t	C <sub>L</sub> = 5 pF	1.65 V	1.65 V		8.84	ns
iow-to-nigh output / nigh-t	5-low output		2.3 V		8.08	
			3 V		7.88	
			0.9 V		41.3	
			1.2 V		8.02	
	C <sub>L</sub> = 5 pF	2.3 V	1.65 V		5.73	
			2.3 V		4.92	
			3 V		4.2	
			0.9 V		42.5	
		3 V	1.2 V		7.61	
	C <sub>L</sub> = 5 pF		1.65 V		4.5	
	ο <sub>L</sub> = 3 μι		2.3 V		3.65	
			3 V		3.39	
			0.9 V	28.		
		0.9 V	1.2 V	19.		
	C 40 = F		1.65 V			
	C <sub>L</sub> = 10 pF			17.		
			2.3 V		8	
			3 V	18.		
		1.2 V	0.9 V		43.22	
			1.2 V		12.33	
	C <sub>L</sub> = 10 pF		1.65 V		9.57	
			2.3 V		8.81	
			3 V		8.61	
			0.9 V		40.44	
Drana matian dalau tima			1.2 V		9.21	
Propagation delay time low-to-high output / high-t	o-low output C <sub>L</sub> = 10 pF	1.65 V	1.65 V		6.57	ns
			2.3 V		5.5	
			3 V		4.73	
			0.9 V		41.56	
			1.2 V		8.3	
	C <sub>L</sub> = 10 pF	2.3 V	1.65 V		5.54	
			2.3 V		4.42	
			3 V		4.01	
			0.9 V		42.81	
			1.2 V		7.87	
	C <sub>L</sub> = 10 pF	3 V	1.65 V		4.55	
	-2 -7-		2.3 V		3.8	
			2.0 \$	1	0.0	

Submit Documentation Feedback

Copyright © 2012–2018, Texas Instruments Incorporated




# **Electrical Characteristics: AC (continued)**

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN	TYP	MAX	UNIT
				0.9 V		30.6		
			1.2 V		21.6			
	C <sub>L</sub> = 15 pF	0.9 V	1.65 V		19.6			
			2.3 V		19.7			
			3 V		20.3			
				0.9 V			43.87	
				1.2 V			12.98	
		C <sub>L</sub> = 15 pF	1.2 V	1.65 V			10.3	
				2.3 V			9.54	
				3 V			9.34	
				0.9 V			40.78	
				1.2 V			9.59	
/t <sub>PHL</sub>	Propagation delay time low-to-high output / high-to-low output	C <sub>L</sub> = 15 pF	1.65 V	1.65 V			6.95	ns
	low-to-night output / night-to-low output			2.3 V			5.87	
				3 V			5.07	
				0.9 V			41.79	
				1.2 V			8.55	
		C <sub>1</sub> = 15 pF	2.3 V	1.65 V			5.8	
		ο <sub>[</sub> = 10 μι	2.0 V	2.3 V			4.68	
			3 V			4.27		
			0.9 V			43.09		
				1.2 V				
	0 45 - 5	2 \/				8.16		
		C <sub>L</sub> = 15 pF	3 V	1.65 V			4.84	
				2.3 V			4.09	
				3 V			3.65	
		C <sub>L</sub> = 30 pF	0.9 V	0.9 V		32.1		
				1.2 V		21.3		
				1.65 V		18.7		
				2.3 V		18		
				3 V		18.3		
				0.9 V			45.65	
				1.2 V			14.76	
		C <sub>L</sub> = 30 pF	1.2 V	1.65 V			12.37	
				2.3 V			11.61	
				3 V			11.41	
				0.9 V			41.72	
				1.2 V			10.65	
t <sub>PHL</sub>	Propagation delay time low-to-high output / high-to-low output	C <sub>L</sub> = 30 pF	1.65 V	1.65 V			8.01	ns
	5			2.3 V			6.94	
				3 V			5.99	
				0.9 V			42.44	
				1.2 V			9.26	
		C <sub>L</sub> = 30 pF	2.3 V	1.65 V			6.51	
				2.3 V			5.39	
				3 V			4.97	
				0.9 V			43.69	
				1.2 V			8.8	
		C. = 30 pF	3 \/	1.65 V			5.48	
		C <sub>L</sub> = 30 pF	3 V		1		J.40	
				2.3 V			4.72	





 $\begin{aligned} &V_{MI} = &V_{IH}/2; \ V_{MO} = \ V_{CCB}/2 \\ &t_R = t_F = 2.0 \ ns, \ 10\% \ to \ 90\%; \ f = 1 \ MHz; \ t_W = 500 \ ns \end{aligned}$ 

Figure 1. Waveform 1 – Propagation Delays



## 6.7 Typical Characteristics





Figure 2. Low Level Output Voltage vs Low Level Output Current

## 7 Parameter Measurement Information



#### **TEST**

 $t_{\text{PLH}},\,t_{\text{PHL}}$ 

C<sub>L</sub> = 5 pF, 10 pF, 15 pF, 30 pF or equivalent (includes probe and jig capacitance)

 $R_L = 1 M\Omega$  or equivalent

 $Z_{OUT}$  of pulse generator = 50  $\Omega$ 

Figure 3. AC (Propagation Delay) Test Circuit

Copyright © 2012–2018, Texas Instruments Incorporated

Submit Documentation Feedback




## 8 Detailed Description

#### 8.1 Overview

The SN74AUP1T34 is a unidirectional, single-bit, dual-supply, noninverting voltage-level translator. Pin A, which is referenced to  $V_{CCA}$ , receives the signal that is to be level translated. Pin B, which is referenced to  $V_{CCB}$ , transmits the level translated signal. Both supply pins  $V_{CCA}$  and  $V_{CCB}$  support a voltage range from 0.9 V to 3.6 V.

#### 8.2 Functional Block Diagram



## 8.3 Feature Description

#### 8.3.1 Fully Configurable Dual-Rail Design

Both  $V_{CCA}$  and  $V_{CCB}$  can be supplied at any voltage from 0.9 V to 3.6 V, making the device suitable for translating between any of the voltage nodes (1 V, 1.2 V, 1.8 V, 2.5 V, and 3.3 V).

#### 8.3.2 Partial-Power-Down Mode Operation

 $I_{\text{off}}$  circuitry disables the outputs, preventing damaging current backflow through the SN74AUP1T34 when it is powered down. This can occur in applications where subsections of a system are powered down (partial-power-down) to reduce power consumption.

#### 8.3.3 V<sub>CC</sub> Isolation

The  $V_{CC}$  isolation feature ensures that if either  $V_{CCA}$  or  $V_{CCB}$  are at GND (or < 0.4 V), both ports A and B are set to a high-impedance state, preventing false logic levels from being presented to either bus.

#### 8.3.4 Input Hysteresis

Input hysteresis allows the input to support slew rates as slow as 200 ns/V, improving switching noise immunity.

#### 8.4 Device Functional Modes

Table 1 lists the functional modes of the SN74AUP1T34.

**Table 1. Function Table** 

INPUT	OUTPUT
A PORT	B PORT
L	L
Н	Н



# 9 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 9.1 Application Information

The SN74AUP1T34 can be used in level-translation applications for interfacing devices or systems operating at different interface voltages with one another.

## 9.2 Typical Application




Figure 4. Typical Application Example

#### 9.2.1 Design Requirements

Table 2 lists the design requirements of the SN74AUP1T34.

**Table 2. Design Parameters** 

DESIGN PARAMETER	EXAMPLE VALUE
Input Voltage Range	0.9 V to 3.6 V
Output Voltage Range	0.9 V to 3.6 V

## 9.2.2 Detailed Design Procedure

To begin the design process, determine the following:

- Input voltage range
  - Use the supply voltage of the device that is driving the SN74AUP1T34 device to determine the input voltage range. For a valid logic-high, the value must exceed the V<sub>IH</sub> of the input port. For a valid logic low the value must be less than the V<sub>II</sub> of the input port.
- Output voltage range
  - Use the supply voltage of the device that the SN74AUP1T34 device is driving to determine the output voltage range.



## 9.2.3 Application Curve




Figure 5. 10-MHz Up Translation (0.9 V to 3.6 V)



## 10 Power Supply Recommendations

Connect ground before applying either  $V_{CCA}$  or  $V_{CCB}$ . There is no specific power sequence requirement for the SN74AUP1T34.  $V_{CCA}$  or  $V_{CCB}$  may be powered up first, and  $V_{CCA}$  or  $V_{CCB}$  may be powered down first.


## 11 Layout

## 11.1 Layout Guidelines

To ensure reliability of the device, TI recommends following common printed-circuit board layout guidelines is recommended.

- Bypass capacitors must be used on power supplies.
- Short trace lengths must be used to avoid excessive loading.
- Placing pads on the signal paths for loading capacitors or pullup resistors helps adjust rise and fall times of signals depending on the system requirements.

#### 11.2 Layout Example






Figure 6. Example Layout

Copyright © 2012–2018, Texas Instruments Incorporated

Submit Documentation Feedback



## 12 Device and Documentation Support

## 12.1 Support Resources

TI E2E<sup>TM</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 12.2 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

## 12.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## 12.4 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

# 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



www.ti.com

# 13.1 Package Option Addendum

## 13.1.1 Packaging Information

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish <sup>(3)</sup>	MSL Peak Temp (4)	Op Temp (°C)	Device Marking <sup>(5)(6)</sup>
SN74AUP1T34DCKR	ACTIVE	SC70	DCK	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	U2Q, U2E
SN74AUP1T34DRYR	ACTIVE	SON	DRY	6	5000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	U2
SN74AUP1T34DSFR	ACTIVE	SON	DSF	6	5000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	U2

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PRE\_PROD Unannounced device, not in production, not available for mass market, nor on the web, samples not available.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.
- (4) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (5) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device
- (6) Multiple Device markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 30-Nov-2023

## TAPE AND REEL INFORMATION



# TAPE DIMENSIONS KO P1 BO W Cavity A0

A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AUP1T34DCKR	SC70	DCK	5	3000	180.0	8.4	2.3	2.5	1.2	4.0	8.0	Q3
SN74AUP1T34DRYR	SON	DRY	6	5000	180.0	9.5	1.15	1.6	0.75	4.0	8.0	Q1
SN74AUP1T34DSFR	SON	DSF	6	5000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2

www.ti.com 30-Nov-2023



## \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AUP1T34DCKR	SC70	DCK	5	3000	210.0	185.0	35.0
SN74AUP1T34DRYR	SON	DRY	6	5000	184.0	184.0	19.0
SN74AUP1T34DSFR	SON	DSF	6	5000	210.0	185.0	35.0



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.









#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.





NOTES: (continued)

3. For more information, see QFN/SON PCB application report in literature No. SLUA271 (www.ti.com/lit/slua271).





NOTES: (continued)

Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.







#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. Reference JEDEC registration MO-287, variation X2AAF.





NOTES: (continued)

4. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).





4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.





SMALL OUTLINE TRANSISTOR



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  2. This drawing is subject to change without notice.
  3. Reference JEDEC MO-203.

- 4. Support pin may differ or may not be present.5. Lead width does not comply with JEDEC.
- 6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 10. Board assembly site may have different recommendations for stencil design.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated