







CD54AC08, CD74AC08

SCHS307D - JANUARY 2001 - REVISED AUGUST 2024

# **CDx4AC08 Quadruple 2-Input Positive-and Gates**

#### 1 Features

- AC types feature 1.5V to 5.5V operation and balanced noise immunity at 30% of the supply voltage
- Speed of bipolar F, AS, and S, with significantly reduced power consumption
- Balanced propagation delays
- **Buffered inputs**
- ±24mA output drive current
  - Fanout to 15 F devices
- SCR-latchup-resistant CMOS process and circuit
- Exceeds 2kV ESD protection per MIL-STD-883, method 3015

## 2 Description

The 'AC08 devices are quadruple 2-input positive-AND gates. These devices perform the Boolean function  $Y = A \cdot B$  in positive logic.

#### **Device Information**

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE(2)	BODY SIZE(3)
	D (SOIC, 14)	8.65mm × 6mm	8.65mm × 3.9mm
CDx4AC08	N (PDIP, 14)	19.3mm × 9.4mm	19.3mm × 6.35mm
	J (CDIP, 14)	19.55mm x 7.9mm	19.55 mm x 6.7mm

- For more information, see Mechanical, Packaging, and Orderable Information.
- The package size (length × width) is a nominal value and includes pins, where applicable.
- The body size (length × width) is a nominal value and does not include pins.



Logic Diagram, Each Gate (Positive Logic)



## **Table of Contents**

1 Features1	6.1 Functional Block Diagram	. 8
2 Description1	6.2 Device Functional Modes	3.
3 Pin Configuration and Functions3	7 Application and Implementation	. 9
4 Specifications4	7.1 Power Supply Recommendations	. 9
4.1 Absolute Maximum Ratings4	7.2 Layout	. 9
4.2 ESD Ratings 4	8 Device and Documentation Support	
4.3 Recommended Operating Conditions4	8.1 Documentation Support (Analog)	
4.4 Thermal Information5	8.2 Receiving Notification of Documentation Updates	
4.5 Electrical Characteristics5	8.3 Support Resources	10
4.6 Switching Characteristics, V <sub>CC</sub> = 1.5 V5	8.4 Trademarks	10
4.7 Switching Characteristics, V <sub>CC</sub> = 3.3V ± 0.3V6	8.5 Electrostatic Discharge Caution	10
4.8 Switching Characteristics, V <sub>CC</sub> = 5V ± 0.5V6	8.6 Glossary	10
4.9 Operating Characteristics	9 Revision History	
5 Parameter Measurement Information7	10 Mechanical, Packaging, and Orderable	
6 Detailed Description8	Information	10
• • • • • • • • • • • • • • • • • • •		



# 3 Pin Configuration and Functions




Figure 3-1. CD54AC08 J Package, 14-Pin CDIP; CD74AC08 N or D Package, 14-Pin PDIP or SOIC (Top View)

**Table 3-1. Pin Functions** 

	PIN		
NAME	SOIC, PDIP, CDIP	I/O1	DESCRIPTION
1A	1	I	1A Input
1B	2	I	1B Input
1Y	3	0	1Y Output
2A	4	I	2A Input
2B	5	I	2B Input
2Y	6	0	2Y Output
3Y	8	0	3Y Output
3A	9	I	3A Input
3B	10	I	3B Input
4Y	11	0	4Y Output
4A	12	I	4A Input
4B	13	I	4B Input
GND	7	_	Ground Pin
NC	_	_	No Connection
V <sub>CC</sub>	14	_	Power Pin

1. I = input, O = output, P = power, FB = feedback, GND = ground, N/A = not applicable



## 4 Specifications

## 4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage range		-0.5	6	V
I <sub>IK</sub> (2)	Input clamp current	$(V_I < 0 \text{ or } V_I > V_{CC})$		±20	mA
I <sub>OK</sub> (2)	Output clamp current	$(V_O < 0 \text{ or } V_O > V_{CC})$		±50	mA
Io	Continuous output current	$(V_O = 0 \text{ to } V_{CC})$		±50	mA
	Continuous current through V <sub>CC</sub> or GND			±100	mA
T <sub>stg</sub>	Storage temperature range		-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 4.2 ESD Ratings

			VALUE	UNIT
V <sub>(ESD)</sub>	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2000	V

JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 500-V HBM is possible with the necessary precautions.

## 4.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

			$T_A = 2$	T <sub>A</sub> = 25°C		85°C	-55°C TO 125°C		UNIT
			MIN	MAX	MIN	MAX	MIN	MAX	UNII
V <sub>CC</sub>	Supply voltage		1.5	5.5	1.5	5.5	1.5	5.5	V
		V <sub>CC</sub> = 1.5 V	1.2		1.2		1.2		
V <sub>IH</sub> High-level input voltage	V <sub>CC</sub> = 3 V	2.1		2.1		2.1		V	
	V <sub>CC</sub> = 5.5 V	3.85		3.85		3.85			
V <sub>IL</sub> Low-level input voltage	V <sub>CC</sub> = 1.5 V		0.3		0.3		0.3		
	V <sub>CC</sub> = 3 V		0.9		0.9		0.9	V	
		V <sub>CC</sub> = 5.5 V		1.65		1.65		1.65	
VI	Input voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>	0	V <sub>CC</sub>	V
Vo	Output voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>	0	V <sub>CC</sub>	V
I <sub>OH</sub>	High-level output current	V <sub>CC</sub> = 4.5 V to 5.5 V		-24		-24		-24	mA
I <sub>OL</sub>	Low-level output current	V <sub>CC</sub> = 4.5 V to 5.5 V		24		24		24	mA
Δt/Δν	Input transition rise or fell rate	V <sub>CC</sub> = 1.5 V to 3 V		50		50		50	ns/V
Δt/Δv Input transition rise or fall rate		V <sub>CC</sub> = 3.6 V to 5.5 V		20		20		20	115/ V

<sup>(1)</sup> All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

Submit Document Feedback

<sup>(2)</sup> The input and output voltage ratings may be exceeded if the input and output current ratings are observed.



#### 4.4 Thermal Information

		CD74	AC08	
	THERMAL METRIC <sup>(1)</sup>		N (PDIP)	UNIT
			14 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	119.9	119.9 80	

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

#### 4.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CON	DITIONS	\ \ \	T <sub>A</sub> = 2	5°C	-40°C TC	85°C	-55°C TO	125°C	UNIT
PARAMETER	TEST CONDITIONS		V <sub>cc</sub>	MIN	MAX	MIN	MAX	MIN	MAX	UNII
			1.5 V	1.4		1.4		1.4		
		I <sub>OH</sub> = -50 μA	3 V	2.9		2.9		2.9		
			4.5 V	4.4		4.4		4.4		
V <sub>OH</sub>	$V_I = V_{IH}$ or $V_{IL}$	I <sub>OH</sub> = -4 mA	3 V	2.58		2.48		2.4		V
		I <sub>OH</sub> = -24 mA	4.5 V	3.94		3.8		3.7		
		I <sub>OH</sub> = -50 mA <sup>(1)</sup>	5.5 V					3.85		
		I <sub>OH</sub> = -75 mA <sup>(1)</sup>	5.5 V			3.85				
			1.5 V		0.1		0.1		0.1	
		I <sub>OL</sub> = 50 μA	3 V		0.1		0.1		0.1	
			4.5 V		0.1		0.1		0.1	
V <sub>OL</sub>	$V_I = V_{IH}$ or $V_{IL}$	I <sub>OL</sub> = 12 mA	3 V		0.36		0.44		0.5	V
		I <sub>OL</sub> = 24 mA	4.5 V		0.36		0.44		0.5	
		I <sub>OL</sub> = 50 mA <sup>(1)</sup>	5.5 V						1.65	
		I <sub>OL</sub> = 75 mA <sup>(1)</sup>	5.5 V				1.65			
I <sub>I</sub>	V <sub>I</sub> = V <sub>CC</sub> or GND		5.5 V		±0.1		±1		±1	μA
I <sub>CC</sub>	$V_I = V_{CC}$ or GND,	I <sub>O</sub> = 0	5.5 V		4		40		80	μA
C <sub>i</sub>					10		10		10	PF

<sup>(1)</sup> Test one output at a time, not exceeding 1-second duration. Measurement is made by forcing indicated current and measuring voltage to minimize power dissipation. Test verifies a minimum 50-Ω transmission-line drive capability at 85°C and 75-Ω transmission-line drive capability at 125°C.

## 4.6 Switching Characteristics, V<sub>CC</sub> = 1.5 V

over recommended operating free-air temperature range, V<sub>CC</sub> = 1.5V, C<sub>L</sub> = 50pF (unless otherwise noted) (see Figure 5-1)

PARAMETER	EDOM (INDLIT)	FROM (INPUT) TO (OUTPUT)		O 85°C	-55°C TO	O 125°C	UNIT
PARAMETER	PROM (MPOT)	10 (001701)	MIN	MAX	MIN	MAX	ONIT
t <sub>PLH</sub>	A or B	V		99		109	ns
t <sub>PHL</sub>	AOID	1		99		109	115



# 4.7 Switching Characteristics, $V_{CC} = 3.3V \pm 0.3V$

over recommended operating free-air temperature range,  $V_{CC}$  = 3.3V ± 0.3V,  $C_L$  = 50pF (unless otherwise noted) (see Figure 5-1)

PARAMETER	FROM (INPUT)	то (оитрит)	-40°C TO 85°C		–55°C 125°		UNIT
			MIN	MAX	MIN	MAX	
t <sub>PLH</sub>	A D	V	3.1	11.1	3.1	12.2	no
t <sub>PHL</sub>	A or B	T	3.1	11.1	3.1	12.2	ns

# 4.8 Switching Characteristics, $V_{CC} = 5V \pm 0.5V$

over recommended operating free-air temperature range,  $V_{CC}$  = 5V  $\pm$  0.5V,  $C_L$  = 50pF (unless otherwise noted) (see Figure 5-1)

PARAMETER	FROM (INPUT)	ТО (ОИТРИТ)	-40°C TC	-40°C TO 85°C		TO C	UNIT
			MIN	MAX	MIN	MAX	
t <sub>PLH</sub>	A or B	V	2.2	7.9	2.2	8.7	ns
t <sub>PHL</sub>	AUID	T T	2.2	7.9	2.2	8.7	115

## 4.9 Operating Characteristics


 $V_{CC} = 5 \text{ V}, T_A = 25^{\circ}\text{C}$ 

PARAMETER	TYP	UNIT
C <sub>pd</sub> Power dissipation capacitance	50	pF

Submit Document Feedback



#### **5 Parameter Measurement Information**



- A. C<sub>L</sub> includes probe and test-fixture capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz,  $Z_O = 50 \Omega$ ,  $t_r = 3$  ns,  $t_f = 3$  ns. Phase relationships between waveforms are arbitrary.
- D. For clock inputs,  $f_{max}$  is measured with the input duty cycle at 50%.
- E. The outputs are measured one at a time with one input transition per measurement.
- F. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>pd</sub>.
- G.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
- H. t<sub>PLZ</sub> and t<sub>PHZ</sub> are the same as t<sub>dis</sub>.

Figure 5-1. Load Circuit and Voltage Waveforms



## **6 Detailed Description**

## **6.1 Functional Block Diagram**



Figure 6-1. Logic Diagram, Each Gate (Positive Logic)

### **6.2 Device Functional Modes**

Function Table (Each Gate) is the function table for the CDx4AC08.

**Table 6-1. Function Table (Each Gate)** 

II	NPUTS	OUTPUT Y
Α	В	COTFOLI
Н	Н	Н
L	Х	L
Х	L	L

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated



## 7 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

#### 7.1 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the Section 4.1 table.

Each  $V_{CC}$  pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, 0.1  $\mu$ F is recommended. If there are multiple  $V_{CC}$  pins, 0.01  $\mu$ F or 0.022  $\mu$ F is recommended for each power pin. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. A 0.1  $\mu$ F and 1  $\mu$ F are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.

### 7.2 Layout

#### 7.2.1 Layout Guidelines

When using multiple bit logic devices inputs should not ever float.

In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. Specified in Figure 7-1 are the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{\rm CC}$ ; whichever makes more sense or is more convenient. It is generally acceptable to float outputs unless the part is a transceiver. If the transceiver has an output enable pin, it will disable the outputs section of the part when asserted. This will not disable the input section of the IOs, so they cannot float when disabled.

#### 7.2.2 Layout Example




Figure 7-1. Layout Example for the CDx4AC08



## 8 Device and Documentation Support

## 8.1 Documentation Support (Analog)

#### 8.1.1 Related Documentation

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 8-1. Related Links

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
CD54AC08	Click here	Click here	Click here	Click here	Click here
CD74AC08	Click here	Click here	Click here	Click here	Click here

#### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

## 8.3 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 8.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

#### 8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 8.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

#### 9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

## Changes from Revision C (June 2002) to Revision D (July 2024)

Pag

- Added Package Information table, Pin Functions table, ESD Ratings table, Thermal Information table, Device Functional Modes, Application and Implementation section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section
- Updated RθJA values: D = 86 to 119.9, all values in °C/W......5

### 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

www.ti.com 30-Jul-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
CD54AC08F3A	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	CD54AC08F3A	Samples
CD74AC08E	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD74AC08E	Samples
CD74AC08M	OBSOLETE	SOIC	D	14		TBD	Call TI	Call TI	-55 to 125	AC08M	
CD74AC08M96	ACTIVE	SOIC	D	14	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	AC08M	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and

## PACKAGE OPTION ADDENDUM

www.ti.com 30-Jul-2024

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CD54AC08, CD74AC08:

Catalog : CD74AC08

Military: CD54AC08

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 8-Oct-2024

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD74AC08M96	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CD74AC08M96	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 8-Oct-2024



#### \*All dimensions are nominal

Device		Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CD74AC08N	196	SOIC	D	14	2500	353.0	353.0	32.0
CD74AC08N	196	SOIC	D	14	2500	356.0	356.0	35.0

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 8-Oct-2024

### **TUBE**



#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
CD74AC08E	N	PDIP	14	25	506	13.97	11230	4.32
CD74AC08E	N	PDIP	14	25	506	13.97	11230	4.32

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040083-5/G





CERAMIC DUAL IN LINE PACKAGE



#### NOTES:

- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- His package is remitted by sealed with a ceramic its using glass mit.
   Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
   Falls within MIL-STD-1835 and GDIP1-T14.



CERAMIC DUAL IN LINE PACKAGE



# N (R-PDIP-T\*\*)

## PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SMALL OUTLINE INTEGRATED CIRCUIT



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
- 5. Reference JEDEC registration MS-012, variation AB.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated