SMJ320VC5416 Fixed-Point Digital Signal Processor

Data Manual

Literature Number: SGUS035A April 2003 - Revised July 2003

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.







REVISION HISTORY

| REVISION | DATE | PRODUCT STATUS | HIGHLIGHTS |
|----------|------------|-----------------|---------------|
| * | March 2003 | Production Data | Original |
| А | July 2003 | Production Data | Limit changes |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |

Contents

| Se | ction | | | Page |
|----|-------------|------------|--|------|
| 1 | SMJ32 | 0VC5416 | Features | . 1 |
| 2 | Introdu | uction | | . 2 |
| | 2.1 | Descriptio | on | . 2 |
| | 2.2 | | nments | |
| | | 2.2.1 | Pin Assignments for the HFG Package | |
| | 2.3 | Signal De | escriptions | |
| 3 | Functi | | view | |
| | 3.1 | | | |
| | | 3.1.1 | Data Memory | |
| | | 3.1.2 | Program Memory | |
| | | 3.1.3 | Extended Program Memory | |
| | 3.2 | | ROM With Bootloader | |
| | 3.3 | • | RAM | |
| | 3.4 | • | Memory Security | |
| | 3.5 | | Мар | |
| | 0.0 | 3.5.1 | Relocatable Interrupt Vector Table | |
| | 3.6 | | Peripherals | |
| | 0.0 | 3.6.1 | Software-Programmable Wait-State Generator | |
| | | 3.6.2 | Programmable Bank-Switching | |
| | | 3.6.3 | Bus Holders | |
| | 3.7 | | O Ports | |
| | 5.7 | 3.7.1 | Enhanced 8-/16-Bit Host-Port Interface (HPI8/16) | |
| | | 3.7.1 | HPI Nonmultiplexed Mode | |
| | 3.8 | | nel Buffered Serial Ports (McBSPs) | |
| | 3.8 3.9 | | | |
| | 3.9 3.10 | | | |
| | | | | |
| | 3.11 | | d External Parallel Interface (XIO2) | |
| | 3.12 | | ntroller | |
| | | 3.12.1 | | |
| | | 3.12.2 | DMA External Access | |
| | | 3.12.3 | DMA Memory Map | |
| | | 3.12.4 | DMA Priority Level | |
| | | 3.12.5 | DMA Source/Destination Address Modification | |
| | | 3.12.6 | DMA in Autoinitialization Mode | |
| | | 3.12.7 | DMA Transfer Counting | |
| | | 3.12.8 | DMA Transfer in Doubleword Mode | |
| | | 3.12.9 | DMA Channel Index Registers | |
| | | 3.12.10 | DMA Interrupts | |
| | | 3.12.11 | DMA Controller Synchronization Events | |
| | 3.13 | | Purpose I/O Pins | |
| | | 3.13.1 | McBSP Pins as General-Purpose I/O | |
| | | 3.13.2 | HPI Data Pins as General-Purpose I/O | |
| | 3.14 | Device ID |) Register | 35 |
| | 3.15 | Memory-I | Mapped Registers | 35 |
| | 3.16 | | Control Registers and Subaddresses | |
| | 3.17 | DMA Sub | bank Addressed Registers | 39 |

| | 3.18 | | S | |
|---|---------|----------------------|---|----|
| 4 | Docun | nentation | Support | 42 |
| 5 | Electri | | ifications | |
| | 5.1 | | Maximum Ratings | |
| | 5.2 | | nended Operating Conditions | 43 |
| | 5.3 | Electrica (Unless | Il Characteristics Over Recommended Operating Case Temperature Range Otherwise Noted) | 44 |
| | 5.4 | Package | Thermal Resistance Characteristics | 45 |
| | 5.5 | Timing F | Parameter Symbology | 45 |
| | 5.6 | Internal | Oscillator With External Crystal | 45 |
| | 5.7 | Clock O | ptions | 46 |
| | | 5.7.1 | Divide-By-Two and Divide-By-Four Clock Options | 46 |
| | | 5.7.2 | Multiply-By-N Clock Option (PLL Enabled) | 48 |
| | 5.8 | Memory | and Parallel I/O Interface Timing | 49 |
| | | 5.8.1 | Memory Read | 49 |
| | | 5.8.2 | Memory Write | 52 |
| | | 5.8.3 | I/O Read | 53 |
| | | 5.8.4 | I/O Write | 54 |
| | 5.9 | Ready T | iming for Externally Generated Wait States | 55 |
| | 5.10 | | nd HOLDA Timings | |
| | 5.11 | Reset, B | BIO, Interrupt, and MP/MC Timings | 62 |
| | 5.12 | Instructio | on Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings | 64 |
| | 5.13 | External | Flag (XF) and TOUT Timings | 65 |
| | 5.14 | Multicha | nnel Buffered Serial Port (McBSP) Timing | 66 |
| | | 5.14.1 | McBSP Transmit and Receive Timings | 66 |
| | | 5.14.2 | McBSP General-Purpose I/O Timing | 69 |
| | | 5.14.3 | McBSP as SPI Master or Slave Timing | 70 |
| | 5.15 | Host-Po | rt Interface Timing | 74 |
| | | 5.15.1 | HPI8 Mode | 74 |
| | | 5.15.2 | HPI16 Mode | 78 |
| 6 | Mecha | nical Dat | a | 82 |
| | 6.1 | Ceramic | Quad Flatpack Mechanical Data | 82 |

List of Figures

| Figure | Page |
|--|------|
| 2-1. 164-Pin HFG Ceramic Quad Flatpack (Top View) | 4 |
| 3-1. SMJ320VC5416 Functional Block Diagram | . 10 |
| 3-2. Program and Data Memory Map | . 13 |
| 3-3. Extended Program Memory Map | . 13 |
| 3-4. Processor Mode Status (PMST) Register | . 14 |
| 3-5. Software Wait-State Register (SWWSR) [Memory-Mapped Register (MMR) Address 0028h] | . 16 |
| 3-6. Software Wait-State Control Register (SWCR) [MMR Address 002Bh] | . 17 |
| 3-7. Bank-Switching Control Register (BSCR) [MMR Address 0029h] | . 17 |
| 3-8. Host-Port Interface — Nonmultiplexed Mode | . 20 |
| 3-9. HPI Memory Map | . 21 |
| 3-10. Multichannel Control Registers (MCR1 and MCR2) | . 23 |
| 3-11. Pin Control Register (PCR) | . 23 |
| 3-12. Nonconsecutive Memory Read and I/O Read Bus Sequence | . 26 |
| 3-13. Consecutive Memory Read Bus Sequence (n = 3 reads) | . 27 |
| 3-14. Memory Write and I/O Write Bus Sequence | . 28 |
| 3-15. DMA Transfer Mode Control Register (DMMCRn) | . 29 |
| 3-16. On-Chip DMA Memory Map for Program Space (DLAXS = 0 and SLAXS = 0) | . 30 |
| 3-17. On-Chip DMA Memory Map for Data and IO Space (DLAXS = 0 and SLAXS = 0) | . 31 |
| 3-18. DMPREC Register | . 32 |
| 3-19. General-Purpose I/O Control Register (GPIOCR) [MMR Address 003Ch] | . 34 |
| 3-20. General-Purpose I/O Status Register (GPIOSR) [MMR Address 003Dh] | . 34 |
| 3-21. Device ID Register (CSIDR) [MMR Address 003Eh] | . 35 |
| 3-22. IFR and IMR | . 41 |
| 5-1. 3.3-V Test Load Circuit | . 44 |
| 5-2. Internal Divide-by-Two Clock Option With External Crystal | . 46 |
| 5-3. External Divide-by-Two Clock Timing | . 47 |
| 5-4. Multiply-by-One Clock Timing | . 48 |
| 5-5. Nonconsecutive Mode Memory Reads | . 50 |
| 5-6. Consecutive Mode Memory Reads | . 51 |
| 5-7. Memory Write (MSTRB = 0) | . 52 |
| 5-8. Parallel I/O Port Read (IOSTRB = 0) | . 53 |
| 5-9. Parallel I/O Port Write (IOSTRB = 0) | . 54 |
| 5-10. Memory Read With Externally Generated Wait States | . 56 |
| 5-11. Memory Write With Externally Generated Wait States | . 57 |
| 5-12. I/O Read With Externally Generated Wait States | . 58 |
| 5-13. I/O Write With Externally Generated Wait States | . 59 |
| 5-14. HOLD and HOLDA Timings (HM = 1) | . 61 |
| 5-15. Reset and BIO Timings | . 63 |
| 5-16. Interrupt Timing | . 63 |
| 5-17. MP/MC Timing | . 63 |

Figures

| 5-18. | Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings | 64 |
|--------|--|----|
| 5-19. | External Flag (XF) Timing | 65 |
| 5-20. | TOUT Timing | 65 |
| 5-21. | McBSP Receive Timings | 67 |
| 5-22. | McBSP Transmit Timings | 68 |
| 5-23. | McBSP General-Purpose I/O Timings | 69 |
| 5-24. | McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 0 | 70 |
| 5-25. | McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 0 | 71 |
| 5-26. | McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 1 | 72 |
| 5-27. | McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 1 | 73 |
| 5-28. | Using HDS to Control Accesses (HCS Always Low) | 76 |
| 5-29. | Using HCS to Control Accesses | 77 |
| 5-30. | HINT Timing | 77 |
| 5-31. | GPIOx Timings | 77 |
| 5-32. | Nonmultiplexed Read Timings | 80 |
| 5-33. | Nonmultiplexed Write Timings | 81 |
| 5-34. | HRDY Relative to CLKOUT | 81 |
| 6-1. 5 | SMJ320VC5416 164-Pin Ceramic Quad Flatpack (HFG) | 82 |

List of Tables

| Table H | Page |
|--|---|
| 2-1. Terminal Assignments for the SMJ320VC5416HFG (164-Pin CQFP Package)† 2-2. Signal Descriptions 3-1. Standard On-Chip ROM Layout† 3-2. Processor Mode Status (PMST) Register Bit Fields 3-3. Software Wait-State Register (SWWSR) Bit Fields 3-4. Software Wait-State Control Register (SWCR) Bit Fields 3-5. Bank-Switching Control Register (BSCR) Fields 3-6. Bus Holder Control Bits 3-7. Sample Rate Input Clock Selection 3-8. Clock Mode Settings at Reset 3-9. DMD Section of the DMMCRn Register | 5 . 12 . 15 . 16 . 17 . 18 . 19 . 23 . 25 . 30 |
| 3-10. DMA Reload Register Selection | |
| 3–12. DMA Synchronization Events | |
| 3-13. DMA Channel Interrupt Selection | |
| 3-14. CPU Memory-Mapped Registers | . 35 |
| 3-15. Peripheral Memory-Mapped Registers for Each DSP Subsystem | . 37 |
| 3-16. McBSP Control Registers and Subaddresses | |
| 3-17. DMA Subbank Addressed Registers | |
| 3-18. Interrupt Locations and Priorities | |
| 5-1. Thermal Resistance Characteristics | |
| 5-2. Input Clock Frequency Characteristics | |
| 5-3. Clock Mode Pin Settings for the Divide-By-2 and By Divide-by-4 Clock Options | |
| 5-4. Divide-By-2 and Divide-by-4 Clock Options Timing Requirements | |
| 5-5. Divide-By-2 and Divide-by-4 Clock Options Switching Characteristics | |
| 5-6. Multiply-By-N Clock Option Timing Requirements | |
| 5-7. Multiply-By-N Clock Option Switching Characteristics | |
| 5-8. Memory Read Timing Requirements | |
| 5-9. Memory Read Switching Characteristics | |
| 5-10. Memory Write Switching Characteristics | |
| 5-11. I/O Read Switching Characteristics | |
| 5-13. I/O Write Switching Characteristics | |
| 5-14. Ready Timing Requirements for Externally Generated Wait States† | |
| 5-15. Ready Switching Characteristics for Externally Generated Wait States 1 | |
| 5-16. HOLD and HOLDA Timing Requirements | |
| 5-17. HOLD and HOLDA Switching Characteristics | |
| 5–18. Reset, BIO, Interrupt, and MP/MC Timing Requirements | |
| 5–19. Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Switching Characteristics | |
| 5-20. External Flag (XF) and TOUT Switching Characteristics | |
| 5-21. McBSP Transmit and Receive Timing Requirements† | |
| 5-22. McBSP Transmit and Receive Switching Characteristics† | |
| 5-23. McBSP General-Purpose I/O Timing Requirements | |
| 5-24. McBSP General-Purpose I/O Switching Characteristics | |
| 5-25. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 0)† | |
| 5-26. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 0)† | |

Tables

| 5-27. | McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 0)† | 71 |
|-------|---|----|
| 5-28. | McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 0)† | 71 |
| 5-29. | McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 1)† | 72 |
| 5-30. | McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 1)† | 72 |
| 5-31. | McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 1)† | 73 |
| 5-32. | McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 1)† | 73 |
| 5-33. | HPI8 Mode Timing Requirements | 74 |
| 5-34. | HPI8 Mode Switching Characteristics | 75 |
| 5-35. | HPI16 Mode Timing Requirements | 78 |
| 5-36. | HPI16 Mode Switching Characteristics | 79 |

1 SMJ320VC5416 Features

- Processed to MIL-PRF-38535 (QML)
- Advanced Multibus Architecture With Three Separate 16-Bit Data Memory Buses and One Program Memory Bus
- 40-Bit Arithmetic Logic Unit (ALU) Including a 40-Bit Barrel Shifter and Two Independent 40-Bit Accumulators
- 17 x 17-Bit Parallel Multiplier Coupled to a 40-Bit Dedicated Adder for Non-Pipelined Single-Cycle Multiply/Accumulate (MAC) Operation
- Compare, Select, and Store Unit (CSSU) for the Add/Compare Selection of the Viterbi Operator
- Exponent Encoder to Compute an Exponent Value of a 40-Bit Accumulator Value in a Single Cycle
- Two Address Generators With Eight Auxiliary Registers and Two Auxiliary Register Arithmetic Units (ARAUs)
- Data Bus With a Bus Holder Feature
- Extended Addressing Mode for 8M x 16-Bit Maximum Addressable External Program Space
- 128K x 16-Bit On-Chip RAM Composed of:
 - Eight Blocks of 8K x 16-Bit On-Chip Dual-Access Program/Data RAM
 - Eight Blocks of 8K x 16-Bit On-Chip Single-Access Program RAM
- 16K x 16-Bit On-Chip ROM Configured for Program Memory
- Enhanced External Parallel Interface (XIO2)
- Single-Instruction-Repeat and Block-Repeat Operations for Program Code
- Block-Memory-Move Instructions for Better Program and Data Management

- Instructions With a 32-Bit Long Word Operand
- Instructions With Two- or Three-Operand Reads
- Arithmetic Instructions With Parallel Store and Parallel Load
- Conditional Store Instructions
- Fast Return From Interrupt
- On-Chip Peripherals
 - Software-Programmable Wait-State Generator and Programmable Bank-Switching
 - On-Chip Programmable Phase-Locked Loop (PLL) Clock Generator With External Clock Source
 - One 16-Bit Timer
 - Six-Channel Direct Memory Access (DMA) Controller
 - Three Multichannel Buffered Serial Ports (McBSPs)
 - 8/16-Bit Enhanced Parallel Host-Port Interface (HPI8/16)
- Power Consumption Control With IDLE1, IDLE2, and IDLE3 Instructions With Power-Down Modes
- CLKOUT Off Control to Disable CLKOUT
- On-Chip Scan-Based Emulation Logic, IEEE Std 1149.1[†] (JTAG) Boundary Scan Logic
- 164-Pin Ceramic Quad Flatpack (CQFP) (HFG Suffix)
- 10-ns Single-Cycle Fixed-Point Instruction Execution Time (100 MIPS)
- 3.3-V I/O Supply Voltage
- 1.5-V Core Supply Voltage
- -55°C to 115°C Operating Temperature Range, QML Processing



[†] IEEE Standard 1149.1-1990 Standard-Test-Access Port and Boundary Scan Architecture.

2 Introduction

This section describes the main features of the SMJ320VC5416, lists the pin assignments, and describes the function of each pin. This data manual also provides a detailed description section, electrical specifications, parameter measurement information, and mechanical data about the available packaging.

NOTE: This data manual is designed to be used in conjunction with the *TMS320C54x[™] DSP Functional Overview* (literature number SPRU307).

2.1 Description

The SMJ320VC5416 fixed-point, digital signal processor (DSP) (hereafter referred to as the 5416 unless otherwise specified) is based on an advanced modified Harvard architecture that has one program memory bus and three data memory buses. This processor provides an arithmetic logic unit (ALU) with a high degree of parallelism, application-specific hardware logic, on-chip memory, and additional on-chip peripherals. The basis of the operational flexibility and speed of this DSP is a highly specialized instruction set.

Separate program and data spaces allow simultaneous access to program instructions and data, providing a high degree of parallelism. Two read operations and one write operation can be performed in a single cycle. Instructions with parallel store and application-specific instructions can fully utilize this architecture. In addition, data can be transferred between data and program spaces. Such parallelism supports a powerful set of arithmetic, logic, and bit-manipulation operations that can all be performed in a single machine cycle. The 5416 also includes the control mechanisms to manage interrupts, repeated operations, and function calls.

2.2 Pin Assignments

Figure 2-1 provides the pin assignments for the 164-pin ceramic quad flatpack (CQFP) package.

Table 2-2 lists terminal names, terminal functions, and operating modes for the SMJ320VC5416.


| PIN NUMBER | PIN NAME |
|------------|------------------|------------|------------------|------------|------------------|------------|------------------|
| 1 | V _{SS} | 42 | V _{SS} | 83 | V _{SS} | 124 | A19 |
| 2 | NC | 43 | BCLKR1 | 84 | BCLKX1 | 125 | A20 |
| 3 | A22 | 44 | HCNTL0 | 85 | BFSX1 | 126 | NC |
| 4 | NC | 45 | V _{SS} | 86 | BDX1 | 127 | V _{SS} |
| 5 | V _{SS} | 46 | BCLKR0 | 87 | DV _{DD} | 128 | DV_DD |
| 6 | DV _{DD} | 47 | BCLKR2 | 88 | CLKMD1 | 129 | D6 |
| 7 | A10 | 48 | BFSR0 | 89 | CLKMD2 | 130 | D7 |
| 8 | HD7 | 49 | BFSR2 | 90 | CLKMD3 | 131 | D8 |
| 9 | A11 | 50 | BDR0 | 91 | HPI16 | 132 | D9 |
| 10 | A12 | 51 | HCNTL1 | 92 | HD2 | 133 | D10 |
| 11 | A13 | 52 | V _{SS} | 93 | TOUT | 134 | D11 |
| 12 | A14 | 53 | BDR2 | 94 | EMU0 | 135 | V _{SS} |
| 13 | A15 | 54 | CV _{DD} | 95 | EMU1/OFF | 136 | CV _{DD} |
| 14 | NC | 55 | BCLKX0 | 96 | TDO | 137 | D12 |
| 15 | CV _{DD} | 56 | BCLKX2 | 97 | V _{SS} | 138 | HD4 |
| 16 | HAS | 57 | NC | 98 | TDI | 139 | D13 |
| 17 | V _{SS} | 58 | V _{SS} | 99 | CV _{DD} | 140 | D14 |
| 18 | CV _{DD} | 59 | HINT | 100 | TRST | 141 | D15 |
| 19 | HCS | 60 | NC | 101 | ТСК | 142 | HD5 |
| 20 | HR/W | 61 | CV _{DD} | 102 | TMS | 143 | V_{SS} |
| 21 | READY | 62 | BFSX0 | 103 | V _{SS} | 144 | NC |
| 22 | PS | 63 | BFSX2 | 104 | NC | 145 | HDS1 |
| 23 | CV _{DD} | 64 | HRDY | 105 | CV _{DD} | 146 | V _{SS} |
| 24 | DS | 65 | DV _{DD} | 106 | HPIENA | 147 | HDS2 |
| 25 | V _{SS} | 66 | V _{SS} | 107 | V _{SS} | 148 | DV _{DD} |
| 26 | IS | 67 | HD0 | 108 | CV _{DD} | 149 | A0 |
| 27 | R/W | 68 | BDX0 | 109 | CLKOUT | 150 | A1 |
| 28 | MSTRB | 69 | BDX2 | 110 | HD3 | 151 | CV _{DD} |
| 29 | IOSTRB | 70 | CV _{DD} | 111 | X1 | 152 | A2 |
| 30 | MSC | 71 | IACK | 112 | X2/CLKIN | 153 | V _{SS} |
| 31 | XF | 72 | V _{SS} | 113 | RS | 154 | A3 |
| 32 | HOLDA | 73 | HBIL | 114 | D0 | 155 | HD6 |
| 33 | IAQ | 74 | NMI | 115 | D1 | 156 | A4 |
| 34 | HOLD | 75 | INTO | 116 | D2 | 157 | A5 |
| 35 | BIO | 76 | INT1 | 117 | D3 | 158 | A6 |
| 36 | MP/MC | 77 | INT2 | 118 | D4 | 159 | A7 |
| 37 | DV _{DD} | 78 | INT3 | 119 | D5 | 160 | A8 |
| 38 | NC | 79 | NC | 120 | A16 | 161 | A9 |
| 39 | V _{SS} | 80 | CV _{DD} | 121 | V _{SS} | 162 | CV _{DD} |
| 40 | BDR1 | 81 | HD1 | 122 | A17 | 163 | A21 |
| 41 | BFSR1 | 82 | NC | 123 | A18 | 164 | V _{SS} |

Table 2-1. Terminal Assignments for the SMJ320VC5416HFG (164-Pin CQFP Package) †

[†] DV_{DD} is the power supply for the I/O pins while CV_{DD} is the power supply for the core CPU, and V_{SS} is the ground for both the I/O pins and the core CPU.

2.2.1 Pin Assignments for the HFG Package

The SMJ320VC5416HFG 164-pin ceramic quad flatpack (CQFP) pin assignments are shown in Figure 2-1.



NC - No internal connection

[†] NC = No connection

[‡] DV_{DD} is the power supply for the I/O pins while CV_{DD} is the power supply for the core CPU, and V_{SS} is the ground for both the I/O pins and the core CPU.

Figure 2-1. 164-Pin HFG Ceramic Quad Flatpack (Top View)

2.3 **Signal Descriptions**

Table 2-2 lists each signal, function, and operating mode(s) grouped by function. See Section 2.2 for exact pin locations based on package type.

| T | ERMINAL NAME | I/O† | DESCRIPTION |
|---|-----------------|---------------------|---|
| | | | DATA SIGNALS |
| A22 A21 A20 A19 A18 A17 A16 A15 A14 A13 A12 A11 A10 A9 A8 A7 A6 A5 A4 A3 A2 A1 A0 | (MSB) | I/O/Z‡§ | Parallel address bus A22 [most significant bit (MSB)] through A0 [least significant bit (LSB)]. The sixteen LSB lines, A0 to A15, are multiplexed to address external memory (program, data) or I/O. The seven MSB lines, A16 to A22, address external program space memory. A22-A0 is placed in the high-impedance state in the hold mode. A22-A0 also goes into the high-impedance state when OFF is low. A17-A0 are inputs in HPI16 mode. These pins can be used to address internal memory via the host-port interface (HPI) when the HPI16 pin is high. These pins also have Schmitt trigger inputs. The address bus has a bus holder feature that eliminates passive components and the power dissipation associated with them. The bus holder keeps the address bus at the previous logic level when the bus goes into a high-impedance state. |
| D15 D14 D13 D12 D11 D9 D8 D7 D6 D5 D4 D5 D4 D3 D2 D1 D0 | (MSB) | I/O/Z ^{‡§} | Parallel data bus D15 (MSB) through D0 (LSB). D15-D0 is multiplexed to transfer data between the core CPU and external data/program memory or I/O devices or HPI in HPI16 mode (when HPI16 pin is high). D15-D0 is placed in the high-impedance state when not outputting data or when RS or HOLD is asserted. D15-D0 also goes into the high-impedance state when OFF is low. These pins also have Schmitt trigger inputs. The data bus has a bus holder feature that eliminates passive components and the power dissipation associated with them. The bus holder keeps the data bus at the previous logic level when the bus goes into the high-impedance state. The bus holders on the data bus can be enabled/disabled under software control. |

Table 2-2. Signal Descriptions

[†] I = Input, O = Output, Z = High-impedance, S = Supply [‡] These pins have Schmitt trigger inputs.

§ This pin has an internal bus holder controlled by way of the BSCR register.

[¶] This pin has an internal pullup resistor.

[#] This pin has an internal pulldown resistor.

| TERMINAL NAME | I/O† | DESCRIPTION |
|--|------|---|
| | | INITIALIZATION, INTERRUPT AND RESET OPERATIONS |
| IACK | O/Z | Interrupt acknowledge signal. IACK indicates receipt of an interrupt and that the program counter is fetching the interrupt vector location designated by A15-A0. IACK also goes into the high-impedance state when OFF is low. |
| INT0 [‡] INT1 [‡] INT2 [‡] INT3 [‡] | I | External user interrupt inputs. INT0-INT3 are maskable and are prioritized by the interrupt mask register (IMR) and the interrupt mode bit. INT0 -INT3 can be polled and reset by way of the interrupt flag register (IFR). |
| NMI‡ | I | Nonmaskable interrupt. $\overline{\text{NMI}}$ is an external interrupt that cannot be masked by way of the INTM or the IMR. When $\overline{\text{NMI}}$ is activated, the processor traps to the appropriate vector location. |
| RS‡ | I | Reset. RS causes the digital signal processor (DSP) to terminate execution and forces the program counter to 0FF80h. When RS is brought to a high level, execution begins at location 0FF80h of program memory. RS affects various registers and status bits. |
| MP/MC | I | Microprocessor/microcomputer mode select. If active low at reset, microcomputer mode is selected, and the internal program ROM is mapped into the upper 16K words of program memory space. If the pin is driven high during reset, microprocessor mode is selected, and the on-chip ROM is removed from program space. This pin is only sampled at reset, and the MP/MC bit of the processor mode status (PMST) register can override the mode that is selected at reset. |
| | | MULTIPROCESSING SIGNALS |
| BIO‡ | I | Branch control. A branch can be conditionally executed when BIO is active. If low, the processor executes the conditional instruction. The BIO condition is sampled during the decode phase of the pipeline for the XC instruction, and all other instructions sample BIO during the read phase of the pipeline. |
| XF | O/Z | External flag output (latched software-programmable signal). XF is set high by the SSBX XF instruction, set low by RSBX XF instruction or by loading ST1. XF is used for signaling other processors in multiprocessor configurations or used as a general-purpose output pin. XF goes into the high-impedance state when OFF is low, and is set high at reset. |
| | | MEMORY CONTROL SIGNALS |
| <u>ଅପ</u> ଅମ୍ ଅ | O/Z | Data, program, and I/O space select signals. DS, PS, and IS are always high unless driven low for communicating to a particular external space. Active period corresponds to valid address information. DS, PS, and IS are placed into the high-impedance state in the hold mode; these signals also go into the high-impedance state when OFF is low. |
| MSTRB | O/Z | Memory strobe signal. MSTRB is always high unless low-level asserted to indicate an external bus access to data or program memory. MSTRB is placed in the high-impedance state in the hold mode; it also goes into the high-impedance state when OFF is low. |
| READY | I | Data ready. READY indicates that an external device is prepared for a bus transaction to be completed. If the device is not ready (READY is low), the processor waits one cycle and checks READY again. Note that the processor performs ready detection if at least two software wait states are programmed. The READY signal is not sampled until the completion of the software wait states. |
| R/W | O/Z | Read/write signal. R/W indicates transfer direction during communication to an external device. R/W is normally in the read mode (high), unless it is asserted low when the DSP performs a write operation. R/W is placed in the high-impedance state in the hold mode; and it also goes into the high-impedance state when \overline{OFF} is low. |
| IOSTRB | O/Z | I/O strobe signal. IOSTRB is always high unless low-level asserted to indicate an external bus access to an I/O device. IOSTRB is placed in the high-impedance state in the hold mode; it also goes into the high-impedance state when OFF is low. |
| HOLD | I | Hold input. HOLD is asserted to request control of the address, data, and control lines. When acknowledged by the 5416, these lines go into the high-impedance state. |

[†] I = Input, O = Output, Z = High-impedance, S = Supply
[‡] These pins have Schmitt trigger inputs.
[§] This pin has an internal bus holder controlled by way of the BSCR register.
[¶] This pin has an internal pullup resistor.
[#] This pin has an internal pulldown resistor.

| TERMINAL NAME | I/O† | DESCRIPTION |
|---|-----------|--|
| | | MEMORY CONTROL SIGNALS (CONTINUED) |
| HOLDA | O/Z | Hold acknowledge. HOLDA indicates to the external circuitry that the processor is in a hold state and that the address, data, and control lines are in the high-impedance state, allowing them to be available to the external circuitry. HOLDA also goes into the high-impedance state when OFF is low. This pin is driven high during reset. |
| MSC | O/Z | Microstate complete. $\overline{\text{MSC}}$ indicates completion of all software wait states. When two or more software wait states are enabled, the $\overline{\text{MSC}}$ pin goes active at the beginning of the first software wait state and goes inactive high at the beginning of the last software wait state. If connected to the READY input, $\overline{\text{MSC}}$ forces one external wait state after the last internal wait state is completed. $\overline{\text{MSC}}$ also goes into the high-impedance state when $\overline{\text{OFF}}$ is low. |
| IAQ | O/Z | Instruction acquisition signal. IAQ is asserted (active low) when there is an instruction address on the address bus and goes into the high-impedance state when OFF is low. |
| | | TIMER SIGNALS |
| CLKOUT | O/Z | Clock output signal. CLKOUT can represent the machine-cycle rate of the CPU divided by 1, 2, 3, or 4 as configured in the bank-switching control register (BSCR). Following reset, CLKOUT represents the machine-cycle rate divided by 4. |
| CLKMD1 [‡] CLKMD2 [‡] CLKMD3 [‡] | I | Clock mode select signals. CLKMD1-CLKMD3 allow the selection and configuration of different clock modes such as crystal, external clock, and PLL mode. The external CLKMD1-CLKMD3 pins are sampled to determine the desired clock generation mode while $\overline{\text{RS}}$ is low. Following reset, the clock generation mode can be reconfigured by writing to the internal clock mode register in software. |
| X2/CLKIN [‡] | I | Clock/oscillator input. If the internal oscillator is not being used, X2/CLKIN functions as the clock input. (This is revision-dependent, see Section 3.10 for additional information.) |
| X1 | 0 | Output pin from the internal oscillator for the crystal. If the internal oscillator is not used, X1 should be left unconnected. X1 does not go into the high-impedance state when OFF is low. (This is revision-dependent, see Section 3.10 for additional information.) |
| TOUT | O/Z | Timer output. TOUT signals a pulse when the on-chip timer counts down past zero. The pulse is one CLKOUT cycle wide. TOUT also goes into the high-impedance state when OFF is low. |
| MULTICH | ANNEL BUF | FERED SERIAL PORT 0 (McBSP #0), MULTICHANNEL BUFFERED SERIAL PORT 1 (McBSP #1), AND MULTICHANNEL BUFFERED SERIAL PORT 2 (McBSP #2) SIGNALS |
| BCLKR0 [‡] BCLKR1 [‡] BCLKR2 [‡] | I/O/Z | Receive clock input. BCLKR can be configured as an input or an output; it is configured as an input following reset. BCLKR serves as the serial shift clock for the buffered serial port receiver. |
| BDR0 BDR1 BDR2 | I | Serial data receive input |
| BFSR0 BFSR1 BFSR2 | I/O/Z | Frame synchronization pulse for receive input. BFSR can be configured as an input or an output; it is configured as an input following reset. The BFSR pulse initiates the receive data process over BDR. |
| BCLKX0 [‡] BCLKX1 [‡] BCLKX2 [‡] | I/O/Z | Transmit clock. BCLKX serves as the serial shift clock for the McBSP transmitter. BCLKX can be configured as an input or an output, and is configured as an input following reset. BCLKX enters the high-impedance state when OFF goes low. |
| BDX0 BDX1 BDX2 | O/Z | Serial data transmit output. BDX is placed in the high-impedance state when not transmitting, when RS is asserted, or when OFF is low. |
| BFSX0 BFSX1 BFSX2 | I/O/Z | Frame synchronization pulse for transmit input/output. The BFSX pulse initiates the data transmit process over BDX. BFSX can be configured as an input or an output, and is configured as an input following reset. BFSX goes into the high-impedance state when OFF is low. gh-impedance, S = Supply |

¹ These pins have Schmitt trigger inputs.
 [§] This pin has an internal bus holder controlled by way of the BSCR register.
 [¶] This pin has an internal pullup resistor.
 [#] This pin has an internal pulldown resistor.

| TERMINAL NAME | I/O† | DESCRIPTION |
|--|-------|---|
| | | HOST-PORT INTERFACE SIGNALS |
| HD0-HD7 ^{‡§} | I/O/Z | Parallel bidirectional data bus. The HPI data bus is used by a host device bus to exchange information with the HPI registers. These pins can also be used as general-purpose I/O pins. HD0-HD7 is placed in the high-impedance state when not outputting data or when OFF is low. The HPI data bus includes bus holders to reduce the static power dissipation caused by floating, unused pins. When the HPI data bus is not being driven by the 5416, the bus holders keep the pins at the previous logic level. The HPI data bus holders are disabled at reset and can be enabled/disabled via the HBH bit of the BSCR. These pins also have Schmitt trigger inputs. |
| HCNTL0 [¶] HCNTL1 [¶] | I | Control inputs. HCNTL0 and HCNTL1 select a host access to one of the three HPI registers. The control inputs have internal pullups that are only enabled when HPIENA = 0. These pins are not used when HPI16 = 1. |
| HBIL [¶] | I | Byte identification. HBIL identifies the first or second byte of transfer. The HPIL input has an internal pullup resistor that is only enabled when HPIENA = 0. This pin is not used when HPI16 = 1. |
| HCS ^{‡¶} | I | Chip select. \overline{HCS} is the select input for the HPI and must be driven low during accesses. The chip select input has an internal pullup resistor that is only enabled when HPIENA = 0. |
| HDS1 [‡] ¶ HDS2 [‡] ¶ | I | Data strobe. $\overline{\text{HDS1}}$ and $\overline{\text{HDS2}}$ are driven by the host read and write strobes to control the transfer. The strobe inputs have internal pullup resistors that are only enabled when HPIENA = 0. |
| HAS ^{‡¶} | I | Address strobe. Host with multiplexed address and data pins requires \overline{HAS} to latch the address in the HPIA register. \overline{HAS} input has an internal pullup resistor that is only enabled when HPIENA = 0. |
| HR/₩ [¶] | I | Read/write. HR/ \overline{W} controls the direction of the HPI transfer. HR/ \overline{W} has an internal pullup resistor that is only enabled when HPIENA = 0. |
| HRDY | O/Z | Ready output. HRDY goes into the high-impedance state when \overline{OFF} is low. The ready output informs the host when the HPI is ready for the next transfer. This pin is driven high during reset. |
| HINT | O/Z | Interrupt output. This output is used to interrupt the host. When the DSP is in reset, \overline{HINT} is driven high. \overline{HINT} goes into the high-impedance state when \overline{OFF} is low. This pin is not used when HPI16 = 1. |
| HPIENA [#] | I | HPI module select. HPIENA must be tied to DV_{DD} to have HPI selected. If HPIENA is left open or connected to ground, the HPI module is not selected, internal pullup for the HPI input pins are enabled, and the HPI data bus has holders set. HPIENA is provided with an internal pulldown resistor that is always active. HPIENA is sampled when $\overline{\text{RS}}$ goes high and is ignored until $\overline{\text{RS}}$ goes low again. This pin should never be changed while reset is high |
| HPI16 [#] | I | HPI16 mode selection |
| | | SUPPLY PINS |
| CV _{SS} | S | Ground. Dedicated ground for the core CPU |
| CV _{DD} | S | +V _{DD} . Dedicated power supply for the core CPU |
| DV _{SS} | S | Ground. Dedicated ground for I/O pins |
| DV _{DD} | S | +V _{DD} . Dedicated power supply for I/O pins |

[†] I = Input, O = Output, Z = High-impedance, S = Supply
 [‡] These pins have Schmitt trigger inputs.
 [§] This pin has an internal bus holder controlled by way of the BSCR register.


[¶] This pin has an internal pullup resistor.

[#] This pin has an internal pulldown resistor.

| TERMINAL NAME | I/O† | DESCRIPTION |
|-------------------|-------|--|
| | | TEST PINS |
| TCK ^{‡¶} | I | IEEE standard 1149.1 test clock. TCK is normally a free-running clock signal with a 50% duty cycle. The changes on test access port (TAP) of input signals TMS and TDI are clocked into the TAP controller, instruction register, or selected test data register on the rising edge of TCK. Changes at the TAP output signal (TDO) occur on the falling edge of TCK. |
| TDI¶ | I | IEEE standard 1149.1 test data input. Pin with internal pullup device. TDI is clocked into the selected register (instruction or data) on a rising edge of TCK. |
| TDO | O/Z | IEEE standard 1149.1 test data output. The contents of the selected register (instruction or data) are shifted out of TDO on the falling edge of TCK. TDO is in the high-impedance state except when the scanning of data is in progress. TDO also goes into the high-impedance state when OFF is low. |
| TMS [¶] | I | IEEE standard 1149.1 test mode select. Pin with internal pullup device. This serial control input is clocked into the TAP controller on the rising edge of TCK. |
| TRST# | I | IEEE standard 1149.1 test reset. TRST, when high, gives the IEEE standard 1149.1 scan system control of the operations of the device. If TRST is not connected or driven low, the device operates in its functional mode, and the IEEE standard 1149.1 signals are ignored. Pin with internal pulldown device. |
| EMU0 | I/O/Z | Emulator 0 pin. When TRST is driven low, EMU0 must be high for activation of the OFF condition. When TRST is driven high, EMU0 is used as an interrupt to or from the emulator system and is defined as input/output by way of the IEEE standard 1149.1 scan system. |
| EMU1/OFF | I/O/Z | Emulator 1 pin/disable all outputs. When TRST is driven high, EMU1/OFF is used as an interrupt to or from the emulator system and is defined as input/output by way of IEEE standard 1149.1 scan system. When TRST is driven low, EMU1/OFF is configured as OFF. The EMU1/OFF signal, when active low, puts all output drivers into the high-impedance state. Note that OFF is used exclusively for testing and emulation purposes (not for multiprocessing applications). Therefore, for the OFF condition, the following apply: TRST = low, EMU0 = high EMU1/OFF = low |

[†] I = Input, O = Output, Z = High-impedance, S = Supply
[‡] These pins have Schmitt trigger inputs.
[§] This pin has an internal bus holder controlled by way of the BSCR register.
[¶] This pin has an internal pullup resistor.
[#] This pin has an internal pulldown resistor.

3 Functional Overview



The following functional overview is based on the block diagram in Figure 3-1.

Figure 3-1. SMJ320VC5416 Functional Block Diagram

3.1 Memory

The 5416 device provides both on-chip ROM and RAM memories to aid in system performance and integration.

3.1.1 Data Memory

The data memory space addresses up to 64K of 16-bit words. The device automatically accesses the on-chip RAM when addressing within its bounds. When an address is generated outside the RAM bounds, the device automatically generates an external access.

The advantages of operating from on-chip memory are as follows:

- Higher performance because no wait states are required
- Higher performance because of better flow within the pipeline of the central arithmetic logic unit (CALU)
- Lower cost than external memory
- Lower power than external memory

The advantage of operating from off-chip memory is the ability to access a larger address space.

3.1.2 Program Memory

Software can configure their memory cells to reside inside or outside of the program address map. When the cells are mapped into program space, the device automatically accesses them when their addresses are within bounds. When the program-address generation (PAGEN) logic generates an address outside its bounds, the device automatically generates an external access. The advantages of operating from on-chip memory are as follows:

- Higher performance because no wait states are required
- Lower cost than external memory
- Lower power than external memory

The advantage of operating from off-chip memory is the ability to access a larger address space.

3.1.3 Extended Program Memory

The 5416 uses a paged extended memory scheme in program space to allow access of up to 8192K of program memory. In order to implement this scheme, the 5416 includes several features which are also present on C548/549/5410:

- Twenty-three address lines, instead of sixteen
- An extra memory-mapped register, the XPC
- Six extra instructions for addressing extended program space

Program memory in the 5416 is organized into 128 pages that are each 64K in length.

The value of the XPC register defines the page selection. This register is memory-mapped into data space to address 001Eh. At a hardware reset, the XPC is initialized to 0.

3.2 On-Chip ROM With Bootloader

The 5416 features a 16K-word \times 16-bit on-chip maskable ROM that can only be mapped into program memory space.

Customers can arrange to have the ROM of the 5416 programmed with contents unique to any particular application.

A bootloader is available in the standard 5416 on-chip ROM. This bootloader can be used to automatically transfer user code from an external source to anywhere in the program memory at power up. If MP/\overline{MC} of the device is sampled low during a hardware reset, execution begins at location FF80h of the on-chip ROM. This location contains a branch instruction to the start of the bootloader program.

The standard 5416 devices provide different ways to download the code to accommodate various system requirements:

- Parallel from 8-bit or 16-bit-wide EPROM
- Parallel from I/O space, 8-bit or 16-bit mode
- Serial boot from serial ports, 8-bit or 16-bit mode
- Host-port interface boot
- Warm boot

The standard on-chip ROM layout is shown in Table 3-1.

| ADDRESS RANGE | DESCRIPTION |
|---------------|---|
| C000h-D4FFh | ROM tables for the GSM EFR speech codec |
| D500h-F7FFh | Reserved |
| F800h-FBFFh | Bootloader |
| FC00h-FCFFh | μ-Law expansion table |
| FD00h-FDFFh | A-Law expansion table |
| FE00h-FEFFh | Sine look-up table |
| FF00h-FF7Fh | Reserved [†] |
| FF80h-FFFFh | Interrupt vector table |

Table 3-1. Standard On-Chip ROM Layout[†]

[†] In the 5416 ROM, 128 words are reserved for factory device-testing purposes. Application code to be implemented in on-chip ROM must reserve these 128 words at addresses FF00h-FF7Fh in program space.

3.3 On-Chip RAM

The 5416 device contains 64K-word \times 16-bit of on-chip dual-access RAM (DARAM) and 64K-word \times 16-bit of on-chip single-access RAM (SARAM).


The DARAM is composed of eight blocks of 8K words each. Each block in the DARAM can support two reads in one cycle, or a read and a write in one cycle. Four blocks of DARAM are located in the address range 0080h-7FFFh in data space, and can be mapped into program/data space by setting the OVLY bit to one. The other four blocks of DARAM are located in the address range 18000h-1FFFFh in program space. The DARAM located in the address range 18000h-1FFFFh in program space by setting the OVLY bit to one. The DARAM located in the address range 18000h-1FFFFh in program space can be mapped into data space by setting the DROM bit to one.

The SARAM is composed of eight blocks of 8K words each. Each of these eight blocks is a single-access memory. For example, an instruction word can be fetched from one SARAM block in the same cycle as a data word is written to another SARAM block. The SARAM is located in the address range 28000h–2FFFFh, and 38000h–3FFFFh in program space.

3.4 On-Chip Memory Security


The 5416 device has a maskable option to protect the contents of on-chip memories. When the ROM protect bit is set, no externally originating instruction can access the on-chip memory spaces; HPI writes have no restriction, but HPI reads are restricted to 4000h – 5FFFh.


3.5 Memory Map





DARAM0: 0080h-1FFFh; DARAM2: 4000h-5FFFh; DARAM4: 8000h-9FFFh; DARAM6: C000h-DFFFh; DARAM1: 2000h-3FFFh DARAM3: 6000h-7FFFh DARAM5: A000h-BFFFh DARAM7: E000h-FFFFh







3.5.1 Relocatable Interrupt Vector Table

The reset, interrupt, and trap vectors are addressed in program space. These vectors are soft — meaning that the processor, when taking the trap, loads the program counter (PC) with the trap address and executes the code at the vector location. Four words, either two 1-word instructions or one 2-word instruction, are reserved at each vector location to accommodate a delayed branch instruction which allows branching to the appropriate interrupt service routine without the overhead.

At device reset, the reset, interrupt, and trap vectors are mapped to address FF80h in program space. However, these vectors can be remapped to the beginning of any 128-word page in program space after device reset. This is done by loading the interrupt vector pointer (IPTR) bits in the PMST register with the appropriate 128-word page boundary address. After loading IPTR, any user interrupt or trap vector is mapped to the new 128-word page.

NOTE: The hardware reset (RS) vector cannot be remapped because the hardware reset loads the IPTR with 1s. Therefore, the reset vector is always fetched at location FF80h in program space.

| 15 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|---------|---|-------|-------|-------|-------|------------|-------|-------|
| IPTR | | MP/MC | OVLY | AVIS | DROM | CLK OFF | SMUL | SST |
| B/W-1FF | | MP/MC | R/W-0 | R/W-0 | R/W-0 | R/W-0 | R/W-0 | R/W-0 |
| | | Pin | | | | | | |

LEGEND: R = Read, W = Write

Figure 3-4. Processor Mode Status (PMST) Register

| | BIT | RESET | |
|------|--------|--------------|---|
| NO. | NAME | VALUE | FUNCTION |
| 15-7 | IPTR | 1FFh | Interrupt vector pointer. The 9-bit IPTR field points to the 128-word program page where the interrupt vectors reside. The interrupt vectors can be remapped to RAM for boot-loaded operations. At reset, these bits are all set to 1; the reset vector always resides at address FF80h in program memory space. The RESET instruction does not affect this field. |
| 6 | MP/MC | MP/MC pin | Microprocessor/microcomputer mode. MP/MC enables/disables the on-chip ROM to be addressable in program memory space. MP/MC = 0: The on-chip ROM is enabled and addressable. MP/MC = 1: The on-chip ROM is not available. MP/MC is set to the value corresponding to the logic level on the MP/MC pin when sampled at reset. This pin is not sampled again until the next reset. The RESET instruction does not affect this bit. This bit can also be set or cleared by software. |
| 5 | OVLY | 0 | RAM overlay. OVLY enables on-chip dual-access data RAM blocks to be mapped into program space. The values for the OVLY bit are: OVLY = 0: The on-chip RAM is addressable in data space but not in program space. OVLY = 1: The on-chip RAM is mapped into program space and data space. Data page 0 (addresses 0h to 7Fh), however, is not mapped into program space. |
| 4 | AVIS | 0 | Address visibility mode. AVIS enables/disables the internal program address to be visible at the address pins. AVIS = 0: The external address lines do not change with the internal program address. Control and data lines are not affected and the address bus is driven with the last address on the bus. AVIS = 1: This mode allows the internal program address to appear at the pins of the 5416 so that the internal program address can be traced. Also, it allows the interrupt vector to be decoded in conjunction with IACK when the interrupt vectors reside on on-chip memory. |
| 3 | DROM | 0 | DROM enables on-chip DARAM4-7 to be mapped into data space. The DROM bit values are: DROM = 0: The on-chip DARAM4-7 is not mapped into data space. DROM = 1: The on-chip DARAM4-7 is mapped into data space. |
| 2 | CLKOFF | 0 | CLOCKOUT off. When the CLKOFF bit is 1, the output of CLKOUT is disabled and remains at a high level. |
| 1 | SMUL | N/A | Saturation on multiplication. When SMUL = 1, saturation of a multiplication result occurs before performing the accumulation in a MAC of MAS instruction. The SMUL bit applies only when $OVM = 1$ and FRCT = 1. |
| 0 | SST | N/A | Saturation on store. When SST = 1, saturation of the data from the accumulator is enabled before storing in memory. The saturation is performed after the shift operation. |

| Table 3-2. | Processor | Mode | Status | (PMST) | Register | Bit Fields |
|------------|-----------|------|--------|--------|----------|------------|
|------------|-----------|------|--------|--------|----------|------------|

3.6 On-Chip Peripherals

The 5416 device has the following peripherals:

- Software-programmable wait-state generator
- Programmable bank-switching
- A host-port interface (HPI8/16)
- Three multichannel buffered serial ports (McBSPs)
- A hardware timer
- A clock generator with a multiple phase-locked loop (PLL)
- Enhanced external parallel interface (XIO2)
- A DMA controller (DMA)

3.6.1 Software-Programmable Wait-State Generator

The software wait-state generator of the 5416 can extend external bus cycles by up to fourteen machine cycles. Devices that require more than fourteen wait states can be interfaced using the hardware READY line. When all external accesses are configured for zero wait states, the internal clocks to the wait-state generator are automatically disabled. Disabling the wait-state generator clocks reduces the power consumption of the 5416.

The software wait-state register (SWWSR) controls the operation of the wait-state generator. The 14 LSBs of the SWWSR specify the number of wait states (0 to 7) to be inserted for external memory accesses to five separate address ranges. This allows a different number of wait states for each of the five address ranges. Additionally, the software wait-state multiplier (SWSM) bit of the software wait-state control register (SWCR) defines a multiplication factor of 1 or 2 for the number of wait states. At reset, the wait-state generator is initialized to provide seven wait states on all external memory accesses. The SWWSR bit fields are shown in Figure 3–5 and described in Table 3–3.

| _ | 15 | 14 | | 12 | 11 | | 9 | 8 | | 6 | 5 | | 3 | 2 | | 0 |
|---|-------|----|---------|----|----|---------|---|---|---------|---|---|---------|---|---|---------|---|
| | XPA | | I/O | | | Data | | | Data | | | Program | | | Program | |
| | R/W-0 | | R/W-111 | | | R/W-111 | | | R/W-111 | | | R/W-111 | | | R/W-111 | |

LEGEND: R=Read, W=Write, 0=Value after reset

Figure 3-5. Software Wait-State Register (SWWSR) [Memory-Mapped Register (MMR) Address 0028h]

| | BIT | RESET | FUNCTION |
|-------|---------|-------|--|
| NO. | NAME | VALUE | FUNCTION |
| 15 | XPA | 0 | Extended program address control bit. XPA is used in conjunction with the program space fields (bits 0 through 5) to select the address range for program space wait states. |
| 14-12 | I/O | 111 | I/O space. The field value (0-7) corresponds to the base number of wait states for I/O space accesses within addresses 0000-FFFFh. The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. |
| 11-9 | Data | 111 | Upper data space. The field value (0-7) corresponds to the base number of wait states for external data space accesses within addresses 8000-FFFFh. The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. |
| 8-6 | Data | 111 | Lower data space. The field value (0-7) corresponds to the base number of wait states for external data space accesses within addresses 0000-7FFFh. The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. |
| 5-3 | Program | 111 | Upper program space. The field value (0-7) corresponds to the base number of wait states for external program space accesses within the following addresses: XPA = 0: xx8000 - xxFFFh |
| 0.0 | riogram | | XPA = 1: 400000h - 7FFFFFh The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. |
| | | | Program space. The field value (0-7) corresponds to the base number of wait states for external program space accesses within the following addresses: |
| 2-0 | Program | 111 | □ XPA = 0: xx0000 - xx7FFFh |
| | | | XPA = 1: 000000 - 3FFFFFh |
| | | | The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. |

Table 3-3. Software Wait-State Register (SWWSR) Bit Fields

The software wait-state multiplier bit of the software wait-state control register (SWCR) is used to extend the base number of wait states selected by the SWWSR. The SWCR bit fields are shown in Figure 3–6 and described in Table 3–4.

| _ | 15 1 | 0 |
|---|----------|-------|
| | Reserved | SWSM |
| | R/W-0 | R/W-0 |

LEGEND: R = Read, W = Write

...

Figure 3-6. Software Wait-State Control Register (SWCR) [MMR Address 002Bh]

| | PIN | RESET | | | | | | |
|------|----------|-------|--|--|--|--|--|--|
| NO. | NAME | VALUE | FUNCTION | | | | | |
| 15-1 | Reserved | 0 | hese bits are reserved and are unaffected by writes. | | | | | |
| | | | Software wait-state multiplier. Used to multiply the number of wait states defined in the SWWSR by a factor of 1 or 2. | | | | | |
| 0 | SWSM | 0 | SWSM = 0: wait-state base values are unchanged (multiplied by 1). | | | | | |
| | | | SWSM = 1: wait-state base values are multiplied by 2 for a maximum of 14 wait states. | | | | | |

Table 3-4. Software Wait-State Control Register (SWCR) Bit Fields

3.6.2 Programmable Bank-Switching

Programmable bank-switching logic allows the 5416 to switch between external memory banks without requiring external wait states for memories that need additional time to turn off. The bank-switching logic automatically inserts one cycle when accesses cross a 32K-word memory-bank boundary inside program or data space.

Bank-switching is defined by the bank-switching control register (BSCR), which is memory-mapped at address 0029h. The bit fields of the BSCR are shown in Figure 3–7 and are described in Table 3–5.

R = Read, W = Write

| 15 | 14 | 13 | 12 | 11 | 2 | 1 | 0 | |
|--------|-----|------|---------|----------|-------|-------|-----|--|
| CONSEC | DIV | FCT | IACKOFF | Reserved | HBH | BH | Res | |
| R/W-1 | R/V | /-11 | R/W-1 | R | R/W-0 | R/W-0 | R | |

Figure 3-7. Bank-Switching Control Register (BSCR) [MMR Address 0029h]

| BIT | NAME | RESET VALUE | | FUNCTION | | | | |
|-------|---------------------|----------------|-----------------|--|--|--|--|--|
| | | | Consecutive ba | nk-switching. Specifies the bank-switching mode. | | | | |
| 15 | CONSEC [†] | 1 | CONSEC = 0: | Bank-switching on 32K bank boundaries only. This bit is cleared if fast access is desired for continuous memory reads (i.e., no starting and trailing cycles between read cycles). | | | | |
| | | | CONSEC = 1: | Consecutive bank switches on external memory reads. Each read cycle consists of 3 cycles: starting cycle, read cycle, and trailing cycle. | | | | |
| | | | | t divide factor. The CLKOUT output is driven by an on-chip source having a frequency FCT+1) of the DSP clock. | | | | |
| | | | DIVFCT = 00: | CLKOUT is not divided. | | | | |
| 13-14 | DIVFCT | 11 | DIVFCT = 01: | CLKOUT is divided by 2 from the DSP clock. | | | | |
| | | | DIVFCT = 10: | CLKOUT is divided by 3 from the DSP clock. | | | | |
| | | | DIVFCT = 11: | CLKOUT is divided by 4 from the DSP clock (default value following reset). | | | | |
| | | | IACK signal out | put off. Controls the output of the IACK signal. IACKOFF is set to 1 at reset. | | | | |
| 12 | IACKOFF | 1 | IACKOFF = 0: | The IACK signal output off function is disabled. | | | | |
| | | | IACKOFF = 1: | The IACK signal output off function is enabled. | | | | |
| 11-3 | Rsvd | - | Reserved | | | | | |
| | | | HPI bus holder. | Controls the HPI bus holder. HBH is cleared to 0 at reset. | | | | |
| 2 | нвн | 0 | HBH = 0: | The bus holder is disabled except when HPI16 = 1. | | | | |
| | | | HBH = 1: | The bus holder is enabled. When not driven, the HPI data bus, HD[7:0] is held in the previous logic level. | | | | |
| | | | Bus holder. Cor | trols the bus holder. BH is cleared to 0 at reset. | | | | |
| 1 | вн | 0 | BH = 0: | The bus holder is disabled. | | | | |
| | DIT | Ū | BH = 1: | The bus holder is enabled. When not driven, the data bus, D[15:0] is held in the previous logic level. | | | | |
| 0 | Rsvd | - | Reserved | | | | | |

| Table 3-5. | Bank-Switching | Control | Register | (BSCR) | Fields |
|------------|-----------------------|---------|----------|--------|--------|
|------------|-----------------------|---------|----------|--------|--------|

[†] For additional information, see Section 3.11 of this document.

The 5416 has an internal register that holds the MSB of the last address used for a read or write operation in program or data space. In the non-consecutive bank switches ($\overline{CONSEC} = 0$), if the MSB of the address used for the current read does not match that contained in this internal register, the \overline{MSTRB} (memory strobe) signal is not asserted for one CLKOUT cycle. During this extra cycle, the address bus switches to the new address. The contents of the internal register are replaced with the MSB for the read of the current address. If the MSB of the address used for the current read matches the bits in the register, a normal read cycle occurs.

In non-consecutive bank switches (CONSEC = 0), if repeated reads are performed from the same memory bank, no extra cycles are inserted. When a read is performed from a different memory bank, memory conflicts are avoided by inserting an extra cycle. For more information, see Section 3.11 of this document.

The bank-switching mechanism automatically inserts one extra cycle in the following cases:

- A memory read followed by another memory read from a different memory bank.
- A program-memory read followed by a data-memory read.
- A data-memory read followed by a program-memory read.
- A program-memory read followed by another program-memory read from a different page.

3.6.3 Bus Holders

The 5416 has two bus holder control bits, BH (BSCR[1]) and HBH (BSCR[2]), to control the bus keepers of the address bus (A[17-0]), data bus (D[15-0]), and the HPI data bus (HD[7-0]). Bus keeper enabling/disabling is described in Table 3-5.

| HPI16 PIN | BH | НВН | D[15-0] | A[17-0] | HD[7-0] |
|-----------|----|-----|---------|---------|---------|
| 0 | 0 | 0 | OFF | OFF | OFF |
| 0 | 0 | 1 | OFF | OFF | ON |
| 0 | 1 | 0 | ON | OFF | OFF |
| 0 | 1 | 1 | ON | OFF | ON |
| 1 | 0 | 0 | OFF | OFF | ON |
| 1 | 0 | 1 | OFF | ON | ON |
| 1 | 1 | 0 | ON | OFF | ON |
| 1 | 1 | 1 | ON | ON | ON |

Table 3-6. Bus Holder Control Bits

3.7 Parallel I/O Ports

The 5416 has a total of 64K I/O ports. These ports can be addressed by the PORTR instruction or the PORTW instruction. The IS signal indicates a read/write operation through an I/O port. The 5416 can interface easily with external devices through the I/O ports while requiring minimal off-chip address-decoding circuits.

3.7.1 Enhanced 8-/16-Bit Host-Port Interface (HPI8/16)

The 5416 host-port interface, also referred to as the HPI8/16, is an enhanced version of the standard 8-bit HPI found on earlier TMS320C54x[™] DSPs (542, 545, 548, and 549). The 5416 HPI can be used to interface to an 8-bit or 16-bit host. When the address and data buses for external I/O is not used (to interface to external devices in program/data/IO spaces), the 5416 HPI can be configured as an HPI16 to interface to a 16-bit host. This configuration can be accomplished by connecting the HPI16 pin to logic "1".

When the HPI16 pin is connected to a logic "0", the 5416 HPI is configured as an HPI8. The HPI8 is an 8-bit parallel port for interprocessor communication. The features of the HPI8 include:

Standard features:

- Sequential transfers (with autoincrement) or random-access transfers
- Host interrupt and C54x[™] interrupt capability
- Multiple data strobes and control pins for interface flexibility

The HPI8 interface consists of an 8-bit bidirectional data bus and various control signals. Sixteen-bit transfers are accomplished in two parts with the HBIL input designating high or low byte. The host communicates with the HPI8 through three dedicated registers — the HPI address register (HPIA), the HPI data register (HPID), and the HPI control register (HPIC). The HPIA and HPID registers are only accessible by the host, and the HPIC register is accessible by both the host and the 5416.

Enhanced features:

- Access to entire on-chip RAM through DMA bus
- Capability to continue transferring during emulation stop

TMS320C54x and C54x are trademarks of Texas Instruments.

The HPI16 is an enhanced 16-bit version of the TMS320C54x[™] DSP 8-bit host-port interface (HPI8). The HPI16 is designed to allow a 16-bit host to access the DSP on-chip memory, with the host acting as the master of the interface. Some of the features of the HPI16 include:

- 16-bit bidirectional data bus
- · Multiple data strobes and control signals to allow glueless interfacing to a variety of hosts
- Only nonmultiplexed address/data modes are supported
- 18-bit address bus used in nonmultiplexed mode to allow access to all internal memory (including internal extended address pages)
- HRDY signal to hold off host accesses due to DMA latency
- The HPI16 acts as a slave to a 16-bit host processor and allows access to the on-chip memory of the DSP.

NOTE: Only the nonmultiplexed mode is supported when the 5416 HPI is configured as a HPI16 (see Figure 3-8).

The 5416 HPI functions as a slave and enables the host processor to access the on-chip memory. A major enhancement to the 5416 HPI over previous versions is that it allows host access to the entire on-chip memory range of the DSP. The host and the DSP both have access to the on-chip RAM at all times and host accesses are always synchronized to the DSP clock. If the host and the DSP contend for access to the same location, the host has priority, and the DSP waits for one cycle. Note that since host accesses are always synchronized to the 5416 clock, an active input clock (CLKIN) is required for HPI accesses during IDLE states, and host accesses are not allowed while the 5416 reset pin is asserted.

3.7.2 HPI Nonmultiplexed Mode

In *nonmultiplexed* mode, a host with separate address/data buses can access the HPI16 data register (HPID) via the HD 16-bit bidirectional data bus, and the address register (HPIA) via the 18-bit HA address bus. The host initiates the access with the strobe signals (HDS1, HDS2, HCS) and controls the direction of the access with the HR/W signal. The HPI16 can stall host accesses via the HRDY signal. Note that the HPIC register is not available in *nonmultiplexed* mode since there are no HCNTL signals available. All host accesses initiate a DMA read or write access. Figure 3-8 shows a block diagram of the HPI16 in *nonmultiplexed* mode.




Figure 3-8. Host-Port Interface — Nonmultiplexed Mode

| Address (Hex) | |
|---------------|--------------------|
| 000 0000 | Reserved |
| 000 005F | |
| 000 0060 | |
| 000 007F | Scratch-Pad RAM |
| 000 0080 | |
| 000 7FFF | DARAM0 - DARAM3 |
| 000 8000 | |
| 001 7FFF | Reserved |
| 001 8000 | |
| 001 FFFF | DARAM4 - DARAM7 |
| 002 0000 | |
| | Reserved |
| 002 7FFF | |
| 002 8000 | |
| 002 FFFF | SARAMO - SARAM3 |
| 003 0000 | |
| | Reserved |
| 003 7FFF | |
| 003 8000 | SARAM4 - SARAM7 |
| 003 FFFF | |
| 004 0000 | |
| 07F FFFF | Reserved |

Figure 3-9. HPI Memory Map

3.8 Multichannel Buffered Serial Ports (McBSPs)

The 5416 device provides three high-speed, full-duplex, multichannel buffered serial ports that allow direct interface to other C54x/LC54x devices, codecs, and other devices in a system. The McBSPs are based on the standard serial-port interface found on other 54x devices. Like their predecessors, the McBSPs provide:

- Full-duplex communication
- Double-buffer data registers, which allow a continuous data stream
- Independent framing and clocking for receive and transmit

In addition, the McBSPs have the following capabilities:

- Direct interface to:
 - T1/E1 framers
 - MVIP switching compatible and ST-BUS compliant devices
 - IOM-2 compliant devices
 - AC97-compliant devices
 - IIS-compliant devices
 - Serial peripheral interface
- Multichannel transmit and receive of up to 128 channels
- A wide selection of data sizes, including 8, 12, 16, 20, 24, or 32 bits
- μ-law and A-law companding
- Programmable polarity for both frame synchronization and data clocks
- Programmable internal clock and frame generation

The McBSP consists of a data path and control path. The six pins, BDX, BDR, BFSX, BFSR, BCLKX, and BCLKR, connect the control and data paths to external devices. The implemented pins can be programmed as general-purpose I/O pins if they are not used for serial communication.

The data is communicated to devices interfacing to the McBSP by way of the data transmit (BDX) pin for transmit and the data receive (BDR) pin for receive. The CPU or DMA reads the received data from the data receive register (DRR) and writes the data to be transmitted to the data transmit register (DXR). Data written to the DXR is shifted out to BDX by way of the transmit shift register (XSR). Similarly, receive data on the BDR pin is shifted into the receive shift register (RSR) and copied into the receive buffer register (RBR). RBR is then copied to DRR, which can be read by the CPU or DMA. This allows internal data movement and external data communications simultaneously.

Control information in the form of clocking and frame synchronization is communicated by way of BCLKX, BCLKR, BFSX, and BFSR. The device communicates to the McBSP by way of 16-bit-wide control registers accessible via the internal peripheral bus.

The control block consists of internal clock generation, frame synchronization signal generation, and their control, and multichannel selection. This control block sends notification of important events to the CPU and DMA by way of two interrupt signals, XINT and RINT, and two event signals, XEVT and REVT.

The on-chip companding hardware allows compression and expansion of data in either μ -law or A-law format. When companding is used, transmitted data is encoded according to the specified companding law and received data is decoded to 2s complement format.

The sample rate generator provides the McBSP with several means of selecting clocking and framing for both the receiver and transmitter. Both the receiver and transmitter can select clocking and framing independently.

The McBSP allows the multiple channels to be independently selected for the transmitter and receiver. When multiple channels are selected, each frame represents a time-division multiplexed (TDM) data stream. In using time-division multiplexed data streams, the CPU may only need to process a few of them. Thus, to save memory and bus bandwidth, multichannel selection allows independent enabling of particular channels for transmission and reception. All 128 channels in a bit stream consisting of a maximum of 128 channels can be enabled.

| 15 | | 10 | 9 | 8 7 | 6 5 | 4 2 | 1 0 |
|----|----------|----|-------|--------|--------|-------|------------|
| | Reserved | | ХМСМЕ | XPBBLK | XPABLK | XCBLK | ХМСМ |
| | R | | R/W | R/W | R/W | R | R/W |
| | | | | | | | |
| 15 | | 10 | 9 | 8 7 | 65 | 4 2 | 1 0 |
| | Reserved | | RMCME | RPBBLK | RPABLK | RCBLK | Resvd RMCM |
| | R | | R/W | R/W | R/W | R | R R/W |

LEGEND: R = Read, W = Write

Figure 3-10. Multichannel Control Registers (MCR1 and MCR2)

The 5416 McBSP has two working modes:

- In the first mode, when (R/X)MCME = 0, it is comparable with the McBSPs used in the 5410 where the normal 32-channel selection is enabled (default).
- In the second mode, when (R/X)MCME = 1, it has 128-channel selection capability. Multichannel control register Bit 9, (R/X)MCME, is used as the 128-channel selection enable bit. Once (R/X)MCME = 1, twelve new registers ((R/X)CERC (R/X)CERH) are used to enable the 128-channel selection.

The clock stop mode (CLKSTP) in the McBSP provides compatibility with the serial port interface protocol. Clock stop mode works with only single-phase frames and one word per frame. The word sizes supported by the McBSP are programmable for 8-, 12-, 16-, 20-, 24-, or 32-bit operation. When the McBSP is configured to operate in SPI mode, both the transmitter and the receiver operate together as a master or as a slave.

Although the BCLKS pin is not available on the 5416 HFG package, the 5416 is capable of synchronization to external clock sources. BCLKX or BCLKR can be used by the sample rate generator for external synchronization. The sample rate clock mode extended (SCLKME) bit field is located in the PCR to accommodate this option.

| 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
|--------|-----------|---------|---------|------|------|-------|-------|
| Res | erved | XIOEN | RIOEN | FSXM | FSRM | CLKXM | CLKRM |
| F | W | RW | RW | RW | RW | RW | RW |
| 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SCLKME | CLKS STAT | DX STAT | DR STAT | FSXP | FSRP | CLKXP | CLKRP |
| RW | RW | RW | RW | RW | RW | RW | RW |

Legend: R = Read, W = Write

Figure 3-11. Pin Control Register (PCR)

The selection of sample rate input clock is made by the combination of the CLKSM (bit 13 in SRGR2) bit value and the SCLKME bit value as shown in Table 3–7.

| | - | • |
|--------|-------|---------------------------------|
| SCLKME | CLKSM | SAMPLE RATE CLOCK MODE |
| 0 | 0 | Reserved (CLKS pin unavailable) |
| 0 | 1 | CPU clock |
| 1 | 0 | BCLKR |
| 1 | 1 | BCLKX |

When the SCLKME bit is cleared to 0, the CLKSM bit is used, as before, to select either the CPU clock or the CLKS pin (not bonded out on the 5416 device package) as the sample rate input clock. Setting the SCLKME bit to 1 enables the CLKSM bit to select between the BCLKR pin or BCLKX pin for the sample rate input clock.

When either the BCLKR or CLKX is configured this way, the output buffer for the selected pin is automatically disabled. For example, with SCLKME = 1 and CLKSM = 0, the BCLKR pin is configured as the input of the sample rate generator. Both the transmitter and receiver circuits can be synchronized to the sample rate generator output by setting the CLKXM and CLKRM bits of the pin configuration register (PCR) to 1. Note that the sample rate generator output will only be driven on the BCLKX pin since the BCLKR output buffer is automatically disabled.

The McBSP is fully static and operates at arbitrary low clock frequencies. For maximum operating frequency, see Section 5.14.

3.9 Hardware Timer

The 5416 device features a 16-bit timing circuit with a 4-bit prescaler. The timer counter is decremented by one every CLKOUT cycle. Each time the counter decrements to 0, a timer interrupt is generated. The timer can be stopped, restarted, reset, or disabled by specific status bits.

3.10 Clock Generator

The clock generator provides clocks to the 5416 device, and consists of a phase-locked loop (PLL) circuit. The clock generator requires a reference clock input, which can be provided from an external clock source. The reference clock input is then divided by two (DIV mode) to generate clocks for the 5416 device, or the PLL circuit can be used (PLL mode) to generate the device clock by multiplying the reference clock frequency by a scale factor, allowing use of a clock source with a lower frequency than that of the CPU. The PLL is an adaptive circuit that, once synchronized, locks onto and tracks an input clock signal.

When the PLL is initially started, it enters a transitional mode during which the PLL acquires lock with the input signal. Once the PLL is locked, it continues to track and maintain synchronization with the input signal. Then, other internal clock circuitry allows the synthesis of new clock frequencies for use as master clock for the 5416 device.

This clock generator allows system designers to select the clock source. The sources that drive the clock generator are:

- A crystal resonator circuit. The crystal resonator circuit is connected across the X1 and X2/CLKIN pins of the 5416 to enable the internal oscillator.
- An external clock. The external clock source is directly connected to the X2/CLKIN pin, and X1 is left unconnected.

NOTE: The crystal oscillator function is not supported by all die revisions of the 5416 device. See the TMS320VC5416 Silicon Errata (literature number SPRZ172) to verify which die revisions support this functionality.

The software-programmable PLL features a high level of flexibility, and includes a clock scaler that provides various clock multiplier ratios, capability to directly enable and disable the PLL, and a PLL lock timer that can be used to delay switching to PLL clocking mode of the device until lock is achieved. Devices that have a built-in software-programmable PLL can be configured in one of two clock modes:

- PLL mode. The input clock (X2/CLKIN) is multiplied by 1 of 31 possible ratios.
- DIV (divider) mode. The input clock is divided by 2 or 4. Note that when DIV mode is used, the PLL can be completely disabled in order to minimize power dissipation.

The software-programmable PLL is controlled using the 16-bit memory-mapped (address 0058h) clock mode register (CLKMD). The CLKMD register is used to define the clock configuration of the PLL clock module. Note that upon reset, the CLKMD register is initialized with a predetermined value dependent only upon the state of the CLKMD1 – CLKMD3 pins. For more programming information, see the *TMS320C54x DSP Reference Set, Volume 1: CPU and Peripherals* (literature number SPRU131). The CLKMD pin configured clock options are shown in Table 3–8.

| CLKMD1 | CLKMD2 | CLKMD3 | CLKMD RESET VALUE | |
|--------|--------|--------|----------------------|------------------------|
| 0 | 0 | 0 | 0000h | 1/2 (PLL disabled) |
| 0 | 0 | 1 | 9007h | PLL x 10 |
| 0 | 1 | 0 | 4007h | PLL x 5 |
| 1 | 0 | 0 | 1007h | PLL x 2 |
| 1 | 1 | 0 | F007h | PLL x 1 |
| 1 | 1 | 1 | 0000h | 1/2 (PLL disabled) |
| 1 | 0 | 1 | F000h | 1/4 (PLL disabled) |
| 0 | 1 | 1 | — | Reserved (Bypass mode) |

| Table 3-8. | Clock Mode Settings at Reset |
|------------|------------------------------|
| | eleen mede eettinge at neeet |

[†] The external CLKMD1-CLKMD3 pins are sampled to determine the desired clock generation mode while RS is low. Following reset, the clock generation mode can be reconfigured by writing to the internal clock mode register in software.

3.11 Enhanced External Parallel Interface (XIO2)

The 5416 external interface has been redesigned to include several improvements, including: simplification of the bus sequence, more immunity to bus contention when transitioning between read and write operations, the ability for external memory access to the DMA controller, and optimization of the power-down modes.

The bus sequence on the 5416 still maintains all of the same interface signals as on previous 54x devices, but the signal sequence has been simplified. Most external accesses now require 3 cycles composed of a leading cycle, an active (read or write) cycle, and a trailing cycle. The leading and trailing cycles provide additional immunity against bus contention when switching between read operations and write operations. To maintain high-speed read access, a consecutive read mode that performs single-cycle reads as on previous 54x devices is available.

Figure 3-12 shows the bus sequence for three cases: all I/O reads, memory reads in nonconsecutive mode, or single memory reads in consecutive mode. The accesses shown in Figure 3-12 always require 3 CLKOUT cycles to complete.




Figure 3-12. Nonconsecutive Memory Read and I/O Read Bus Sequence




Figure 3-13 shows the bus sequence for repeated memory reads in consecutive mode. The accesses shown in Figure 3-13 require (2 + n) CLKOUT cycles to complete, where n is the number of consecutive reads performed.

Figure 3-13. Consecutive Memory Read Bus Sequence (n = 3 reads)

Figure 3-14 shows the bus sequence for all memory writes and I/O writes. The accesses shown in Figure 3-14 always require 3 CLKOUT cycles to complete.




Figure 3-14. Memory Write and I/O Write Bus Sequence

The enhanced interface also provides the ability for DMA transfers to extend to external memory. For more information on DMA capability, see the DMA sections that follow.

The enhanced interface improves the low-power performance already present on the TMS320C5000[™] DSP platform by switching off the internal clocks to the interface when it is not being used. This power-saving feature is automatic, requires no software setup, and causes no latency in the operation of the interface.

Additional features integrated in the enhanced interface are the ability to automatically insert bank-switching cycles when crossing 32K memory boundaries (see Section 3.6.2), the ability to program up to 14 wait states through software (see Section 3.6.1), and the ability to divide down CLKOUT by a factor of 1, 2, 3, or 4. Dividing down CLKOUT provides an alternative to wait states when interfacing to slower external memory or peripheral devices. While inserting wait states extends the bus sequence during read or write accesses, it does not slow down the bus signal sequences at the beginning and the end of the access. Dividing down CLKOUT provides a method of slowing the entire bus sequence when necessary. The CLKOUT divide-down factor is controlled through the DIVFCT field in the bank-switching control register (BSCR) (see Table 3-5).

3.12 DMA Controller

The 5416 direct memory access (DMA) controller transfers data between points in the memory map without intervention by the CPU. The DMA allows movements of data to and from internal program/data memory, internal peripherals (such as the McBSPs), or external memory devices to occur in the background of CPU operation. The DMA has six independent programmable channels, allowing six different contexts for DMA operation.

TMS320C5000 is a trademark of Texas Instruments.

3.12.1 Features

The DMA has the following features:

- The DMA operates independently of the CPU.
- The DMA has six channels. The DMA can keep track of the contexts of six independent block transfers.
- The DMA has higher priority than the CPU for both internal and external accesses.
- Each channel has independently programmable priorities.
- Each channel's source and destination address registers can have configurable indexes through memory on each read and write transfer, respectively. The address may remain constant, be post-incremented, be post-decremented, or be adjusted by a programmable value.
- Each read or write internal transfer may be initialized by selected events.
- On completion of a half- or entire-block transfer, each DMA channel may send an interrupt to the CPU.
- The DMA can perform double-word internal transfers (a 32-bit transfer of two 16-bit words).

3.12.2 DMA External Access

The 5416 DMA supports external accesses to data, I/O, and extended program memory. These overlay pages are only visible to the DMA controller. A maximum of two DMA channels can be used for external memory accesses. The DMA external accesses require a minimum of 8 cycles for external writes and a minimum of 11 cycles for external reads assuming the XIO02 is in consecutive mode ($\overline{CONSEC} = 1$), wait state is set to two, and CLKOUT is not divided (DIVFCT = 00).

The control of the bus is arbitrated between the CPU and the DMA. While the DMA or CPU is in control of the external bus, the other will be held-off via wait states until the current transfer is complete. The DMA takes precedence over XIO requests.

- Only two channels are available for external accesses. (One for external reads and one for external writes.)
- Single-word (16-bit) transfers are supported for external accesses.
- The DMA does not support transfers from the peripherals to external memory.
- The DMA does not support transfers from external memory to the peripherals.
- The DMA does not support external-to-external accesses.
- The DMA does not support synchronized external accesses.

| 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|--------------|------|------|-----------|-------|----|------|---|----|----|-------|---|------|---|----|----|
| AUTO INIT | DINM | IMOD | CT MOD | SLAXS | | SIND | | DI | NS | DLAXS | | DIND | | DI | MD |

These new bit fields were created to allow the user to define the space-select for the DMA (internal/external). The functions of the DLAXS and SLAXS bits are as follows:

| DLAXS(DMMCRn[5]) Destination | 0 = No external access (default internal) |
|------------------------------|---|
| | 1 = External access |
| SLAXS(DMMCRn[11]) Source | 0 = No external access (default internal) |
| | 1 = External access |
| | |

Table 3-9 lists the DMD bit values and their corresponding destination space.


| | er the Billiorin Hegioter |
|-----|---------------------------|
| DMD | DESTINATION SPACE |
| 00 | PS |
| 01 | DS |
| 10 | I/O |
| 11 | Reserved |

Table 3-9. DMD Section of the DMMCRn Register

For the CPU external access, software can configure the memory cells to reside inside or outside the program address map. When the cells are mapped into program space, the device automatically accesses them when their addresses are within bounds. When the address generation logic generates an address outside its bounds, the device automatically generates an external access.

3.12.3 DMA Memory Map

The DMA memory map, shown in Figure 3–16, allows the DMA transfer to be unaffected by the status of the MP/MC, DROM, and OVLY bits.





Functional Overview




Figure 3-17. On-Chip DMA Memory Map for Data and IO Space (DLAXS = 0 and SLAXS = 0)

3.12.4 DMA Priority Level

Each DMA channel can be independently assigned high- or low-priority relative to each other. Multiple DMA channels that are assigned to the same priority level are handled in a round-robin manner.

3.12.5 DMA Source/Destination Address Modification

The DMA provides flexible address-indexing modes for easy implementation of data management schemes such as autobuffering and circular buffers. Source and destination addresses can be indexed separately and can be post-incremented, post-decremented, or post-incremented with a specified index offset.

3.12.6 DMA in Autoinitialization Mode

The DMA can automatically reinitialize itself after completion of a block transfer. Some of the DMA registers can be preloaded for the next block transfer through the DMA reload registers (DMGSA, DMGDA, DMGCR, and DMGFR). Autoinitialization allows:

- Continuous operation: Normally, the CPU would have to reinitialize the DMA immediately after the completion of the current block transfers, but with the reload registers, it can reinitialize these values for the next block transfer any time after the current block transfer begins.
- Repetitive operation: The CPU does not preload the reload register with new values for each block transfer but only loads them on the first block transfer.

The 5416 DMA has been enhanced to expand the DMA reload register sets. Each DMA channel now has its own DMA reload register set. For example, the DMA reload register set for channel 0 has DMGSA0, DMGDA0, DMGCR0, and DMGFR0 while DMA channel 1 has DMGSA1, DMGDA1, DMGCR1, and DMGFR1, etc.

To utilize the additional DMA reload registers, the AUTOIX bit is added to the DMPREC register as shown in Figure 3-18.

| 15 | 14 | 13 | 8 | 7 | 6 | 5 | | 0 |
|------|--------|---------|----|----|------|---|---------|---|
| FREE | AUTOIX | DPRC[5: |)] | IC | DSEL | | DE[5:0] | |

Figure 3-18. DMPREC Register

| Table 3-10. | DMA Reload | Register Selection |
|-------------|------------|--------------------|
|-------------|------------|--------------------|

| Αυτοιχ | DMA RELOAD REGISTER USAGE IN AUTO INIT MODE |
|-------------|--|
| 0 (default) | All DMA channels use DMGSA0, DMGDA0, DMGCR0 and DMGFR0 |
| 1 | Each DMA channel uses its own set of reload registers |

3.12.7 DMA Transfer Counting

The DMA channel element count register (DMCTRx) and the frame count register (DMFRCx) contain bit fields that represent the number of frames and the number of elements per frame to be transferred.

- Frame count. This 8-bit value defines the total number of frames in the block transfer. The maximum number of frames per block transfer is 128 (FRAME COUNT= 0FFh). The counter is decremented upon the last read transfer in a frame transfer. Once the last frame is transferred, the selected 8-bit counter is reloaded with the DMA global frame reload register (DMGFR) if the AUTOINIT bit is set to 1. A frame count of 0 (default value) means the block transfer contains a single frame.
- Element count. This 16-bit value defines the number of elements per frame. This counter is decremented after the read transfer of each element. The maximum number of elements per frame is 65536 (DMCTRn = 0FFFFh). In autoinitialization mode, once the last frame is transferred, the counter is reloaded with the DMA global count reload register (DMGCR).

3.12.8 DMA Transfer in Doubleword Mode

Doubleword mode allows the DMA to transfer 32-bit words in any index mode. In doubleword mode, two consecutive 16-bit transfers are initiated and the source and destination addresses are automatically updated following each transfer. In this mode, each 32-bit word is considered to be one element.

3.12.9 DMA Channel Index Registers

The particular DMA channel index register is selected by way of the SIND and DIND fields in the DMA transfer mode control register (DMMCRn). Unlike basic address adjustment, in conjunction with the frame index DMFRI0 and DMFRI1, the DMA allows different adjustment amounts depending on whether or not the element transfer is the last in the current frame. The normal adjustment value (element index) is contained in the element index registers DMIDX0 and DMIDX1. The adjustment value (frame index) for the end of the frame, is determined by the selected DMA frame index register, either DMFRI0 or DMFRI1.

The element index and the frame index affect address adjustment as follows:

- Element index: For all except the last transfer in the frame, the element index determines the amount to be added to the DMA channel for the source/destination address register (DMSRCx/DMDSTx) as selected by the SIND/DIND bits.
- Frame index: If the transfer is the last in a frame, frame index is used for address adjustment as selected by the SIND/DIND bits. This occurs in both single-frame and multiframe transfers.

3.12.10 DMA Interrupts

The ability of the DMA to interrupt the CPU based on the status of the data transfer is configurable and is determined by the IMOD and DINM bits in the DMA transfer mode control register (DMMCRn). The available modes are shown in Table 3–11.

| MODE | DINM | IMOD | INTERRUPT | | |
|---|-----------------|---------------------|--|--|--|
| ABU (non-decrement) 1 0 At full buffer only | | At full buffer only | | | |
| ABU (non-decrement) | -decrement) 1 1 | | At half buffer and full buffer | | |
| Multiframe 1 0 | | 0 | At block transfer complete (DMCTRn = DMSEFCn[7:0] = 0) | | |
| Multiframe | 1 | 1 | At end of frame and end of block (DMCTRn = 0) | | |
| Either | 0 | Х | No interrupt generated | | |
| Either | 0 | Х | No interrupt generated | | |

3.12.11 DMA Controller Synchronization Events

The transfers associated with each DMA channel can be synchronized to one of several events. The DSYN bit field of the DMSEFCn register selects the synchronization event for a channel. The list of possible events and the DSYN values are shown in Table 3–12.

| DSYN VALUE | DMA SYNCHRONIZATION EVENT |
|------------|-----------------------------------|
| 0000b | No synchronization used |
| 0001b | McBSP0 receive event |
| 0010b | McBSP0 transmit event |
| 0011b | McBSP2 receive event |
| 0100b | McBSP2 transmit event |
| 0101b | McBSP1 receive event |
| 0110b | McBSP1 transmit event |
| 0111b | McBSP0 receive event - ABIS mode |
| 1000b | McBSP0 transmit event - ABIS mode |
| 1001b | McBSP2 receive event - ABIS mode |
| 1010b | McBSP2 transmit event - ABIS mode |
| 1011b | McBSP1 receive event - ABIS mode |
| 1100b | McBSP1 transmit event - ABIS mode |
| 1101b | Timer interrupt event |
| 1110b | INT3 goes active |
| 1111b | Reserved |

 Table 3-12. DMA Synchronization Events

The DMA controller can generate a CPU interrupt for each of the six channels. However, due to a limit on the number of internal CPU interrupt inputs, channels 0, 1, 2, and 3 are multiplexed with other interrupt sources. DMA channels 0, 1, 2, and 3 share an interrupt line with the receive and transmit portions of the McBSP. When the 5416 is reset, the interrupts from these three DMA channels are deselected. The INTSEL bit field in the DMPREC register can be used to select these interrupts, as shown in Table 3–13.

| INTSEL Value | IMR/IFR[6] IMR/IFR[7] | | IMR/IFR[10] | IMR/IFR[11] | | | |
|--------------|-----------------------|--------|-------------|-----------------|--|--|--|
| 00b (reset) | BRINT2 | BXINT2 | BRINT1 | BXINT1 DMAC3 | | | |
| 01b | BRINT2 | BXINT2 | DMAC2 | | | | |
| 10b | 10b DMAC0 | | DMAC2 | DMAC3 | | | |
| 11b | Reserved | | | | | | |

Table 3-13. DMA Channel Interrupt Selection

3.13 General-Purpose I/O Pins

In addition to the standard $\overline{\text{BIO}}$ and XF pins, the 5416 has pins that can be configured for general-purpose I/O. These pins are:

- 18 McBSP pins BCLKX0/1/2, BCLKR0/1/2, BDR0/1/2, BFSX0/1/2, BFSR0/1/2, BDX0/1/2
- 8 HPI data pins—HD0-HD7

The general-purpose I/O function of these pins is only available when the primary pin function is not required.

3.13.1 McBSP Pins as General-Purpose I/O

When the receive or transmit portion of a McBSP is in reset, its pins can be configured as general-purpose inputs or outputs. For more details on this feature, see Section 3.8.

3.13.2 HPI Data Pins as General-Purpose I/O

The 8-bit bidirectional data bus of the HPI can be used as general-purpose input/output (GPIO) pins when the HPI is disabled (HPIENA = 0) or when the HPI is used in HPI16 mode (HPI16 = 1). Two memory-mapped registers are used to control the GPIO function of the HPI data pins—the general-purpose I/O control register (GPIOCR) and the general-purpose I/O status register (GPIOSR). The GPIOCR is shown in Figure 3-19.

| 15 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|----------|-------|-------|-------|-------|-------|-------|-------|-------|
| Reserved | DIR7 | DIR6 | DIR5 | DIR4 | DIR3 | DIR2 | DIR1 | DIR0 |
| 0 | R/W-0 |

Figure 3-19. General-Purpose I/O Control Register (GPIOCR) [MMR Address 003Ch]

The direction bits (DIRx) are used to configure HD0-HD7 as inputs or outputs.

The status of the GPIO pins can be monitored using the bits of the GPIOSR. The GPIOSR is shown in Figure 3-20.

| 15 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------|------|-------|-------|-------|-------|-------|-------|-------|-------|
| Rese | rved | 107 | IO6 | 105 | 104 | 103 | 102 | IO1 | 100 |
| - | 0 | R/W-0 |

Figure 3-20. General-Purpose I/O Status Register (GPIOSR) [MMR Address 003Dh]

3.14 Device ID Register

A read-only memory-mapped register has been added to the 5416 to allow user application software to identify on which device the program is being executed.

| 15-8 | 7 | | 4 | 3 | | 0 |
|---------|---|---------------|---|---|----------|----------|
| Chip ID | | Chip Revision | | | SUBSYSID | |
| R | | R | | | R | <u> </u> |

Bits 15:8: Chip_ID (hex code of 16)

Bits 7:4: Chip_Revision ID

Bits 3:0: Subsystem_ID (0000b for single core device)

Figure 3-21. Device ID Register (CSIDR) [MMR Address 003Eh]

3.15 Memory-Mapped Registers

The 5416 has 27 memory-mapped CPU registers, which are mapped in data memory space address 0h to 1Fh. Each 5416 device also has a set of memory-mapped registers associated with peripherals. Table 3–14 gives a list of CPU memory-mapped registers (MMRs) available on 5416. Table 3–15 shows additional peripheral MMRs associated with the 5416.

| | ADD | RESS | | | | | |
|------|-----|------|----------------------------------|--|--|--|--|
| NAME | DEC | HEX | DESCRIPTION | | | | |
| IMR | 0 | 0 | Interrupt mask register | | | | |
| IFR | 1 | 1 | Interrupt flag register | | | | |
| — | 2-5 | 2-5 | Reserved for testing | | | | |
| ST0 | 6 | 6 | Status register 0 | | | | |
| ST1 | 7 | 7 | Status register 1 | | | | |
| AL | 8 | 8 | Accumulator A low word (15-0) | | | | |
| AH | 9 | 9 | Accumulator A high word (31-16) | | | | |
| AG | 10 | А | Accumulator A guard bits (39-32) | | | | |
| BL | 11 | В | Accumulator B low word (15-0) | | | | |
| BH | 12 | С | Accumulator B high word (31-16) | | | | |
| BG | 13 | D | Accumulator B guard bits (39-32) | | | | |
| TREG | 14 | E | Temporary register | | | | |
| TRN | 15 | F | Transition register | | | | |
| AR0 | 16 | 10 | Auxiliary register 0 | | | | |
| AR1 | 17 | 11 | Auxiliary register 1 | | | | |
| AR2 | 18 | 12 | Auxiliary register 2 | | | | |
| AR3 | 19 | 13 | Auxiliary register 3 | | | | |
| AR4 | 20 | 14 | Auxiliary register 4 | | | | |
| AR5 | 21 | 15 | Auxiliary register 5 | | | | |
| AR6 | 22 | 16 | Auxiliary register 6 | | | | |
| AR7 | 23 | 17 | Auxiliary register 7 | | | | |
| SP | 24 | 18 | Stack pointer register | | | | |
| BK | 25 | 19 | Circular buffer size register | | | | |
| BRC | 26 | 1A | Block repeat counter | | | | |
| RSA | 27 | 1B | Block repeat start address | | | | |

| NAME | ADDI | RESS | DECODIDENCI | | |
|------|------|------|---------------------------------------|--|--|
| | DEC | HEX | DESCRIPTION | | |
| REA | 28 | 1C | Block repeat end address | | |
| PMST | 29 | 1D | Processor mode status (PMST) register | | |
| XPC | 30 | 1E | Extended program page register | | |
| — | 31 | 1F | Reserved | | |

Table 3-14. CPU Memory-Mapped Registers (Continued)

| NAME | ADDRESS DEC HEX | | DESCRIPTION |
|--------|--------------------|-------|---|
| DRR20 | 32 | 20 | McBSP 0 Data Receive Register 2 |
| DRR10 | 33 | 21 | McBSP 0 Data Receive Register 1 |
| DXR20 | 34 | 22 | McBSP 0 Data Transmit Register 2 |
| DXR10 | 35 | 23 | McBSP 0 Data Transmit Register 1 |
| ТІМ | 36 | 24 | Timer Register |
| PRD | 37 | 25 | Timer Period Register |
| TCR | 38 | 26 | Timer Control Register |
| _ | 39 | 27 | Reserved |
| SWWSR | 40 | 28 | Software Wait-State Register |
| BSCR | 41 | 29 | Bank-Switching Control Register |
| _ | 42 | 2A | Reserved |
| SWCR | 43 | 2B | Software Wait-State Control Register |
| HPIC | 44 | 2C | HPI Control Register (HMODE = 0 only) |
| | 45-47 | 2D-2F | Reserved |
| DRR22 | 48 | 30 | McBSP 2 Data Receive Register 2 |
| DRR12 | 49 | 31 | McBSP 2 Data Receive Register 1 |
| DXR22 | 50 | 32 | McBSP 2 Data Transmit Register 2 |
| DXR12 | 51 | 33 | McBSP 2 Data Transmit Register 1 |
| SPSA2 | 52 | 34 | McBSP 2 Subbank Address Register [†] |
| SPSD2 | 53 | 35 | McBSP 2 Subbank Data Register [†] |
| | 54-55 | 36-37 | Reserved |
| SPSA0 | 56 | 38 | McBSP 0 Subbank Address Register [†] |
| SPSD0 | 57 | 39 | McBSP 0 Subbank Data Register [†] |
| | 58-59 | 3A-3B | Reserved |
| GPIOCR | 60 | ЗC | General-Purpose I/O Control Register |
| GPIOSR | 61 | 3D | General-Purpose I/O Status Register |
| CSIDR | 62 | 3E | Device ID Register |
| | 63 | ЗF | Reserved |
| DRR21 | 64 | 40 | McBSP 1 Data Receive Register 2 |
| DRR11 | 65 | 41 | McBSP 1 Data Receive Register 1 |
| DXR21 | 66 | 42 | McBSP 1 Data Transmit Register 2 |
| DXR11 | 67 | 43 | McBSP 1 Data Transmit Register 1 |
| | 68-71 | 44-47 | Reserved |
| SPSA1 | 72 | 48 | McBSP 1 Subbank Address Register [†] |
| SPSD1 | 73 | 49 | McBSP 1 Subbank Data Register [†] |
| — | 74-83 | 4A-53 | Reserved |
| DMPREC | 84 | 54 | DMA Priority and Enable Control Register |
| DMSA | 85 | 55 | DMA Subbank Address Register [‡] |
| DMSDI | 86 | 56 | DMA Subbank Data Register with Autoincrement [‡] |
| DMSDN | 87 | 57 | DMA Subbank Data Register [‡] |
| CLKMD | 88 | 58 | Clock Mode Register (CLKMD) |
| — | 89-95 | 59-5F | Reserved |

Table 3-15. Peripheral Memory-Mapped Registers for Each DSP Subsystem

[†] See Table 3-16 for a detailed description of the McBSP control registers and their subaddresses.

[‡] See Table 3-17 for a detailed description of the DMA subbank addressed registers.

3.16 McBSP Control Registers and Subaddresses

The control registers for the multichannel buffered serial port (McBSP) are accessed using the subbank addressing scheme. This allows a set or subbank of registers to be accessed through a single memory location. The McBSP subbank address register (SPSA) is used as a pointer to select a particular register within the subbank. The McBSP data register (SPSDx) is used to access (read or write) the selected register. Table 3-16 shows the McBSP control registers and their corresponding subaddresses.

| McBSP0 | | | BSP1 | | 3SP2 | SUB- | | | |
|--------|---------|--------|---------|--------|---------|---------|---|--|--|
| NAME | ADDRESS | NAME | ADDRESS | NAME | ADDRESS | ADDRESS | DESCRIPTION | | |
| SPCR10 | 39h | SPCR11 | 49h | SPCR12 | 35h | 00h | Serial port control register 1 | | |
| SPCR20 | 39h | SPCR21 | 49h | SPCR22 | 35h | 01h | Serial port control register 2 | | |
| RCR10 | 39h | RCR11 | 49h | RCR12 | 35h | 02h | Receive control register 1 | | |
| RCR20 | 39h | RCR21 | 49h | RCR22 | 35h | 03h | Receive control register 2 | | |
| XCR10 | 39h | XCR11 | 49h | XCR12 | 35h | 04h | Transmit control register 1 | | |
| XCR20 | 39h | XCR21 | 49h | XCR22 | 35h | 05h | Transmit control register 2 | | |
| SRGR10 | 39h | SRGR11 | 49h | SRGR12 | 35h | 06h | Sample rate generator register 1 | | |
| SRGR20 | 39h | SRGR21 | 49h | SRGR22 | 35h | 07h | Sample rate generator register 2 | | |
| MCR10 | 39h | MCR11 | 49h | MCR12 | 35h | 08h | Multichannel register 1 | | |
| MCR20 | 39h | MCR21 | 49h | MCR22 | 35h | 09h | Multichannel register 2 | | |
| RCERA0 | 39h | RCERA1 | 49h | RCERA2 | 35h | 0Ah | Receive channel enable register partition A | | |
| RCERB0 | 39h | RCERB1 | 49h | RCERA2 | 35h | 0Bh | Receive channel enable register partition B | | |
| XCERA0 | 39h | XCERA1 | 49h | XCERA2 | 35h | 0Ch | Transmit channel enable register partition A | | |
| XCERB0 | 39h | XCERB1 | 49h | XCERA2 | 35h | 0Dh | Transmit channel enable register partition B | | |
| PCR0 | 39h | PCR1 | 49h | PCR2 | 35h | 0Eh | Pin control register | | |
| RCERC0 | 39h | RCERC1 | 49h | RCERC2 | 35h | 010h | Additional channel enable register for 128-channel selection | | |
| RCERD0 | 39h | RCERD1 | 49h | RCERD2 | 35h | 011h | Additional channel enable register for 128-channel selection | | |
| XCERC0 | 39h | XCERC1 | 49h | XCERC2 | 35h | 012h | Additional channel enable register for 128-channel selection | | |
| XCERD0 | 39h | XCERD1 | 49h | XCERD2 | 35h | 013h | Additional channel enable register for 128-channel selection | | |
| RCERE0 | 39h | RCERE1 | 49h | RCERE2 | 35h | 014h | Additional channel enable register for 128-channel selection | | |
| RCERF0 | 39h | RCERF1 | 49h | RCERF2 | 35h | 015h | Additional channel enable register for 128-channel selection | | |
| XCERE0 | 39h | XCERE1 | 49h | XCERE2 | 35h | 016h | Additional channel enable register for 128-channel selection | | |
| XCERF0 | 39h | XCERF1 | 49h | XCERF2 | 35h | 017h | Additional channel enable register for 128-channel selection | | |
| RCERG0 | 39h | RCERG1 | 49h | RCERG2 | 35h | 018h | Additional channel enable register for 128-channel selection | | |
| RCERH0 | 39h | RCERH1 | 49h | RCERH2 | 35h | 019h | Additional channel enable register for 128-channel selection | | |
| XCERG0 | 39h | XCERG1 | 49h | XCERG2 | 35h | 01Ah | Additional channel enable register for 128-channel selection | | |
| XCERH0 | 39h | XCERH1 | 49h | XCERH2 | 35h | 01Bh | Additional channel enable register for 128-channel selection | | |

Table 3-16. McBSP Control Registers and Subaddresses

3.17 DMA Subbank Addressed Registers

The direct memory access (DMA) controller has several control registers associated with it. The main control register (DMPREC) is a standard memory-mapped register. However, the other registers are accessed using the subbank addressing scheme. This allows a set or subbank of registers to be accessed through a single memory location. The DMA subbank address (DMSA) register is used as a pointer to select a particular register within the subbank, while the DMA subbank data (DMSD) register or the DMA subbank data register with autoincrement (DMSDI) is used to access (read or write) the selected register.

When the DMSDI register is used to access the subbank, the subbank address is automatically postincremented so that a subsequent access affects the next register within the subbank. This autoincrement feature is intended for efficient, successive accesses to several control registers. If the autoincrement feature is not required, the DMSDN register should be used to access the subbank. Table 3–17 shows the DMA controller subbank addressed registers and their corresponding subaddresses.

| NAME | ADDRESS | SUB- ADDRESS | DESCRIPTION |
|--------|---------|-----------------|--|
| DMSRC0 | 56h/57h | 00h | DMA channel 0 source address register |
| DMDST0 | 56h/57h | 01h | DMA channel 0 destination address register |
| DMCTR0 | 56h/57h | 02h | DMA channel 0 element count register |
| DMSFC0 | 56h/57h | 03h | DMA channel 0 sync select and frame count register |
| DMMCR0 | 56h/57h | 04h | DMA channel 0 transfer mode control register |
| DMSRC1 | 56h/57h | 05h | DMA channel 1 source address register |
| DMDST1 | 56h/57h | 06h | DMA channel 1 destination address register |
| DMCTR1 | 56h/57h | 07h | DMA channel 1 element count register |
| DMSFC1 | 56h/57h | 08h | DMA channel 1 sync select and frame count register |
| DMMCR1 | 56h/57h | 09h | DMA channel 1 transfer mode control register |
| DMSRC2 | 56h/57h | 0Ah | DMA channel 2 source address register |
| DMDST2 | 56h/57h | 0Bh | DMA channel 2 destination address register |
| DMCTR2 | 56h/57h | 0Ch | DMA channel 2 element count register |
| DMSFC2 | 56h/57h | 0Dh | DMA channel 2 sync select and frame count register |
| DMMCR2 | 56h/57h | 0Eh | DMA channel 2 transfer mode control register |
| DMSRC3 | 56h/57h | 0Fh | DMA channel 3 source address register |
| DMDST3 | 56h/57h | 10h | DMA channel 3 destination address register |
| DMCTR3 | 56h/57h | 11h | DMA channel 3 element count register |
| DMSFC3 | 56h/57h | 12h | DMA channel 3 sync select and frame count register |
| DMMCR3 | 56h/57h | 13h | DMA channel 3 transfer mode control register |
| DMSRC4 | 56h/57h | 14h | DMA channel 4 source address register |
| DMDST4 | 56h/57h | 15h | DMA channel 4 destination address register |
| DMCTR4 | 56h/57h | 16h | DMA channel 4 element count register |
| DMSFC4 | 56h/57h | 17h | DMA channel 4 sync select and frame count register |
| DMMCR4 | 56h/57h | 18h | DMA channel 4 transfer mode control register |
| DMSRC5 | 56h/57h | 19h | DMA channel 5 source address register |
| DMDST5 | 56h/57h | 1Ah | DMA channel 5 destination address register |
| DMCTR5 | 56h/57h | 1Bh | DMA channel 5 element count register |
| DMSFC5 | 56h/57h | 1Ch | DMA channel 5 sync select and frame count register |
| DMMCR5 | 56h/57h | 1Dh | DMA channel 5 transfer mode control register |
| DMSRCP | 56h/57h | 1Eh | DMA source program page address (common channel) |

Table 3-17. DMA Subbank Addressed Registers

| NAME | ADDRESS | SUB- ADDRESS | DESCRIPTION |
|--------|---------|-----------------|--|
| DMDSTP | 56h/57h | 1Fh | DMA destination program page address (common channel) |
| DMIDX0 | 56h/57h | 20h | DMA element index address register 0 |
| DMIDX1 | 56h/57h | 21h | DMA element index address register 1 |
| DMFRI0 | 56h/57h | 22h | DMA frame index register 0 |
| DMFRI1 | 56h/57h | 23h | DMA frame index register 1 |
| DMGSA0 | 56h/57h | 24h | DMA global source address reload register, channel 0 |
| DMGDA0 | 56h/57h | 25h | DMA global destination address reload register, channel 0 |
| DMGCR0 | 56h/57h | 26h | DMA global count reload register, channel 0 |
| DMGFR0 | 56h/57h | 27h | DMA global frame count reload register, channel 0 |
| XSRCDP | 56h/57h | 28h | DMA extended source data page (currently not supported) |
| XDSTDP | 56h/57h | 29h | DMA extended destination data page (currently not supported) |
| DMGSA1 | 56h/57h | 2Ah | DMA global source address reload register, channel 1 |
| DMGDA1 | 56h/57h | 2Bh | DMA global destination address reload register, channel 1 |
| DMGCR1 | 56h/57h | 2Ch | DMA global count reload register, channel 1 |
| DMGFR1 | 56h/57h | 2Dh | DMA global frame count reload register, channel 1 |
| DMGSA2 | 56h/57h | 2Eh | DMA global source address reload register, channel 2 |
| DMGDA2 | 56h/57h | 2Fh | DMA global destination address reload register, channel 2 |
| DMGCR2 | 56h/57h | 30h | DMA global count reload register, channel 2 |
| DMGFR2 | 56h/57h | 31h | DMA global frame count reload register, channel 2 |
| DMGSA3 | 56h/57h | 32h | DMA global source address reload register, channel 3 |
| DMGDA3 | 56h/57h | 33h | DMA global destination address reload register, channel 3 |
| DMGCR3 | 56h/57h | 34h | DMA global count reload register, channel 3 |
| DMGFR3 | 56h/57h | 35h | DMA global frame count reload register, channel 3 |
| DMGSA4 | 56h/57h | 36h | DMA global source address reload register, channel 4 |
| DMGDA4 | 56h/57h | 37h | DMA global destination address reload register, channel 4 |
| DMGCR4 | 56h/57h | 38h | DMA global count reload register, channel 4 |
| DMGFR4 | 56h/57h | 39h | DMA global frame count reload register, channel 4 |
| DMGSA5 | 56h/57h | 3Ah | DMA global source address reload register, channel 5 |
| DMGDA5 | 56h/57h | 3Bh | DMA global destination address reload register, channel 5 |
| DMGCR5 | 56h/57h | 3Ch | DMA global count reload register, channel 5 |
| DMGFR5 | 56h/57h | 3Dh | DMA global frame count reload register, channel 5 |

Table 3-17. DMA Subbank Addressed Registers (Continued)

3.18 Interrupts

Vector-relative locations and priorities for all internal and external interrupts are shown in Table 3-18.

| NAME | DECIMAL | HEX | PRIORITY | FUNCTION | | | | | |
|---------------|---------|-------|----------|---------------------------------------|--|--|--|--|--|
| RS, SINTR | 0 | 00 | 1 | Reset (hardware and software reset) | | | | | |
| NMI, SINT16 | 4 | 04 | 2 | Nonmaskable interrupt | | | | | |
| SINT17 | 8 | 08 | — | Software interrupt #17 | | | | | |
| SINT18 | 12 | 0C | — | Software interrupt #18 | | | | | |
| SINT19 | 16 | 10 | — | Software interrupt #19 | | | | | |
| SINT20 | 20 | 14 | — | Software interrupt #20 | | | | | |
| SINT21 | 24 | 18 | — | Software interrupt #21 | | | | | |
| SINT22 | 28 | 1C | — | Software interrupt #22 | | | | | |
| SINT23 | 32 | 20 | — | Software interrupt #23 | | | | | |
| SINT24 | 36 | 24 | — | Software interrupt #24 | | | | | |
| SINT25 | 40 | 28 | — | Software interrupt #25 | | | | | |
| SINT26 | 44 | 2C | — | Software interrupt #26 | | | | | |
| SINT27 | 48 | 30 | — | Software interrupt #27 | | | | | |
| SINT28 | 52 | 34 | — | Software interrupt #28 | | | | | |
| SINT29 | 56 | 38 | _ | Software interrupt #29 | | | | | |
| SINT30 | 60 | зC | — | Software interrupt #30 | | | | | |
| INTO, SINTO | 64 | 40 | 3 | External user interrupt #0 | | | | | |
| INT1, SINT1 | 68 | 44 | 4 | External user interrupt #1 | | | | | |
| INT2, SINT2 | 72 | 48 | 5 | External user interrupt #2 | | | | | |
| TINT, SINT3 | 76 | 4C | 6 | Timer interrupt | | | | | |
| RINT0, SINT4 | 80 | 50 | 7 | McBSP #0 receive interrupt (default) | | | | | |
| XINT0, SINT5 | 84 | 54 | 8 | McBSP #0 transmit interrupt (default) | | | | | |
| RINT2, SINT6 | 88 | 58 | 9 | McBSP #2 receive interrupt (default) | | | | | |
| XINT2, SINT7 | 92 | 5C | 10 | McBSP #2 transmit interrupt (default) | | | | | |
| INT3, SINT8 | 96 | 60 | 11 | External user interrupt #3 | | | | | |
| HINT, SINT9 | 100 | 64 | 12 | HPI interrupt | | | | | |
| RINT1, SINT10 | 104 | 68 | 13 | McBSP #1 receive interrupt (default) | | | | | |
| XINT1, SINT11 | 108 | 6C | 14 | McBSP #1 transmit interrupt (default) | | | | | |
| DMAC4,SINT12 | 112 | 70 | 15 | DMA channel 4 (default) | | | | | |
| DMAC5,SINT13 | 116 | 74 | 16 | DMA channel 5 (default) | | | | | |
| Reserved | 120-127 | 78-7F | | Reserved | | | | | |

 Table 3-18. Interrupt Locations and Priorities

The bit layout of the interrupt flag register (IFR) and the interrupt mask register (IMR) is shown in Figure 3-22.

| 15-14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|-------|-------|-------|-------|-------|------|------|-------|-------|-------|--------------|------|------|------|-------------|
| Resvd | DMAC5 | DMAC4 | XINT1 | RINT1 | HINT | INT3 | XINT2 | RINT2 | XINTO | RINT0 | TINT | INT2 | INT1 | INTO |

Figure 3-22. IFR and IMR

4 Documentation Support

Extensive documentation supports all TMS320[™] DSP family of devices from product announcement through applications development. The following types of documentation are available to support the design and use of the C5000[™] platform of DSPs:

- *TMS320C54x[™] DSP Functional Overview* (literature number SPRU307)
- Device-specific data sheets
- Complete user's guides
- Development support tools
- Hardware and software application reports

The five-volume TMS320C54x DSP Reference Set (literature number SPRU210) consists of:

- Volume 1: CPU and Peripherals (literature number SPRU131)
- Volume 2: Mnemonic Instruction Set (literature number SPRU172)
- Volume 3: Algebraic Instruction Set (literature number SPRU179)
- Volume 4: Applications Guide (literature number SPRU173)
- Volume 5: Enhanced Peripherals (literature number SPRU302)

The reference set describes in detail the TMS320C54x[™] DSP products currently available and the hardware and software applications, including algorithms, for fixed-point TMS320[™] DSP family of devices.

A series of DSP textbooks is published by Prentice-Hall and John Wiley & Sons to support digital signal processing research and education. The TMS320[™] DSP newsletter, *Details on Signal Processing*, is published quarterly and distributed to update TMS320[™] DSP customers on product information.

Information regarding TI DSP products is also available on the Worldwide Web at *http://www.ti.com* uniform resource locator (URL).

TMS320 and C5000 are trademarks of Texas Instruments.

5 Electrical Specifications

This section provides the absolute maximum ratings and the recommended operating conditions for the SMJ320VC5416 DSP.

5.1 Absolute Maximum Ratings

The list of absolute maximum ratings are specified over operating case temperature. Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Section 5.2 is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. All voltage values are with respect to DV_{SS} . Figure 5–1 provides the test load circuit values for a 3.3-V device.

| Supply voltage I/O range, DV _{DD} | |
|---|----------------|
| Supply voltage core range, CV _{DD} | 0.3 V to 2.0 V |
| Input voltage range | 0.3 V to 4.5 V |
| Output voltage range | 0.3 V to 4.5 V |
| Thermal resistance, Junction-to-Case, Θ_{JC} | 1.82°C/W |
| Operating case temperature range, T _C | 55°C to 115°C |
| Storage temperature range, T _{stg} | 55°C to 150°C |

5.2 Recommended Operating Conditions

| | | MIN | NOM | МАХ | UNIT |
|--|---|--|--|--|--|
| Device supply voltage, I/O | | 2.75 | 3.3 | 3.6 | V |
| Device supply voltage, core (VC5416-1 | 00) | 1.45 | 1.5 | 1.65 | V |
| Supply voltage, GND | | | 0 | | V |
| High-level input voltage, I/O | RS, INTn, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS1, HDS2, HAS, TRST, BIO, Dn, An, HDn, TCK DV _{DD} = 2.75 V to 3.6 V | 2.4 | | DV _{DD} + 0.3* | V |
| | All other inputs | 2 | | DV _{DD} + 0.3* | |
| | X2/CLKIN | -0.3* | | 0.42 | |
| Low-level input voltage | All other inputs | -0.3* | | 0.8 | V |
| High-level output current [†] | | | | -8 | mA |
| Low-level output current [†] | | | | 8 | mA |
| Operating case temperature | | -55 | | 115 | °C |
| | Device supply voltage, core (VC5416-1 Supply voltage, GND High-level input voltage, I/O Low-level input voltage High-level output current [†] Low-level output current [†] | Device supply voltage, core (VC5416-100) Supply voltage, GND High-level input voltage, I/O RS, INTn, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS1, HDS2, HAS, TRST, BIO, Dn, An, HDn, TCK DV _{DD} = 2.75 V to 3.6 V All other inputs Low-level input voltage High-level output current [†] | Device supply voltage, I/O 2.75 Device supply voltage, core (VC5416-100) 1.45 Supply voltage, GND RS, INTn, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS1, HDS2, HAS, TRST, BIO, Dn, An, HDn, TCK DV _{DD} = 2.75 V to 3.6 V 2.4 Low-level input voltage X2/CLKIN All other inputs 2 Low-level output current [†] -0.3* Low-level output current [†] -0.3* | $\begin{array}{c c c c c c } \hline Device \mbox{supply voltage, I/O} & 2.75 & 3.3 \\ \hline Device \mbox{supply voltage, core (VC5416-100)} & 1.45 & 1.5 \\ \hline Supply \mbox{voltage, GND} & & 1.45 & 0 \\ \hline Supply \mbox{voltage, GND} & & & & & & \\ \hline High-level \mbox{input voltage, I/O} & & & & & \\ \hline High-level \mbox{input voltage, I/O} & & & & & \\ \hline RS, INTn, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS7, HDS2, HAS, TRST, BIO, Dn, An, HDn, TCK DV_{DD} = 2.75 V to 3.6 V & \\ \hline All \mbox{other inputs} & 2 & & & \\ \hline Low-level \mbox{input voltage} & & & & & & \\ \hline High-level \mbox{output current}^{\dagger} & & & & & & \\ \hline Low-level \mbox{output current}^{\dagger} & & & & & & \\ \hline \end{array}$ | $\begin{array}{c c c c c c } \hline Device \mbox{supply voltage, I/O} & 2.75 & 3.3 & 3.6 \\ \hline Device \mbox{supply voltage, core (VC5416-100)} & 1.45 & 1.5 & 1.65 \\ \hline Supply voltage, GND & & & & & & & & & \\ \hline Supply voltage, GND & & & & & & & & & \\ \hline RS, INTri, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS1, HDS2, HAS, TRST, BIO, Dn, An, HDn, TCK DV_{DD} = 2.75 V to 3.6 V & & & & & & & & \\ \hline High-level input voltage, I/O & & & & & & & & & & & & \\ \hline Multiple Voltage input voltage & & & & & & & & & & & & & & \\ \hline Multiple Voltage & & & & & & & & & & & & & & & \\ \hline Multiple Voltage & & & & & & & & & & & & & & & & & & &$ |

* Not production tested.

[†] Note that maximum output currents are DC values only. Transient currents may exceed these values.

5.3 Electrical Characteristics Over Recommended Operating Case Temperature Range (Unless Otherwise Noted)

| | PARAME | ſER | TEST CONDITIONS | MIN | TYP [†] | MAX | UNIT |
|------------------|---|------------------------------|--|------|------------------|-----|------|
| | | t | DV_{DD} = 2.75 V to 3 V, I_{OH} = MAX | 2.2 | | | v |
| V _{OH} | High-level output volta | ige+ | $DV_{DD} = 3 V \text{ to } 3.6 V, I_{OH} = MAX$ | 2.4 | | | v |
| V _{OL} | Low-level output volta | ge‡ | I _{OL} = MAX | | | 0.4 | V |
| | | X2/CLKIN | | -40 | | 40 | μA |
| | | TRST, HPI16 | With internal pulldown | -10 | | 800 | |
| | | HPIENA | With internal pulldown, $\overline{RS} = 0$ | -10 | | 400 | |
| l _l | Input current (V _I = DV _{SS} to DV _{DD}) | TMS, TCK, TDI, HPI§ | With internal pullups | -400 | | 10 | μΑ |
| | | A[17:0], D[15:0], HD[7:0] | Bus holders enabled, $DV_{DD} = MAX \Rightarrow$ | -275 | | 275 | |
| | | All other input-only pins | | -5 | | 5 | |
| I _{DDC} | Supply current, core C | PU | $CV_{DD} = 1.6 \text{ V}, \text{ f}_{\text{x}} = 100 \text{ ,}^{\P} \text{ T}_{\text{C}} = 25^{\circ}\text{C}$ | 60# | | | mA |
| I _{DDP} | Supply current, pins | | DV _{DD} = 3.0 V, f _x = 100 MHz, [¶] T _C = 25°C | | 40 | | mA |
| | | IDLE2 | PLL × 1 mode, 20 MHz input | | 2 | | |
| I _{DD} | Supply current, standby | IDLE3 Divide-by-two | $T_{\rm C} = 25^{\circ}{\rm C}$ | | 1 | | mA |
| | Standby | mode, CLKIN stopped | T _C = 115°C | | 38 | | |
| Ci | Input capacitance | • | | | | 15 | pF |
| Co | Output capacitance | | | | | 15 | pF |

[†] All values are typical unless otherwise specified.

[‡] All input and output voltage levels except RS, INTO-INT3, NMI, X2/CLKIN, CLKMD1-CLKMD3, BCLKRn, BCLKXn, HCS, HAS, HDS1, HDS2, BIO, TCK, TRST, Dn, An, HDn are LVTTL-compatible.

[§] HPI input signals except for HPIENA and HPI16, when HPIENA = 0.

 ¶ Clock mode: PLL × 1 with external source

[#] This value was obtained with 50% usage of MAC and 50% usage of NOP instructions. Actual operating current varies with program being executed.

This value was obtained with single-cycle external writes, CLKOFF = 0 and load = 15 pF. For more details on how this calculation is performed, refer to the *Calculation of TMS320LC54x Power Dissipation* application report (literature number SPRA164).

 $\Rightarrow V_{IL(MIN)} \le V_I \le V_{IL(MAX)}$ or $V_{IH(MIN)} \le V_I \le V_{IH(MAX)}$




Figure 5-1. 3.3-V Test Load Circuit

5.4 Package Thermal Resistance Characteristics

Table 5-1 provides the estimated thermal resistance characteristics for the recommended package types used on the SMJ320VC5416 DSP.

| Table 5-1. | Thermal | Resistance | Characteristics |
|------------|---------|------------|-----------------|
|------------|---------|------------|-----------------|

| PARAMETER | HFG PACKAGE | UNIT | | |
|-----------------|-------------|------|--|--|
| $R_{\Theta JC}$ | 1.82 | °C/W | | |

5.5 Timing Parameter Symbology

Timing parameter symbols used in the timing requirements and switching characteristics tables are created in accordance with JEDEC Standard 100. To shorten the symbols, some of the pin names and other related terminology have been abbreviated as follows:

Lowercase subscripts and their meanings:

| а | access time |
|-----|--|
| с | cycle time (period) |
| d | delay time |
| dis | disable time |
| en | enable time |
| f | fall time |
| h | hold time |
| r | rise time |
| su | setup time |
| t | transition time |
| v | valid time |
| w | pulse duration (width) |
| Х | Unknown, changing, or don't care level |

Letters and symbols and their meanings:

| Н | High |
|---|------|
| L | Low |

- V Valid
- Z High impedance

5.6 Internal Oscillator With External Crystal

The internal oscillator is enabled by selecting the appropriate clock mode at reset (this is device-dependent; see Section 3.10) and connecting a crystal or ceramic resonator across X1 and X2/CLKIN. The CPU clock frequency is one-half, one-fourth, or a multiple of the oscillator frequency. The multiply ratio is determined by the bit settings in the CLKMD register.

The crystal should be in fundamental-mode operation, and parallel resonant, with an effective series resistance of 30 Ω maximum and power dissipation of 1 mW. The connection of the required circuit, consisting of the crystal and two load capacitors, is shown in Figure 5–2. The load capacitors, C₁ and C₂, should be chosen such that the equation below is satisfied. C_L (recommended value of 10 pF) in the equation is the load specified for the crystal.

$$C_{L} = \frac{C_{1}C_{2}}{(C_{1} + C_{2})}$$

Table 5-2. Input Clock Frequency Characteristics

| | MIN | MAX | UNIT |
|--------------------------------------|-----|-----------------|------|
| f _x Input clock frequency | 10† | 20 [‡] | MHz |

 † This device utilizes a fully static design and therefore can operate with $t_{c(CI)}$ approaching $\infty.$

[‡] It is recommended that the PLL multiply by N clocking option be used for maximum frequency operation.




Figure 5-2. Internal Divide-by-Two Clock Option With External Crystal

5.7 Clock Options

The frequency of the reference clock provided at the CLKIN pin can be divided by a factor of two or four or multiplied by one of several values to generate the internal machine cycle.

5.7.1 Divide-By-Two and Divide-By-Four Clock Options

The frequency of the reference clock provided at the X2/CLKIN pin can be divided by a factor of two or four to generate the internal machine cycle. The selection of the clock mode is described in Section 3.10.

When an external clock source is used, the frequency injected must conform to specifications listed in Table 5-4.

An external frequency source can be used by applying an input clock to X2/CLKIN with X1 left unconnected.

Table 5–3 shows the configuration options for the CLKMD pins that generate the external divide-by-2 or divide-by-4 clock option.

| CLKMD1 | CLKMD2 | CLKMD3 | CLOCK MODE |
|--------|--------|--------|-------------------|
| 0 | 0 | 0 | 1/2, PLL disabled |
| 1 | 0 | 1 | 1/4, PLL disabled |
| 1 | 1 | 1 | 1/2, PLL disabled |

Table 5-3. Clock Mode Pin Settings for the Divide-By-2 and By Divide-by-4 Clock Options

Table 5-4 and Table 5-5 assume testing over recommended operating conditions and H = $0.5t_{c(CO)}$ (see Figure 5-3).

| | | 5416-100 | | |
|---------------------|-------------------------------|----------|-----|------|
| | | MIN | MAX | UNIT |
| t _{c(CI)} | Cycle time, X2/CLKIN | 20 | | ns |
| t _{f(CI)} | Fall time, X2/CLKIN | | 4* | ns |
| t _{r(CI)} | Rise time, X2/CLKIN | | 4* | ns |
| t _{w(CIL)} | Pulse duration, X2/CLKIN low | 4* | | ns |
| t _{w(CIH)} | Pulse duration, X2/CLKIN high | 4* | | ns |

Table 5-4. Divide-By-2 and Divide-by-4 Clock Options Timing Requirements

* Not production tested.


Table 5-5. Divide-By-2 and Divide-by-4 Clock Options Switching Characteristics

| | PARAMETER | | 5416-100 | | | |
|------------------------|--|--------|----------|--------|------|--|
| | | | TYP | MAX | UNIT | |
| t _{c(CO)} | Cycle time, CLKOUT | 10† | | ‡ | ns | |
| t _{d(CIH-CO)} | Delay time, X2/CLKIN high to CLKOUT high/low | 4 | 7 | 11 | ns | |
| t _{f(CO)} | Fall time, CLKOUT | | | 2* | ns | |
| t _{r(CO)} | Rise time, CLKOUT | | | 2* | ns | |
| t _{w(COL)} | Pulse duration, CLKOUT low | H -3* | Н | H + 1* | ns | |
| t _{w(COH)} | Pulse duration, CLKOUT high | H - 2* | Н | H + 1* | ns | |

* Not production tested.

[†] It is recommended that the PLL clocking option be used for maximum frequency operation.

[‡] This device utilizes a fully static design and therefore can operate with $t_{c(CI)}$ approaching ∞ .



NOTE A: The CLKOUT timing in this diagram assumes the CLKOUT divide factor (DIVFCT field in the BSCR) is configured as 00 (CLKOUT not divided). DIVFCT is configured as CLKOUT divided-by-4 mode following reset.

Figure 5-3. External Divide-by-Two Clock Timing

5.7.2 Multiply-By-N Clock Option (PLL Enabled)

The frequency of the reference clock provided at the X2/CLKIN pin can be multiplied by a factor of N to generate the internal machine cycle. The selection of the clock mode and the value of N is described in Section 3.10. Following reset, the software PLL can be programmed for the desired multiplication factor. Refer to the *TMS320C54x DSP Reference Set, Volume 1: CPU and Peripherals* (literature number SPRU131) for detailed information on programming the PLL.

When an external clock source is used, the external frequency injected must conform to specifications listed in Table 5–6.

Table 5-6 and Table 5-7 assume testing over recommended operating conditions and H = $0.5t_{c(CO)}$ (see Figure 5-4).

| | | | 5416- | | |
|---------------------|-------------------------------|--|-------|-----|------|
| | | | MIN | MAX | UNIT |
| | | Integer PLL multiplier N (N = 1-15) [†] | 20 | 200 | |
| t _{c(Cl)} | Cycle time, X2/CLKIN | PLL multiplier N = $x.5^{\dagger}$ | 20 | 100 | ns |
| . , | | PLL multiplier N = x.25, x.75 [†] | 20 | 50 | |
| t _{f(CI)} | Fall time, X2/CLKIN | | | 4* | ns |
| t _{r(CI)} | Rise time, X2/CLKIN | | | 4* | ns |
| t _{w(CIL)} | Pulse duration, X2/CLKIN low | | 4* | | ns |
| t _{w(CIH)} | Pulse duration, X2/CLKIN high | | 4* | | ns |

Table 5-6. Multiply-By-N Clock Option Timing Requirements


* Not production tested.

[†] N is the multiplication factor.

Table 5-7. Multiply-By-N Clock Option Switching Characteristics

| | PARAMETER | | | 5416-100 | | |
|-----------------------|--|--|--------|----------|--------|------|
| | | | | TYP | MAX | UNIT |
| t _{c(CO)} | Cycle time, CLKOUT | | 10 | | | ns |
| t _{d(CI-CO)} | Delay time, X2/CLKIN high/low to CLKOUT high/low | | 4 | 7 | 11 | ns |
| t _{f(CO)} | Fall time, CLKOUT | | | | 2* | ns |
| t _{r(CO)} | Rise time, CLKOUT | | | | 2* | ns |
| t _{w(COL)} | Pulse duration, CLKOUT low | | H - 3* | Н | H + 1* | ns |
| t _{w(COH)} | Pulse duration, CLKOUT high | | H - 2* | Н | H + 1* | ns |
| t _p | Transitory phase, PLL lock-up time | | | | 30* | μs |

* Not production tested.



NOTE A: The CLKOUT timing in this diagram assumes the CLKOUT divide factor (DIVFCT field in the BSCR) is configured as 00 (CLKOUT not divided). DIVFCT is configured as CLKOUT divided-by-4 mode following reset.

Figure 5-4. Multiply-by-One Clock Timing

5.8 Memory and Parallel I/O Interface Timing

5.8.1 Memory Read

External memory reads can be performed in consecutive or nonconsecutive mode under control of the $\overline{\text{CONSEC}}$ bit in the BSCR. Table 5–8 and Table 5–9 assume testing over recommended operating conditions with $\overline{\text{MSTRB}} = 0$ and H = $0.5t_{c(CO)}$ (see Figure 5–5 and Figure 5–6).

| | | 5416- | 5416-100 | |
|---------------------|--|-------|----------|----|
| | | MIN | MIN MAX | |
| t _{a(A)M1} | Access time, read data access from address valid, first read $\operatorname{access}^{\dagger}$ | | 4H-9 | ns |
| t _{a(A)M2} | Access time, read data access from address valid, consecutive read accesses [†] | | 2H-9 | ns |
| t _{su(D)R} | Setup time, read data valid before CLKOUT low | 7 | | ns |
| t _{h(D)R} | Hold time, read data valid after CLKOUT low | 0 | | ns |

Table 5-8. Memory Read Timing Requirements


[†] Address,R/W, PS, DS, and IS timings are all included in timings referenced as address.

Table 5-9. Memory Read Switching Characteristics

| | | 5416-100 | | UNIT |
|--------------------------|--|----------|---------|------|
| | PARAMETER | MIN | MIN MAX | |
| t _{d(CLKL-A)} | Delay time, CLKOUT low to address valid [†] | - 1* | 4 | ns |
| t _{d(CLKL-MSL)} | Delay time, CLKOUT low to MSTRB low | - 1* | 4 | ns |
| t _{d(CLKL-MSH)} | Delay time, CLKOUT low to MSTRB high | - 1* | 4* | ns |

* Not production tested.

⁺ Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.



 † Address,R/W, PS, DS, and $\overline{\text{IS}}$ timings are all included in timings referenced as address.

Figure 5-5. Nonconsecutive Mode Memory Reads




Figure 5-6. Consecutive Mode Memory Reads


5.8.2 Memory Write

Table 5–10 assumes testing over recommended operating conditions with $\overline{\text{MSTRB}} = 0$ and $H = 0.5t_{c(CO)}$ (see Figure 5–7).

| | | 541 | 6-100 | |
|--------------------------|---|-----------|---------|------|
| | PARAMETER | MIN | MAX | UNIT |
| t _{d(CLKL-A)} | Delay time, CLKOUT low to address valid [†] | - 1* | 4 | ns |
| t _{su(A)MSL} | Setup time, address valid before MSTRB low [†] | 2H - 3 | | ns |
| t _{d(CLKL-D)W} | Delay time, CLKOUT low to data valid | - 1* | 4 | ns |
| t _{su(D)MSH} | Setup time, data valid before MSTRB high | 2H - 5 | 2H + 6 | ns |
| t _{h(D)MSH} | Hold time, data valid after MSTRB high | 2H - 5* | 2H + 6* | ns |
| t _{d(CLKL-MSL)} | Delay time, CLKOUT low to MSTRB low | - 1* | 4 | ns |
| t _{w(SL)MS} | Pulse duration, MSTRB low | 2H - 3.2* | | ns |
| t _{d(CLKL-MSH)} | Delay time, CLKOUT low to MSTRB high | - 1* | 4* | ns |

* Not production tested.

[†] Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.



[†] Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.

Figure 5-7. Memory Write (MSTRB = 0)

5.8.3 I/O Read

Table 5-11 and Table 5-12 assume testing over recommended operating conditions, $\overline{\text{IOSTRB}} = 0$, and $H = 0.5t_{c(CO)}$ (see Figure 5-8).

| | | 54 | 5416-100 MIN MAX | |
|---------------------|--|-----|---------------------|----|
| | | MIN | | |
| t _{a(A)M1} | Access time, read data access from address valid, first read $\operatorname{access}^{\dagger}$ | | 4H - 9 | ns |
| t _{su(D)R} | Setup time, read data valid before CLKOUT low | 7 | , | ns |
| t _{h(D)R} | Hold time, read data valid after CLKOUT low | (|) | ns |

| Table 5-11. | I/O Read | Timina Rea | quirements |
|-------------|----------|------------|----------------|
| | yo nouu | | quin 011101110 |


[†] Address R/W, PS, DS, and IS timings are included in timings referenced as address.

Table 5-12. I/O Read Switching Characteristics

| | 5410 | | -100 | UNIT |
|---------------------------|--|------|------|------|
| | PARAMETER | MIN | MAX | UNIT |
| t _{d(CLKL-A)} | Delay time, CLKOUT low to address valid [†] | - 1* | 4 | ns |
| t _{d(CLKL-IOSL)} | Delay time, CLKOUT low to IOSTRB low | - 1* | 4 | ns |
| t _{d(CLKL-IOSH)} | Delay time, CLKOUT low to IOSTRB high | - 1* | 4 | ns |

* Not production tested.

[†] Address R/W, PS, DS, and IS timings are included in timings referenced as address.



[†] Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.

Figure 5-8. Parallel I/O Port Read (IOSTRB = 0)


5.8.4 I/O Write

Table 5–13 assumes testing over recommended operating conditions, $\overline{\text{IOSTRB}} = 0$, and $\text{H} = 0.5t_{c(CO)}$ (see Figure 5–9).

| | | 5416-100 | | | |
|---------------------------|--|----------|---------|---------|------|
| | PARAMETER | | MIN | MAX | UNIT |
| t _{d(CLKL-A)} | Delay time, CLKOUT low to address valid [†] | | - 1* | 4 | ns |
| t _{su(A)IOSL} | Setup time, address valid before IOSTRB low [†] | | 2H - 3 | | ns |
| t _{d(CLKL-D)W} | Delay time, CLKOUT low to write data valid | | - 1* | 4 | ns |
| t _{su(D)IOSH} | Setup time, data valid before IOSTRB high | | 2H - 5 | 2H + 6* | ns |
| t _{h(D)IOSH} | Hold time, data valid after IOSTRB high | | 2H - 5* | 2H + 6* | ns |
| t _{d(CLKL-IOSL)} | Delay time, CLKOUT low to IOSTRB low | | - 1* | 4 | ns |
| t _{w(SL)IOS} | Pulse duration, IOSTRB low | | 2H - 2* | | ns |
| t _{d(CLKL-IOSH)} | Delay time, CLKOUT low to IOSTRB high | | - 1* | 4 | ns |

* Not production tested.

[†] Address R/W, PS, DS, and IS timings are included in timings referenced as address.



[†] Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.



5.9 Ready Timing for Externally Generated Wait States

Table 5-14 and Table 5-15 assume testing over recommended operating conditions and H = $0.5t_{c(CO)}$ (see Figure 5-10, Figure 5-11, Figure 5-12, and Figure 5-13).

| Table 5-14. | Ready Timing Rec | quirements for Externally | / Generated Wait States [↑] | |
|-------------|------------------|---------------------------|--------------------------------------|--|
| | | | | |

| | | 541 | 6-100 | |
|----------------------------|---|-----|-----------|------|
| | | MIN | MAX | UNIT |
| t _{su(RDY)} | Setup time, READY before CLKOUT low | 7 | | ns |
| t _{h(RDY)} | Hold time, READY after CLKOUT low | 0 | | ns |
| t _{v(RDY)} MSTRB | Valid time, READY after MSTRB low [‡] | | 4H - 6.2* | ns |
| t _{h(RDY)} MSTRB | Hold time, READY after MSTRB low [‡] | 4H* | | ns |
| t _{v(RDY)} IOSTRB | Valid time, READY after IOSTRB low [‡] | | 4H - 6* | ns |
| t _{h(RDY)} IOSTRB | Hold time, READY after IOSTRB low [‡] | 4H* | | ns |

* Not production tested.

[†] The hardware wait states can be used only in conjunction with the software wait states to extend the bus cycles. To generate wait states by READY, at least two software wait states must be programmed. READY is not sampled until the completion of the internal software wait states.

[‡] These timings are included for reference only. The critical timings for READY are those referenced to CLKOUT.

Table 5-15. Ready Switching Characteristics for Externally Generated Wait States[†]

| | PABAMETER | 5416-100 MIN MAX | | |
|----------------------|------------------------------------|---------------------|---|------|
| | PARAMETER | | | UNIT |
| t _{d(MSCL)} | Delay time, CLKOUT low to MSC low | -1* | 4 | ns |
| t _{d(MSCH)} | Delay time, CLKOUT low to MSC high | -1* | 4 | ns |

* Not production tested.

[†] The hardware wait states can be used only in conjunction with the software wait states to extend the bus cycles. To generate wait states by READY, at least two software wait states must be programmed. READY is not sampled until the completion of the internal software wait states.

Electrical Specifications




Figure 5-10. Memory Read With Externally Generated Wait States




Figure 5-11. Memory Write With Externally Generated Wait States

Electrical Specifications




Figure 5-12. I/O Read With Externally Generated Wait States




Figure 5-13. I/O Write With Externally Generated Wait States

5.10 HOLD and HOLDA Timings

Table 5–16 and Table 5–17 assume testing over recommended operating conditions and H = $0.5t_{c(CO)}$ (see Figure 5–14).

| | | 5416-100 | |
|-----------------------|---|----------|------|
| | | MIN MAX | UNIT |
| t _{w(HOLD)} | Pulse duration, HOLD low duration | 4H+8* | ns |
| t _{su(HOLD)} | Setup time, HOLD before CLKOUT low [†] | 7 | ns |

Table 5-16. HOLD and HOLDA Timing Requirements

* Not production tested.

Table 5-17. HOLD and HOLDA Switching Characteristics

| | | 541 | 5416-100 MIN MAX | |
|---------------------------|--|-------|---------------------|----|
| | PARAMETER | MIN | | |
| t _{dis(CLKL-A)} | Disable time, Address, PS, DS, IS high impedance from CLKOUT low | | 3* | ns |
| t _{dis(CLKL-RW)} | Disable time, R/W high impedance from CLKOUT low | | 3* | ns |
| t _{dis(CLKL-S)} | Disable time, MSTRB, IOSTRB high impedance from CLKOUT low | | 3* | ns |
| t _{en(CLKL-A)} | Enable time, Address, PS, DS, IS valid from CLKOUT low | | 2H+3* | ns |
| t _{en(CLKL-RW)} | Enable time, R/W enabled from CLKOUT low | | 2H+3* | ns |
| t _{en(CLKL-S)} | Enable time, MSTRB, IOSTRB enabled from CLKOUT low | 2 | 2H+3* | ns |
| t _{v(HOLDA)} | Valid time, HOLDA low after CLKOUT low | - 1* | 4 | ns |
| | Valid time, HOLDA high after CLKOUT low | - 1* | 4* | ns |
| t _{w(HOLDA)} | Pulse duration, HOLDA low duration | 2H-3* | | ns |
| | | • | | |

* Not production tested.

[†] This input can be driven from an asynchronous source, therefore, there are no specific timing requirements with respect to CLKOUT, however, if this timing is met, the input will be recognized on the CLKOUT edge referenced.




Figure 5-14. HOLD and HOLDA Timings (HM = 1)

5.11 Reset, BIO, Interrupt, and MP/MC Timings

Table 5-18 assumes testing over recommended operating conditions and H = $0.5t_{c(CO)}$ (see Figure 5-15, Figure 5-16, and Figure 5-17).

| | | 5416-100 | UNIT |
|--------------------------|--|----------|------|
| | | MIN MAX | |
| t _{h(RS)} | Hold time, RS after CLKOUT low# | 2* | ns |
| t _{h(BIO)} | Hold time, BIO after CLKOUT low# | 4 | ns |
| t _{h(INT)} | Hold time, INTn, NMI, after CLKOUT low ^{†#} | 0 | ns |
| t _{h(MPMC)} | Hold time, MP/MC after CLKOUT low [#] | 4* | ns |
| t _{w(RSL)} | Pulse duration, RS low ^{‡§} | 4H+3* | ns |
| t _{w(BIO)S} | Pulse duration, BIO low, synchronous | 2H+3* | ns |
| t _{w(BIO)A} | Pulse duration, BIO low, asynchronous | 4H* | ns |
| t _{w(INTH)} s | Pulse duration, INTn, NMI high (synchronous) | 2H+2* | ns |
| t _{w(INTH)} A | Pulse duration, INTn, NMI high (asynchronous) | 4H* | ns |
| t _{w(INTL)} s | Pulse duration, INTn, NMI low (synchronous) | 2H+2* | ns |
| t _{w(INTL)A} | Pulse duration, INTn, NMI low (asynchronous) | 4H* | ns |
| t _{w(INTL)} WKP | Pulse duration, INTn, NMI low for IDLE2/IDLE3 wakeup | 7* | ns |
| t _{su(RS)} | Setup time, RS before X2/CLKIN low ^{1#} | 3* | ns |
| t _{su(BIO)} | Setup time, BIO before CLKOUT low [#] | 7 | ns |
| t _{su(INT)} | Setup time, INTn, NMI, RS before CLKOUT low# | 7 | ns |
| t _{su(MPMC)} | Setup time, MP/MC before CLKOUT low# | 5* | ns |

Table 5-18. Reset, BIO, Interrupt, and MP/MC Timing Requirements

* Not production tested.


[†] The external interrupts (INT0-INT3, NMI) are synchronized to the core CPU by way of a two-flip-flop synchronizer that samples these inputs with consecutive falling edges of CLKOUT. The input to the interrupt pins is required to represent a 1-0-0 sequence at the timing that is corresponding to three CLKOUTs sampling sequence.


[‡] If the PLL mode is selected, then at power-on sequence, or at wakeup from IDLE3, RS must be held low for at least 50 µs to ensure synchronization and lock-in of the PLL.

§ Note that RS may cause a change in clock frequency, therefore changing the value of H.

[¶] The diagram assumes clock mode is divide-by-2 and the CLKOUT divide factor is set to no-divide mode (DIVFCT=00 field in the BSCR).

[#] These inputs can be driven from an asynchronous source, therefore, there are no specific timing requirements with respect to CLKOUT, however, if setup and hold timings are met, the input will be recognized on the CLKOUT edge referenced.









Figure 5-16. Interrupt Timing





5.12 Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings

Table 5-19 assumes testing over recommended operating conditions and $H = 0.5t_{c(CO)}$ (see Figure 5-18).

Table 5-19. Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Switching Characteristics

| | | 5416-100 | | |
|---|---|---|--|--|
| PARAMETER | MIN | MAX | UNIT | |
| Delay time, CLKOUT low to IAQ low | - 1* | 4 | ns | |
| Delay time, CLKOUT low to IAQ high | - 1* | 4 | ns | |
| Delay time, CLKOUT low to IACK low | - 1.2* | 4 | ns | |
| Delay time, CLKOUT low to IACK high | - 1* | 4 | ns | |
| Delay time, CLKOUT low to address valid | - 1* | 4 | ns | |
| Pulse duration, IAQ low | 2H - 2* | | ns | |
| Pulse duration, IACK low | 2H - 3* | | ns | |
| | Delay time, CLKOUT low to IAQ high Delay time, CLKOUT low to IACK low Delay time, CLKOUT low to IACK high Delay time, CLKOUT low to address valid Pulse duration, IAQ low | PARAMETER MIN Delay time, CLKOUT low to IAQ low - 1* Delay time, CLKOUT low to IAQ high - 1* Delay time, CLKOUT low to IAQK low - 1.2* Delay time, CLKOUT low to IACK low - 1* Delay time, CLKOUT low to IACK high - 1* Delay time, CLKOUT low to IACK high - 1* Delay time, CLKOUT low to address valid - 1* Delay time, CLKOUT low to address valid - 1* Delay time, CLKOUT low to address valid - 1* | PARAMETER MIN MAX Delay time, CLKOUT low to IAQ low - 1* 4 Delay time, CLKOUT low to IAQ high - 1* 4 Delay time, CLKOUT low to IAQ high - 1* 4 Delay time, CLKOUT low to IAQK low - 1.2* 4 Delay time, CLKOUT low to IACK high - 1* 4 Delay time, CLKOUT low to IACK high - 1* 4 Delay time, CLKOUT low to address valid - 1* 4 Delay time, CLKOUT low to address valid - 1* 4 Pulse duration, IAQ low 2H - 2* 2H - 2* | |




Figure 5-18. Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings

5.13 External Flag (XF) and TOUT Timings

Table 5–20 assumes testing over recommended operating conditions and $H = 0.5t_{c(CO)}$ (see Figure 5–19 and Figure 5–20).

| | DADAMETED | | | |
|-----------------------|-------------------------------------|---------|-----|------|
| | PARAMETER | MIN | MAX | UNIT |
| | Delay time, CLKOUT low to XF high | - 1* | 4 | |
| t _{d(XF)} | Delay time, CLKOUT low to XF low | - 1* | 4 | ns |
| t _{d(TOUTH)} | Delay time, CLKOUT low to TOUT high | - 1* | 4* | ns |
| t _{d(TOUTL)} | Delay time, CLKOUT low to TOUT low | - 1* | 4 | ns |
| t _{w(TOUT)} | Pulse duration, TOUT | 2H - 4* | | ns |

Table 5-20. External Flag (XF) and TOUT Switching Characteristics




Figure 5-19. External Flag (XF) Timing




Figure 5-20. TOUT Timing

5.14 Multichannel Buffered Serial Port (McBSP) Timing

5.14.1 McBSP Transmit and Receive Timings

Table 5-21 and Table 5-22 assume testing over recommended operating conditions (see Figure 5-21 and Figure 5-22).

| | | | 5416- | 100 | |
|-----------------------------|--|-------------|-----------------|-----|------|
| | | | MIN | MAX | UNIT |
| t _{c(BCKRX)} | Cycle time, BCLKR/X [‡] | BCLKR/X ext | 4P [§] | | ns |
| t _{w(BCKRX)} | Pulse duration, BCLKR/X high or BCLKR/X low [‡] | BCLKR/X ext | 2P-1*§ | | ns |
| | | BCLKR int | 8 | | |
| t _{su(BFRH-BCKRL)} | Setup time, external BFSR high before BCLKR low | BCLKR ext | 1 | | ns |
| t _{h(BCKRL-BFRH)} | | BCLKR int | 1 | | |
| | Hold time, external BFSR high after BCLKR low | BCLKR ext | 2 | | ns |
| | | BCLKR int | 7 | | |
| t _{su(BDRV-BCKRL)} | Setup time, BDR valid before BCLKR low | BCLKR ext | 1 | | ns |
| | | BCLKR int | 2 | | |
| t _{h(BCKRL-BDRV)} | Hold time, BDR valid after BCLKR low | BCLKR ext | 3 | | ns |
| | | BCLKX int | 8 | | |
| t _{su(BFXH-BCKXL)} | Setup time, external BFSX high before BCLKX low | BCLKX ext | 1 | | ns |
| | | BCLKX int | 0 | | |
| t _{h(BCKXL-BFXH)} | Hold time, external BFSX high after BCLKX low | BCLKX ext | 2 | | ns |
| t _{r(BCKRX)} | Rise time, BCKR/X | BCLKR/X ext | | 6* | ns |
| t _{f(BCKRX)} | Fall time, BCKR/X | BCLKR/X ext | | 6* | ns |

Table 5-21. McBSP Transmit and Receive Timing Requirements[†]

* Not production tested.

[†] CLKRP = CLKXP = FSRP = FSXP = 0. If the polarity of any of the signals is inverted, then the timing references of that signal are also inverted.
 [‡] Note that in some cases, for example when driving another 54x device McBSP, maximum serial port clocking rates may not be achievable at maximum CPU clock frequency due to transmitted data timings and corresponding receive timing requirements. A separate detailed timing analysis should be performed for each specific McBSP interface.

P = 1 / (2 * processor clock)

| | | | 54 | | 5416-100 MIN MAX | | | | | |
|--------------------------------|--|---------------------|-------------|---------------------|---------------------|------|--|--|--|--|
| | PARAMETER | | | | | UNIT | | | | |
| t _{c(BCKRX)} | Cycle time, BCLKR/X [#] | | BCLKR/X int | 4P [‡] | | ns | | | | |
| t _{w(BCKRXH)} | Pulse duration, BCLKR/X high# | | BCLKR/X int | D - 1*§ | D + 1*§ | ns | | | | |
| t _{w(BCKRXL)} | Pulse duration, BCLKR/X low [#] | | BCLKR/X int | C - 1* [§] | C + 1*§ | ns | | | | |
| | | BCLKR int | - 3* | 3 | ns | | | | | |
| t _{d(BCKRH-BFRV)} | Delay time, BCLKR high to internal BFSR valid | BCLKR ext | 0* | 11 | ns | | | | | |
| | | BCLKX int | - 1* | 5 | | | | | | |
| t _{d(BCKXH-BFXV)} | Delay time, BCLKX high to internal BFSX valid | BCLKX ext | 3* | 11 | ns | | | | | |
| | Disable time, BCLKX high to BDX high impedance | following last data | BCLKX int | | 6* | | | | | |
| t _{dis} (BCKXH-BDXHZ) | bit of transfer | BCLKX ext | | 10* | ns | | | | | |
| | | | BCLKX int | - 1* [¶] | 10 | | | | | |
| | | DXENA = 0 | BCLKX ext | 3* | 20 | 1 | | | | |
| t _{d(BCKXH-BDXV)} | Delay time, BCLKX high to BDX valid | | BCLKX int | - 1* [¶] | 20 | ns | | | | |
| | DXENA = 1 | | BCLKX ext | 2.8* | 30 | | | | | |
| | Delay time, BFSX high to BDX valid | | BFSX int | -1.2* [¶] | 7* | | | | | |
| t _{d(BFXH-BDXV)} | ONLY applies when in data delay 0 (XDATDLY = 00b) mode | | BFSX ext | 3* | 11* | ns | | | | |

Table 5-22. McBSP Transmit and Receive Switching Characteristics[†]

* Not production tested.

[†] CLKRP = CLKXP = FSRP = FSXP = 0. If the polarity of any of the signals is inverted, then the timing references of that signal are also inverted. [‡] P = 1 / (2 * processor clock)

§ T = BCLKRX period = (1 + CLKGDV) * 2P

C = BCLKRX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) * 2P when CLKGDV is even

D = BCLKRX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) * 2P when CLKGDV is even

[¶] Minimum delay times also represent minimum output hold times.

Note that in some cases, for example when driving another 54x device McBSP, maximum serial port clocking rates may not be achievable at maximum CPU clock frequency due to transmitted data timings and corresponding receive timing requirements. A separate detailed timing analysis should be performed for each specific McBSP interface.




Figure 5-21. McBSP Receive Timings

Electrical Specifications




Figure 5-22. McBSP Transmit Timings

5.14.2 McBSP General-Purpose I/O Timing

Table 5-23 and Table 5-24 assume testing over recommended operating conditions (see Figure 5-23).

| Table 5-23 | . McBSP General- | Purpose I/O | Timing | Requirements |
|------------|------------------|-------------|--------|--------------|
|------------|------------------|-------------|--------|--------------|

| | 5416-100 MIN MAX | | |
|---|---------------------|---|---|
| | | | UNIT |
| Setup time, BGPIOx input mode before CLKOUT high [†] | 7 | | ns |
| Hold time, BGPIOx input mode after CLKOUT high [†] | 0 | | ns |
| | | MIN Setup time, BGPIOx input mode before CLKOUT high [†] 7 | MIN MAX Setup time, BGPIOx input mode before CLKOUT high [†] 7 |


[†] BGPIOx refers to BCLKRx, BFSRx, BDRx, BCLKXx, or BFSXx when configured as a general-purpose input.

Table 5-24. McBSP General-Purpose I/O Switching Characteristics

| PARAMETER | | 5416- | | |
|---------------------------|--|-------|-----|------|
| | | MIN | MAX | UNIT |
| t _{d(COH-BGPIO)} | Delay time, CLKOUT high to BGPIOx output mode [‡] | - 2* | 4 | ns |

* Not production tested.

[‡] BGPIOx refers to BCLKRx, BFSRx, BCLKXx, BFSXx, or BDXx when configured as a general-purpose output.



[†] BGPIOx refers to BCLKRx, BFSRx, BDRx, BCLKXx, or BFSXx when configured as a general-purpose input.

[‡] BGPIOx refers to BCLKRx, BFSRx, BCLKXx, BFSXx, or BDXx when configured as a general-purpose output.

Figure 5-23. McBSP General-Purpose I/O Timings

5.14.3 McBSP as SPI Master or Slave Timing

Table 5-25 to Table 5-32 assume testing over recommended operating conditions (see Figure 5-24, Figure 5-25, Figure 5-26, and Figure 5-27).

| Table 5-25. | McBSP as | SPI Master or | Slave Timin | g Requirem | ents (CLKSTP = | = 10b, CLKXP = 0) [†] |
|-------------|----------|---------------|-------------|------------|----------------|--------------------------------|
| | | | | | | |

| | | | 5416-100 | | | | |
|-----------------------------|--|-----|----------|------------------------|-------|----|--|
| | | MAS | MASTER | | SLAVE | | |
| | | MIN | MAX | MIN | MAX | | |
| t _{su(BDRV-BCKXL)} | Setup time, BDR valid before BCLKX low | 12 | | 2.2 - 6P* [‡] | | ns | |
| t _{h(BCKXL-BDRV)} | Hold time, BDR valid after BCLKX low | 4 | | 5 + 12P* [‡] | | ns | |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

P = 1 / (2 * processor clock)

| Table 5-26 | McBSP as S | PI Master or Sla | ve Switching | Characteristics (| CLKSTP - 10h | $CIKXP = 0)^{\dagger}$ |
|-------------|--------------|------------------|--------------|-------------------|--------------|--|
| Table 3-20. | INICOUP as U | FI WASLEI UI JIA | ve Switching | Characteristics | CLASIF - IUD | $, \mathbf{OLINAF} = 0 \mathbf{)}^{\cdot}$ |

| PARAMETER | | | 5416-100 | | | | |
|-------------------------------|---|--------|----------|---------------------|-----------------------|------|--|
| | | | TER§ | SL | AVE | UNIT | |
| | | MIN | MAX | MIN | MAX | | |
| t _{h(BCKXL-BFXL)} | Hold time, BFSX low after BCLKX low [¶] | T - 3* | T + 4 | | | ns | |
| t _{d(BFXL-BCKXH)} | Delay time, BFSX low to BCLKX high# | C - 4* | C + 3* | | | ns | |
| t _{d(BCKXH-BDXV)} | Delay time, BCLKX high to BDX valid | - 4* | 5 | 6P + 2*‡ | 10P + 17 [‡] | ns | |
| t _{dis(BCKXL-BDXHZ)} | Disable time, BDX high impedance following last data bit from BCLKX low | C - 2* | C + 3* | | | ns | |
| t _{dis(BFXH-BDXHZ)} | Disable time, BDX high impedance following last data bit from BFSX high | | | 2P- 4* [‡] | 6P + 17* [‡] | ns | |
| t _{d(BFXL-BDXV)} | Delay time, BFSX low to BDX valid | | | 4P+ 2* [‡] | 8P + 17* [‡] | ns | |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

[‡] P = 1 / (2 * processor clock)

§ T = BCLKX period = (1 + CLKGDV) * 2P

C = BCLKX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) * 2P when CLKGDV is even

¹ FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally.

CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP

CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP

[#] BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).






Table 5-27. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 0)^{\dagger}

| | | | 5416-100 | | | |
|-----------------------------|--|-----|----------|------------|-----|------|
| | | MA | STER | SLAVE | | UNIT |
| | | MIN | MAX | MIN | MAX | |
| t _{su(BDRV-BCKXL)} | Setup time, BDR valid before BCLKX low | 12 | | 2.2 - 6P*‡ | | ns |
| t _{h(BCKXH-BDRV)} | Hold time, BDR valid after BCLKX high | 4 | | 5 + 12P*‡ | | ns |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

[‡] P = 1 / (2 * processor clock)

Table 5-28. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 0)[†]

| | PARAMETER | | 5 | 416-100 | | |
|-------------------------------|---|--------|--------|----------------------|------------------------|------|
| | | | TER§ | SLAVE | | UNIT |
| | | | MAX | MIN | MAX | |
| t _{h(BCKXL-BFXL)} | Hold time, BFSX low after BCLKX low [¶] | C -3* | C + 4 | | | ns |
| t _{d(BFXL-BCKXH)} | Delay time, BFSX low to BCLKX high# | T - 4* | T + 3* | | | ns |
| t _{d(BCKXL-BDXV)} | Delay time, BCLKX low to BDX valid | - 4* | 5 | 6P + 2*‡ | 10P + 17 [‡] | ns |
| t _{dis(BCKXL-BDXHZ)} | Disable time, BDX high impedance following last data bit from BCLKX low | - 2* | 4* | 6P - 4* [‡] | 10P + 17* [‡] | ns |
| t _{d(BFXL-BDXV)} | Delay time, BFSX low to BDX valid | D - 2* | D + 4* | 4P + 2* [‡] | 8P + 17* [‡] | ns |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

P = 1 / (2 * processor clock)

§ T = BCLKX period = (1 + CLKGDV) * 2P

C = BCLKX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) * 2P when CLKGDV is even


D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) * 2P when CLKGDV is even

¹ FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally.

CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP

CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP

BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).





| Table 5-29. | McBSP as SPI Maste | r or Slave Timing Require | ments (CLKSTP = 10b, CLKXP = 1) ^{\dagger} |
|-------------|--------------------|---------------------------|---|
| | | | |

| | | | 5416-100 | | | | |
|-----------------------------|---|-----|--------------|-----------|-----|------|--|
| | | MAS | MASTER SLAVE | | E | UNIT | |
| | | MIN | MAX | MIN | MAX | | |
| t _{su(BDRV-BCKXH)} | Setup time, BDR valid before BCLKX high | 12 | | 2 - 6P*‡ | | ns | |
| t _{h(BCKXH-BDRV)} | Hold time, BDR valid after BCLKX high | 4 | | 5 + 12P*‡ | | ns | |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

[‡] P = 1 / (2 * processor clock)

Table 5-30. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = $1)^{\dagger}$

| | PARAMETER | | 5 | 416-100 | UNIT | |
|-------------------------------|--|--------|--------|----------------------|-----------------------|----|
| | | | TER§ | SLAVE | | |
| | | MIN | MAX | MIN | MAX | |
| t _{h(BCKXH-BFXL)} | Hold time, BFSX low after BCLKX high [¶] | T - 3* | T + 4 | | | ns |
| t _{d(BFXL-BCKXL)} | Delay time, BFSX low to BCLKX low [#] | D - 4* | D + 3* | | | ns |
| t _{d(BCKXL-BDXV)} | Delay time, BCLKX low to BDX valid | - 4* | 5 | 6P + 2* [‡] | 10P + 17 [‡] | ns |
| t _{dis(BCKXH-BDXHZ)} | Disable time, BDX high impedance following last data bit from BCLKX high | D - 2* | D + 3* | | | ns |
| t _{dis(BFXH-BDXHZ)} | Disable time, BDX high impedance following last data bit from BFSX high | | | 2P - 4*‡ | 6P + 17* [‡] | ns |
| t _{d(BFXL-BDXV)} | Delay time, BFSX low to BDX valid | | | 4P + 2* [‡] | 8P + 17* [‡] | ns |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

[‡] P = 1 / (2 * processor clock)

§ T = BCLKX period = (1 + CLKGDV) * 2P


D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) * 2P when CLKGDV is even

¹ FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally.

CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP

CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP

[#] BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).





| | U | • | | • | | • |
|-----------------------------|--|-----|------------|-----------|------|----|
| | | | 54 | 5416-100 | | |
| | | MAS | STER SLAVE | | UNIT | |
| | | MIN | MAX | MIN | MAX | |
| t _{su(BDRV-BCKXL)} | Setup time, BDR valid before BCLKX low | 12 | | 2 - 6P*‡ | | ns |
| t _{h(BCKXL-BDRV)} | Hold time, BDR valid after BCLKX low | 4 | | 5 + 12P*‡ | | ns |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

P = 1 / (2 * processor clock)

| | PARAMETER | | 5416-100 | | | | |
|-------------------------------|--|--------|----------|----------|------------------------|----|--|
| | | | TER§ | SI | UNIT | | |
| | | | MAX | MIN | MAX | | |
| t _{h(BCKXH-BFXL)} | Hold time, BFSX low after BCLKX high [¶] | D - 3* | D + 4 | | | ns | |
| t _{d(BFXL-BCKXL)} | Delay time, BFSX low to BCLKX low [#] | T - 4* | T + 3* | | | ns | |
| t _{d(BCKXH-BDXV)} | Delay time, BCLKX high to BDX valid | - 4* | 5 | 6P + 2*‡ | 10P + 17 [‡] | ns | |
| t _{dis(BCKXH-BDXHZ)} | Disable time, BDX high impedance following last data bit from BCLKX high | - 2* | 4* | 6P - 4*‡ | 10P + 17* [‡] | ns | |
| t _{d(BFXL-BDXV)} | Delay time, BFSX low to BDX valid | C - 2* | C + 4* | 4P + 2*‡ | 8P + 17* [‡] | ns | |

* Not production tested.

[†] For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

 ‡ P = 1 / (2 * processor clock)

§ T = BCLKX period = (1 + CLKGDV) * 2P

C = BCLKX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) * 2P when CLKGDV is even


D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) * 2P when CLKGDV is even

¹ FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally.

CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP

 $\mathsf{CLKXM}=\mathsf{CLKRM}=\mathsf{FSXM}=\mathsf{FSRM}=\mathsf{0} \text{ for slave McBSP}$

BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).





5.15 Host-Port Interface Timing

5.15.1 HPI8 Mode

Table 5–33 and Table 5–34 assume testing over recommended operating conditions and P = 1 / (2 * processor clock) (see Figure 5–28 through Figure 5–31). In the following tables, DS refers to the logical OR of $\overline{\text{HCS}}$, $\overline{\text{HDS1}}$, and $\overline{\text{HDS2}}$. HD refers to any of the HPI data bus pins (HD0, HD1, HD2, etc.). HAD stands for HCNTL0, HCNTL1, and HR/W.

| | | 5416-100 | | |
|---------------------------|---|--|-----|------|
| | | MIN MA 6 3 8* 13* 7* 3 2 2 | MAX | UNIT |
| t _{su(HBV-DSL)} | Setup time, HBIL valid before DS low (when $\overline{\text{HAS}}$ is not used), or HBIL valid before $\overline{\text{HAS}}$ low | 6 | | ns |
| t _{h(DSL-HBV)} | Hold time, HBIL valid after DS low (when $\overline{\text{HAS}}$ is not used), or HBIL valid after $\overline{\text{HAS}}$ low | 3 | | ns |
| t _{su(HSL-DSL)} | Setup time, HAS low before DS low | 8* | | ns |
| t _{w(DSL)} | Pulse duration, DS low | 13* | | ns |
| t _{w(DSH)} | Pulse duration, DS high | 7* | | ns |
| t _{su(HDV-DSH)} | Setup time, HD valid before DS high, HPI write | 3 | | ns |
| t _{h(DSH-HDV)} W | Hold time, HD valid after DS high, HPI write | 2 | | ns |
| t _{su(GPIO-COH)} | Setup time, HDx input valid before CLKOUT high, HDx configured as general-purpose input | 6* | | ns |
| t _{h(GPIO-COH)} | Hold time, HDx input valid before CLKOUT high, HDx configured as general-purpose input | 0* | | ns |


| Table 5-33 | HPI8 Mode | Timing | Requirements |
|------------|-----------|--------|--------------|
|------------|-----------|--------|--------------|

| | | | 54 | 16-100 | |
|---------------------------|---|---|-----|------------------------------|----------------------------|
| | PAR | AMETER | MIN | MAX | UNIT |
| t _{en(DSL-HD)} | Enable time, HD driven from DS | S low | 0* | 10* | ns |
| | | Case 1a: Memory accesses when DMAC is active in 32-bit mode and $t_{w(DSH)} < 36 P^{\dagger}$ | 3 | 36P+10-t _{w(DSH)} * | |
| t _{d(DSL-HDV1)} | | Case 1b: Memory accesses when DMAC is active in 32-bit mode and $t_{w(DSH)} \ge 36 P^{\dagger}$ | | 10* | |
| | Delay time, DS low to HD | Case 1c: Memory accesses when DMAC is active in 16-bit mode and $t_{w(DSH)} < I8P^{\dagger}$ | 1 | I8P+10-t _{w(DSH)} * | ns ns ns ns ns |
| | valid for first byte of an HPI read | Case 1d: Memory accesses when DMAC is active in 16-bit mode and $t_{w(DSH)} \ge 18 P^{\dagger}$ | | 10* | ns |
| | | Case 2a: Memory accesses when DMAC is inactive and $t_{w(DSH)} < 10 P^{\dagger}$ | 1 | I0P+10-t _{w(DSH)} * | |
| | | Case 2b: Memory accesses when DMAC is inactive and $t_{w(DSH)} \ge 10 P^{\dagger}$ | | 10* 10* | |
| | | Case 3: Register accesses | | | |
| t _{d(DSL-HDV2)} | Delay time, DS low to HD valid | for second byte of an HPI read | | 10* | ns |
| t _{h(DSH-HDV)} R | Hold time, HD valid after DS hig | h, for a HPI read | 0* | | ns |
| t _{v(HYH-HDV)} | Valid time, HD valid after HRDY | high | | 2* | ns |
| t _{d(DSH-HYL)} | Delay time, DS high to HRDY lo | w [‡] | | 8* | ns |
| | | Case 1a: Memory accesses when DMAC is active in 16-bit mode † | | 18P+6* | |
| t _{d(DSH-HYH)} | Delay time, DS high to HRDY high [‡] | Case 1b: Memory accesses when DMAC is active in 32-bit mode † | | 36P+6* | ns |
| | U | Case 2: Memory accesses when DMAC is inactive [†] | | 10P+6* | |
| | | Case 3: Write accesses to HPIC register§ | | 6P+6* | |
| t _{d(HCS-HRDY)} | Delay time, HCS low/high to HF | IDY low/high | | 6* | ns |
| t _{d(COH-HYH)} | Delay time, CLKOUT high to HF | RDY high | | 9 | ns |
| t _{d(COH-HTX)} | Delay time, CLKOUT high to H | NT change | | 6 | ns |
| t _d (COH-GPIO) | Delay time, CLKOUT high to general-purpose output | o HDx output change. HDx is configured as a | | 5* | ns |

* Not production tested.

[†] DMAC stands for direct memory access controller (DMAC). The HPI8 shares the internal DMA bus with the DMAC, thus HPI8 access times are affected by DMAC activity.

 [‡] The HRDY output is always high when the HCS input is high, regardless of DS timings.
 § This timing applies when writing a one to the DSPINT bit or HINT bit of the HPIC register. All other writes to the HPIC occur asynchronously, and do not cause HRDY to be deasserted.



[‡] When HAS is not used (HAS always high)






Figure 5-31. GPIOx[†] Timings

5.15.2 HPI16 Mode

Table 5–35 and Table 5–36 assume testing over recommended operating conditions and P = 1 / (2 * processor clock) (see Figure 5–32 through Figure 5–34). In the following tables, DS refers to the logical OR of HCS, HDS1, and HDS2, and HD refers to any of the HPI data bus pins (HD0, HD1, HD2, etc.). These timings are shown assuming that HDS is the signal controlling the transfer. See the *TMS320C54x DSP Reference Set*, *Volume 5: Enhanced Peripherals* (literature number SPRU302) for addition information.

| | | | | 5416-1 | UNIT | | |
|----------------------------|---|---|--------|-----------|------|----|--|
| | | | | MIN | | | |
| t _{su(HBV-DSL)} | Setup time, HR/W valid before I | 6 | | ns | | | |
| t _{h(DSL-HBV)} | Hold time, HR/ \overline{W} valid after DS t | 5 | | ns | | | |
| t _{su(HAV-DSH)} | Setup time, address valid before | 5* | | ns | | | |
| t _{su(HAV-DSL)} | Setup time, address valid before | -(4P - 6)* | | ns | | | |
| t _{h(DSH-HAV)} | Hold time, address valid after D | 1* | | ns | | | |
| t _{w(DSL)} | Pulse duration, DS low | 30* | | ns | | | |
| t _{w(DSH)} | Pulse duration, DS high | 10* | | ns | | | |
| t _{c(DSH-DSH)} | | | Reads | 10P + 30* | | | |
| | Cycle time, DS rising edge to next DS rising edge | Memory accesses with no DMA activity. | Writes | 10P + 10* | | | |
| | | | Reads | 16P + 30* | | ns | |
| | | Memory accesses with 16-bit DMA activity. | Writes | 16P + 10* | | | |
| | | | Reads | 24P + 30* | | | |
| | | Memory accesses with 32-bit DMA activity. | Writes | 24P + 10* | | | |
| t _{su(HDV-DSH)} W | Setup time, HD valid before DS | 8 | | ns | | | |
| t _{h(DSH-HDV)} W | Hold time, HD valid after DS risi | 2 | | ns | | | |

| Table 5-35 | HPI16 Mode | Timing | Requirements |
|------------|------------|--------|--------------|
|------------|------------|--------|--------------|

| | | PARAMETER | | | | | |
|---------------------------|--|--|-----|-------------------------------------|----|--|--|
| | | MIN | MAX | UNIT | | | |
| t _{d(DSL-HDD)} | Delay time, DS | low to HD driven | 0* | 10* | | | |
| t _d (DSL-HDV1) | | Case 1a: Memory accesses initiated immediately following a write when DMAC is active in 32-bit mode and $t_{w(DSH)}\text{was}$ < 26P | | 48P + 20 - t _{w(DSH)} * | 1 | | |
| | | Case 1b: Memory access not immediately following a write when DMAC is active in 32-bit mode | | 24P + 20* | 1 | | |
| | Delay time, DS low to HD valid for first word of an HPI read | Case 1c: Memory accesses initiated immediately following a write when DMAC is active in 16-bit mode and $t_{w(DSH)}was$ < 18P | | 32P + 20 - t _{w(DSH)} * | ns | | |
| | | Case 1d: Memory accesses not immediately following a write when DMAC is active in 16-bit mode | | 16P + 20* |] | | |
| | | Case 2a: Memory accesses initiated immediately following a write when DMAC is inactive and $t_{w(DSH)}$ was < 10P | | 20P + 20 - t _{w(DSH)} * | | | |
| | | Case 2b: Memory accesses not immediately following a write when DMAC is inactive | | 10P + 20* | | | |
| t _{d(DSH-HYH)} | Delay time, | Memory writes when no DMA is active | | 10P + 5* | ns | | |
| | DS high to | Memory writes with one or more 16-bit DMA channels active | | 16P + 5* | | | |
| | HRDY high | Memory writes with one or more 32-bit DMA channels active | | 24P + 5* | | | |
| t _{v(HYH-HDV)} | Valid time, HD v | valid after HRDY high | | 7* | ns | | |
| t _{h(DSH-HDV)R} | Hold time, HD v | alid after DS rising edge, read | 1* | 6* | ns | | |
| t _{d(COH-HYH)} | Delay time, CL | OUT rising edge to HRDY high | | 5 | ns | | |
| t _{d(DSL-HYL)} | Delay time, DS | low to HRDY low | | 12* | ns | | |
| t _{d(DSH-HYL)} | Delay time, DS | high to HRDY low | | 12* | ns | | |





Figure 5-32. Nonmultiplexed Read Timings







Figure 5-34. HRDY Relative to CLKOUT

6 Mechanical Data

6.1 Ceramic Quad Flatpack Mechanical Data HFG (S-CQFP-F164)

CERAMIC QUAD FLATPACK WITH NCTB



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. Ceramic quad flatpack with flat leads brazed to non-conductive tie bar carrier
- D. This package is hermetically sealed with a metal lid.
- E. The leads are gold-plated and can be solder-dipped.
- F. Leads not shown for clarity purposes
- G. Falls within JEDEC MO-113AA (REV D)

Figure 6-1. SMJ320VC5416 164-Pin Ceramic Quad Flatpack (HFG)



PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|--------------------|---------------|--------------|--------------------|------|----------------|-----------------|--------------------------------------|----------------------|--------------|---|---------|
| SMJ320VC5416HFGW10 | OBSOLETE | CFP | HFG | 164 | | TBD | Call TI | Call TI | -55 to 115 | 5962-0153001QX A SMJ320VC5416H FGW10 | |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



OTHER QUALIFIED VERSIONS OF SMJ320VC5416 :


• Catalog : TMS320VC5416

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

HFG (S-CQFP-F164)

CERAMIC QUAD FLATPACK WITH NCTB



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. Ceramic quad flatpack with flat leads brazed to non-conductive tie bar carrier.
- D. This package is hermetically sealed with a metal lid.
- E. The leads are gold plated and can be solderdipped.
- F. Leads not shown for clarity purposes.
- G. Falls within JEDEC MO-113AA (REV D)



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated