

## SN74LV174A Hex D-Type Flip-Flops With Clear

### 1 Features

- $V_{CC}$  operation of 2 V to 5.5
- Maximum  $t_{pd}$  of 7.5 ns at 5 V
- Typical  $V_{OLP}$  (output ground bounce) < 0.8 V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- Typical  $V_{OHV}$  (output  $V_{OH}$  undershoot) > 2.3 V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- $I_{off}$  supports partial-power-down mode operation
- Supports mixed-mode voltage operation on all ports
- Latch-up performance exceeds 250 mA per JESD 17

### 2 Applications

- [Output expansion](#)
- [LED matrix control](#)
- [7-segment display control](#)


### 3 Description

The 'LV174A devices are hex D-type flip-flops designed for 2 V to 5.5 V  $V_{CC}$  operation.

#### Package Information<sup>(1)</sup>

| PART NUMBER | PACKAGE         | BODY SIZE (NOM)    |
|-------------|-----------------|--------------------|
| SN74LV174A  | DGV (TVSOP, 16) | 4.00 mm × 3.50 mm  |
|             | PW (TSSOP, 16)  | 5.00 mm × 4.40 mm  |
|             | NS (SO, 16)     | 10.20 mm × 5.30 mm |
|             | D (SOIC, 16)    | 9.00 mm × 3.90 mm  |

- (1) For all available packages, see the orderable addendum at the end of the data sheet.



**Logic Diagram (Positive Logic)**



## Table of Contents

|  |          |  |           |
|--|----------|--|-----------|
| <b>1 Features</b> .....  | <b>1</b> | <b>7 Parameter Measurement Information</b> .....                 | <b>10</b> |
| <b>2 Applications</b> .....  | <b>1</b> | <b>8 Detailed Description</b> .....                              | <b>11</b> |
| <b>3 Description</b> .....   | <b>1</b> | 8.1 Overview.....  | 11        |
| <b>4 Revision History</b> .....  | <b>2</b> | 8.2 Functional Block Diagram.....                                | 11        |
| <b>5 Pin Configuration and Functions</b> .....                                 | <b>3</b> | 8.3 Feature Description.....                                     | 12        |
| <b>6 Specifications</b> .....  | <b>4</b> | 8.4 Device Functional Modes.....                                 | 13        |
| 6.1 Absolute Maximum Ratings.....  | 4        | <b>9 Application and Implementation</b> .....                    | <b>14</b> |
| 6.2 ESD Ratings.....   | 4        | 9.1 Application Information.....                                 | 14        |
| 6.3 Recommended Operating Conditions.....                                      | 5        | 9.2 Typical Application.....                                     | 14        |
| 6.4 Thermal Information.....   | 5        | 9.3 Power Supply Recommendations.....                            | 14        |
| 6.5 Electrical Characteristics.....  | 6        | 9.4 Layout.....  | 14        |
| 6.6 Timing Requirements, $V_{CC} = 2.5\text{ V} \pm 0.2\text{ V}$ .....        | 6        | <b>10 Device and Documentation Support</b> .....                 | <b>16</b> |
| 6.7 Timing Requirements, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ .....        | 7        | 10.1 Documentation Support.....                                  | 16        |
| 6.8 Timing Requirements, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....          | 7        | 10.2 Receiving Notification of Documentation Updates..           | 16        |
| 6.9 Switching Characteristics, $V_{CC} = 2.5\text{ V} \pm 0.2\text{ V}$ .....  | 8        | 10.3 Support Resources.....                                      | 16        |
| 6.10 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ..... | 8        | 10.4 Trademarks.....   | 16        |
| 6.11 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....   | 8        | 10.5 Electrostatic Discharge Caution.....                        | 16        |
| 6.12 Noise Characteristics.....  | 8        | 10.6 Glossary.....   | 16        |
| 6.13 Operating Characteristics.....  | 9        | <b>11 Mechanical, Packaging, and Orderable Information</b> ..... | <b>16</b> |
| 6.14 Typical Characteristics.....  | 9        |  |           |

## 4 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision H (December 2022) to Revision I (March 2023)</b>  | <b>Page</b> |
|--|-------------|
| • Removed references to DB package, removed pinout image of BQB or RGY package, and updated structural layout of document to current standard..... | 1           |
| • Updated thermal values for D package from R $\theta$ JA = 73 to 107.7, all values in °C/W.....   | 5           |

---

| <b>Changes from Revision G (April 1998) to Revision H (December 2022)</b>                  | <b>Page</b> |
|--|-------------|
| • Updated the format of tables, figures, and cross-references throughout the document..... | 1           |

## 5 Pin Configuration and Functions



**Figure 5-1. D, DW, or PW Package,  
16-Pin SOIC, SOP or TSSOP  
(Top View)**

**Table 5-1. Pin Functions**

| PIN             |     | TYPE | DESCRIPTION |
|-----------------|-----|------|-------------|
| NAME            | NO. |      |             |
| CLR             | 1   | I    | Clear Pin   |
| 1Q              | 2   | O    | 1Q Output   |
| 1D              | 3   | I    | 1D Input    |
| 2D              | 4   | I    | 2D Input    |
| 2Q              | 5   | O    | 2Q Output   |
| 3D              | 6   | I    | 3D Input    |
| 3Q              | 7   | O    | 3Q Output   |
| GND             | 8   | —    | Ground Pin  |
| CLK             | 9   | I    | Clock Pin   |
| 4Q              | 10  | O    | 4Q Output   |
| 4D              | 11  | I    | 4D Input    |
| 5Q              | 12  | O    | 5Q Output   |
| 5D              | 13  | I    | 5D Input    |
| 6D              | 14  | I    | 6D Input    |
| 6Q              | 15  | O    | 6Q Output   |
| V <sub>CC</sub> | 16  | P    | Power Pin   |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |   |                                       | MIN  | MAX                   | UNIT |
|------------------|---|---------------------------------------|------|-----------------------|------|
| V <sub>CC</sub>  | Supply voltage range  |                                       | -0.5 | 7                     | V    |
| V <sub>I</sub>   | Input voltage range <sup>(2)</sup>  |                                       | -0.5 | 7                     | V    |
| V <sub>O</sub>   | Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup> |                                       | -0.5 | 7                     | V    |
| V <sub>O</sub>   | Output voltage range applied in the high or low state <sup>(2) (3)</sup>                    |                                       | -0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>  | Input clamp current   | V <sub>I</sub> < 0                    |      | -20                   | mA   |
| I <sub>OK</sub>  | Output clamp current  | V <sub>O</sub> < 0                    |      | -50                   | mA   |
| I <sub>O</sub>   | Continuous output current   | V <sub>O</sub> = 0 to V <sub>CC</sub> |      | ±25                   | mA   |
|                  | Continuous current through V <sub>CC</sub> or GND   |                                       |      | ±50                   | mA   |
| T <sub>stg</sub> | Storage temperature range   |                                       | -65  | 150                   | °CW  |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output negative-voltage ratings may be exceeded if the input and output clamp current ratings are observed.
- (3) This value is limited to 5.5 V maximum.

### 6.2 ESD Ratings

|   |   | VALUE | UNIT |
|---|---|-------|------|
| V <sub>(ESD)</sub>  | Electrostatic discharge   |       |      |
|   | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup> | ±2000 | V    |
|   | Machine Model (MM), per JEDEC specification                       | ±200  |      |
| Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 <sup>(2)</sup> | ±1000   |       |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                 |                                    | MIN                              | MAX                   | UNIT            |   |
|-----------------|------------------------------------|----------------------------------|-----------------------|-----------------|---|
| V <sub>CC</sub> | Supply voltage                     | 2                                | 5.5                   | V               |   |
| V <sub>IH</sub> | High-level input voltage           | V <sub>CC</sub> = 2 V            | 1.5                   | V               |   |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V | V <sub>CC</sub> × 0.7 |                 |   |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V   | V <sub>CC</sub> × 0.7 |                 |   |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V | V <sub>CC</sub> × 0.7 |                 |   |
| V <sub>IL</sub> | Low-level input voltage            | V <sub>CC</sub> = 2 V            | 0.5                   | V               |   |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V | V <sub>CC</sub> × 0.3 |                 |   |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V   | V <sub>CC</sub> × 0.3 |                 |   |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V | V <sub>CC</sub> × 0.3 |                 |   |
| V <sub>I</sub>  | Input voltage                      | 0                                | 5.5                   | V               |   |
| V <sub>O</sub>  | Output voltage                     | High or low state                | 0                     | V <sub>CC</sub> | V |
| I <sub>OH</sub> | High-level output current          | V <sub>CC</sub> = 2 V            | -50                   | μA              |   |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V | -2                    | mA              |   |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V   | -6                    |                 |   |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V | -12                   |                 |   |
| I <sub>OL</sub> | Low-level output current           | V <sub>CC</sub> = 2 V            | 50                    | μA              |   |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V | 2                     | mA              |   |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V   | 6                     |                 |   |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V | 12                    |                 |   |
| Δt/Δv           | Input transition rise or fall rate | V <sub>CC</sub> = 2.3 V to 2.7 V | 200                   | ns/V            |   |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V   | 100                   |                 |   |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V | 20                    |                 |   |
| T <sub>A</sub>  | Operating free-air temperature     | -40                              | 85                    | °C              |   |

(1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, [Implications of Slow or Floating CMOS Inputs](#).

### 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |  | SN74LV174A |     |    |     | UNIT |
|-------------------------------|--|------------|-----|----|-----|------|
|                               |  | D          | DGV | NS | PW  |      |
|                               |  | 16 PINS    |     |    |     |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance | 107.7      | 120 | 64 | 108 | °C/W |

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report ([SPRA953](#)).

## 6.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER        | TEST CONDITIONS   | V <sub>CC</sub> | SN74LV174A            |     |     | UNIT |
|------------------|---|-----------------|-----------------------|-----|-----|------|
|                  |   |                 | MIN                   | TYP | MAX |      |
| V <sub>OH</sub>  | I <sub>OH</sub> = –50 μA                                    | 2 V to 5.5 V    | V <sub>CC</sub> – 0.1 |     |     | V    |
|                  | I <sub>OH</sub> = –2 mA                                     | 2.3 V           | 2                     |     |     |      |
|                  | I <sub>OH</sub> = –6 mA                                     | 3 V             | 2.48                  |     |     |      |
|                  | I <sub>OH</sub> = –12 mA                                    | 3 V             | 3.8                   |     |     |      |
|                  |   | 4.5 V           | 0.1                   |     |     |      |
| V <sub>OL</sub>  | I <sub>OL</sub> = 50 μA                                     | 2 V to 5.5 V    | 0.1                   |     |     | V    |
|                  | I <sub>OL</sub> = 2 mA                                      | 2.3 V           | 0.4                   |     |     |      |
|                  | I <sub>OL</sub> = 6 mA                                      | 3 V             | 0.44                  |     |     |      |
|                  | I <sub>OL</sub> = 12 mA                                     | 4.5             | 0.55                  |     |     |      |
| I <sub>I</sub>   | V <sub>I</sub> = 5.5 V or GND                               | 0 V to 5.5 V    | ±1                    |     |     | μA   |
| I <sub>CC</sub>  | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0 | 5.5 V           | 20                    |     |     | μA   |
| I <sub>off</sub> | V <sub>I</sub> or V <sub>O</sub> = 0 to 5.5 V               | 0 V             | 5                     |     |     | μA   |
| C <sub>i</sub>   | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 3.3 V           | 1.7                   |     |     | pF   |

## 6.6 Timing Requirements, V<sub>CC</sub> = 2.5 V ± 0.2 V

over recommended operating free-air temperature range (unless otherwise noted)

|                 |                           |                 | T <sub>A</sub> = 25°C |     | SN74LV174A |     | UNIT |
|-----------------|---------------------------|-----------------|-----------------------|-----|------------|-----|------|
|                 |                           |                 | MIN                   | MAX | MIN        | MAX |      |
| t <sub>w</sub>  | Pulse duration            | CLR low         | 6                     |     | 6.5        |     | ns   |
|                 |                           | CLK high or low | 7                     |     | 7          |     |      |
| t <sub>su</sub> | Setup time before CLK↑    | Data            | 8.5                   |     | 9.5        |     | ns   |
|                 |                           | CLR inactive    | 4                     |     | 4          |     |      |
| t <sub>h</sub>  | Hold time data after CLK↑ | – 0.5           |                       | 0   |            | ns  |      |

### 6.7 Timing Requirements, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$

over recommended operating free-air temperature range (unless otherwise noted)

|          |                                     |                 | $T_A = 25^\circ\text{C}$ |     | SN74LV174A |     | UNIT |
|----------|-------------------------------------|-----------------|--------------------------|-----|------------|-----|------|
|          |                                     |                 | MIN                      | MAX | MIN        | MAX |      |
| $t_w$    | Pulse duration                      | CLR low         | 5                        |     | 5          |     | ns   |
|          |                                     | CLK high or low | 5                        |     | 5          |     |      |
| $t_{su}$ | Setup time before CLK $\uparrow$    | Data            | 5                        |     | 6          |     | ns   |
|          |                                     | CLR inactive    | 3                        |     | 3          |     |      |
| $t_h$    | Hold time data after CLK $\uparrow$ |                 | 0                        |     | 0          |     | ns   |

### 6.8 Timing Requirements, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$

over recommended operating free-air temperature range (unless otherwise noted)

|          |                                     |                 | $T_A = 25^\circ\text{C}$ |     | SN74LV174A |     | UNIT |
|----------|-------------------------------------|-----------------|--------------------------|-----|------------|-----|------|
|          |                                     |                 | MIN                      | MAX | MIN        | MAX |      |
| $t_w$    | Pulse duration                      | CLR low         | 5                        |     | 5          |     | ns   |
|          |                                     | CLK high or low | 5                        |     | 5          |     | ns   |
| $t_{su}$ | Setup time before CLK $\uparrow$    | Data            | 4.5                      |     | 4.5        |     | ns   |
|          |                                     | CLR inactive    | 2.5                      |     | 2.5        |     | ns   |
| $t_h$    | Hold time data after CLK $\uparrow$ |                 | 0.5                      |     | 0.5        |     | ns   |

## 6.9 Switching Characteristics, $V_{CC} = 2.5\text{ V} \pm 0.2\text{ V}$

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER          | FROM (INPUT)            | TO (OUTPUT) | LOAD CAPACITANCE     | $T_A = 25^\circ\text{C}$ |      |      | SN74LV174A |      | UNIT |
|--------------------|-------------------------|-------------|----------------------|--------------------------|------|------|------------|------|------|
|                    |                         |             |                      | MIN                      | TYP  | MAX  | MIN        | MAX  |      |
| $f_{\text{max}}$   |                         |             | $C_L = 15\text{ pF}$ | 55                       | 115  |      | 50         |      | MHz  |
|                    |                         |             | $C_L = 50\text{ pF}$ | 45                       | 90   |      | 40         |      |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 15\text{ pF}$ |                          | 6.3  | 17.3 | 1          | 19.5 | ns   |
|                    | CLK                     |             |                      |                          | 8.4  | 17.1 | 1          | 19   |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 50\text{ pF}$ |                          | 8.2  | 21.9 | 1          | 23.5 | ns   |
|                    | CLK                     |             |                      |                          | 10.8 | 20.6 | 1          | 23   |      |
| $t_{\text{sk(o)}}$ |                         |             |                      |                          |      | 2    |            | 2    |      |

## 6.10 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER          | FROM (INPUT)            | TO (OUTPUT) | LOAD CAPACITANCE     | $T_A = 25^\circ\text{C}$ |     |      | SN74LV174A |      | UNIT |
|--------------------|-------------------------|-------------|----------------------|--------------------------|-----|------|------------|------|------|
|                    |                         |             |                      | MIN                      | TYP | MAX  | MIN        | MAX  |      |
| $f_{\text{max}}$   |                         |             | $C_L = 15\text{ pF}$ | 95                       | 170 |      | 80         |      | MHz  |
|                    |                         |             | $C_L = 50\text{ pF}$ | 55                       | 130 |      | 50         |      |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 15\text{ pF}$ |                          | 4.5 | 11.4 | 1          | 13.5 | ns   |
|                    | CLK                     |             |                      |                          | 5.8 | 11   | 1          | 13   |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 50\text{ pF}$ |                          | 6   | 14.9 | 1          | 17   | ns   |
|                    | CLK                     |             |                      |                          | 7.5 | 14.5 | 1          | 16.5 |      |
| $t_{\text{sk(o)}}$ |                         |             |                      |                          |     | 1.5  |            | 1.5  |      |

## 6.11 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER          | FROM (INPUT)            | TO (OUTPUT) | LOAD CAPACITANCE     | $T_A = 25^\circ\text{C}$ |     |     | SN74LV174A |      | UNIT |
|--------------------|-------------------------|-------------|----------------------|--------------------------|-----|-----|------------|------|------|
|                    |                         |             |                      | MIN                      | TYP | MAX | MIN        | MAX  |      |
| $f_{\text{max}}$   |                         |             | $C_L = 15\text{ pF}$ | 130                      | 240 |     | 110        | 5    | MHz  |
|                    |                         |             | $C_L = 50\text{ pF}$ | 90                       | 180 |     | 80         |      |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 15\text{ pF}$ |                          | 3   | 7.6 | 1          | 9    | ns   |
|                    | CLK                     |             |                      |                          | 4.1 | 7.2 | 1          | 8.5  |      |
| $t_{\text{pd}}$    | $\overline{\text{CLR}}$ | Q           | $C_L = 50\text{ pF}$ |                          | 4.2 | 9.6 | 1          | 11   | ns   |
|                    | CLK                     |             |                      |                          | 5.5 | 9.2 | 1          | 10.5 |      |
| $t_{\text{sk(o)}}$ |                         |             |                      |                          |     | 1   |            | 1    |      |

## 6.12 Noise Characteristics

$V_{CC} = 3.3\text{ V}$ ,  $C_L = 50\text{ pF}$ ,  $T_A = 25^\circ\text{C}$ <sup>(1)</sup>

| PARAMETER          |   | SN74LV174A |      |      | UNIT |
|--------------------|---|------------|------|------|------|
|                    |   | MIN        | TYP  | MAX  |      |
| $V_{\text{OL(P)}}$ | Quiet output, maximum dynamic $V_{\text{OL}}$ |            | 0.34 | 0.8  | V    |
| $V_{\text{OL(V)}}$ | Quiet output, minimum dynamic $V_{\text{OL}}$ |            | -0.3 | -0.8 | V    |
| $V_{\text{OH(V)}}$ | Quiet output, minimum dynamic $V_{\text{OH}}$ |            | 3.02 |      | V    |
| $V_{\text{IH(D)}}$ | High-level dynamic input voltage              |            | 2.31 |      | V    |
| $V_{\text{IL(D)}}$ | Low-level dynamic input voltage               |            |      | 0.99 | V    |

(1) Characteristics are for surface-mount packages only.




### 6.13 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER |                               | TEST CONDITIONS      |                     | $V_{CC}$ | TYP  | UNIT |
|-----------|-------------------------------|----------------------|---------------------|----------|------|------|
| $C_{pd}$  | Power dissipation capacitance | $C_L = 50\text{ pF}$ | $f = 10\text{ MHz}$ | 3.3      | 14   | pF   |
|           |                               |                      |                     | 5        | 15.1 |      |

### 6.14 Typical Characteristics



**Figure 6-1. TPD vs V<sub>CC</sub>**

## 7 Parameter Measurement Information



- A.  $C_L$  includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1\text{ MHz}$ ,  $Z_O = 50\ \Omega$ ,  $t_r \leq 3\text{ ns}$ ,  $t_f \leq 3\text{ ns}$ .
- D. The outputs are measured one at a time, with one input transition per measurement.
- E.  $t_{PZL}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
- F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
- G.  $t_{PHL}$  and  $t_{PLH}$  are the same as  $t_{pd}$ .
- H. All parameters and waveforms are not applicable to all devices.

**Figure 7-1. Load Circuit and Voltage Waveforms**


## 8 Detailed Description

### 8.1 Overview

The 'LV174A devices are positive-edge-triggered flip-flops with a direct clear (CLR) input. Information at the data (D) inputs meeting the setup time requirements is transferred to the outputs on the positive-going edge of the clock pulse. Clock triggering occurs at a particular voltage level and is not directly related to the transition time of the positive-going edge of the clock pulse. When the clock (CLK) input is at either the high or low level, the D-input signal has no effect at the output.

### 8.2 Functional Block Diagram

**Figure 8-1. Logic Diagram (Positive Logic)**



**Figure 8-2.**

## 8.3 Feature Description

### 8.3.1 Balanced CMOS Push-Pull Outputs

This device includes balanced CMOS push-pull outputs. The term *balanced* indicates that the device can sink and source similar currents. The drive capability of this device may create fast edges into light loads, so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to overcurrent. The electrical and thermal limits defined in the *Absolute Maximum Ratings* must be followed at all times.

Unused push-pull CMOS outputs should be left disconnected.

### 8.3.2 Latching Logic

This device includes latching logic circuitry. Latching circuits commonly include D-type latches and D-type flip-flops, but include all logic circuits that act as volatile memory.

When the device is powered on, the state of each latch is unknown. There is no default state for each latch at start-up.

The output state of each latching logic circuit only remains stable as long as power is applied to the device within the supply voltage range specified in the *Recommended Operating Conditions* table.

### 8.3.3 Partial Power Down ( $I_{off}$ )

This device includes circuitry to disable all outputs when the supply pin is held at 0 V. When disabled, the outputs will neither source nor sink current, regardless of the input voltages applied. The amount of leakage current at each output is defined by the  $I_{off}$  specification in the *Electrical Characteristics* table.

### 8.3.4 Clamp Diode Structure

Figure 8-3 shows the inputs and outputs to this device have negative clamping diodes only.

**CAUTION**

Voltages beyond the values specified in the *Absolute Maximum Ratings* table can cause damage to the device. The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




Figure 8-3. Electrical Placement of Clamping Diodes for Each Input and Output

## 8.4 Device Functional Modes

**Table 8-1. Function Table**

| INPUTS <sup>(1)</sup> |     |   | OUTPUT |
|-----------------------|-----|---|--------|
| CLR                   | CLK | D | Q      |
| L                     | X   | X | L      |
| H                     | ↑   | H | H      |
| H                     | ↑   | L | L      |
| H                     | L   | X | Qo     |

(1) H = High Voltage Level, L = Low Voltage Level, X = Do not Care, Z = High Impedance

## 9 Application and Implementation

### Note


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 9.1 Application Information

The SN74LV174A is a low-drive CMOS device that can be used for a multitude of bus interface type applications where output ringing is a concern. The low drive and slow edge rates will minimize overshoot and undershoot on the outputs. The inputs are 5-V tolerant allowing for down translation to  $V_{CC}$ .

### 9.2 Typical Application

#### 9.2.1 Application Curves



**Figure 9-1. Simplified Functional Diagram Showing Clock Operation**

### 9.3 Power Supply Recommendations

The power supply can be any voltage between the min and max supply voltage rating located in [Section 6.3](#).

Each  $V_{CC}$  terminal should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, a 0.1  $\mu\text{F}$  capacitor is recommended. If there are multiple  $V_{CC}$  terminals then 0.01  $\mu\text{F}$  or 0.022  $\mu\text{F}$  capacitors are recommended for each power terminal. It is ok to parallel multiple bypass capacitors to reject different frequencies of noise. 0.1  $\mu\text{F}$  and 1.0  $\mu\text{F}$  capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for the best results.

### 9.4 Layout

#### 9.4.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of

digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or VCC, whichever makes more sense for the logic function or is more convenient.

## 10 Device and Documentation Support

### 10.1 Documentation Support

#### 10.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [CMOS Power Consumption and Cpd Calculation application report](#)
- Texas Instruments, [Thermal Characteristics of Standard Linear and Logic \(SLL\) Packages and Devices application report](#)

### 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 10.3 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 10.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 10.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

| Orderable Device | Status<br>(1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan<br>(2) | Lead finish/<br>Ball material<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|-----------------|--------------------------------------|----------------------|--------------|-------------------------|---------|
| SN74LV174AD      | OBSOLETE      | SOIC         | D               | 16   |             | TBD             | Call TI                              | Call TI              | -40 to 85    | LV174A                  |         |
| SN74LV174ADGVR   | ACTIVE        | TVSOP        | DGV             | 16   | 2000        | RoHS & Green    | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | LV174A                  | Samples |
| SN74LV174ADR     | ACTIVE        | SOIC         | D               | 16   | 2500        | RoHS & Green    | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | LV174A                  | Samples |
| SN74LV174ANSR    | ACTIVE        | SO           | NS              | 16   | 2000        | RoHS & Green    | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | 74LV174A                | Samples |
| SN74LV174APW     | OBSOLETE      | TSSOP        | PW              | 16   |             | TBD             | Call TI                              | Call TI              | -40 to 85    | LV174A                  |         |
| SN74LV174APWR    | ACTIVE        | TSSOP        | PW              | 16   | 2000        | RoHS & Green    | NIPDAU   SN                          | Level-1-260C-UNLIM   | -40 to 85    | LV174A                  | Samples |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LV174ADGVR | TVSOP        | DGV             | 16   | 2000 | 330.0              | 12.4               | 6.8     | 4.0     | 1.6     | 8.0     | 12.0   | Q1            |
| SN74LV174ADR   | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| SN74LV174ANSR  | SO           | NS              | 16   | 2000 | 330.0              | 16.4               | 8.2     | 10.5    | 2.5     | 12.0    | 16.0   | Q1            |
| SN74LV174APWR  | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| SN74LV174APWR  | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LV174ADGVR | TVSOP        | DGV             | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74LV174ADR   | SOIC         | D               | 16   | 2500 | 356.0       | 356.0      | 35.0        |
| SN74LV174ANSR  | SO           | NS              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74LV174APWR  | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74LV174APWR  | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |



# PACKAGE OUTLINE

## NS0016A

### SOP - 2.00 mm max height

SOP



4220735/A 12/2021

#### NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.

# EXAMPLE BOARD LAYOUT

NS0016A

SOP - 2.00 mm max height

SOP



4220735/A 12/2021

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

NS0016A

SOP - 2.00 mm max height

SOP



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:7X


4220735/A 12/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - $\triangle$  Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  - $\triangle$  Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AC.





NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4220204/A 02/2017

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220204/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

DGV (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE

24 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.  
 D. Falls within JEDEC: 24/48 Pins – MO-153  
 14/16/20/56 Pins – MO-194

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated