

FEATURES

- Qualified for Automotive Applications
- Low Power Consumption
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- Low Total Harmonic Distortion: 0.003% Typ
- High Input Impedance: JFET-Input Stage
- Latchup-Free Operation
- High Slew Rate: 13 V/µs Typ
- Common-Mode Input Voltage Range Includes V_{CC+}

DESCRIPTION/ORDERING INFORMATION

The TL082 JFET-input operational amplifier incorporates well-matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit. The device features high slew rates, low input bias and offset currents, and low offset-voltage temperature coefficient.

The I-suffix device is characterized for operation from -40° C to 85° C. The Q-suffix device is characterized for operation from -40° C to 125° C.

ORDERING INFORMATION⁽¹⁾


TJ	PACK	AGE ⁽²⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING		
–40°C to 85°C	SOIC – D	Reel of 2500	TL082IDRQ1	TL082I		
–40°C to 125°C	SOIC – D	Reel of 2500	TL082QDRQ1	TL082Q		

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.






SYMBOL (EACH AMPLIFIER)



SCHEMATIC (EACH AMPLIFIER)



A. Component values shown are nominal.



ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

			VALUE
V_{CC+}	Supply voltage, positive ⁽²⁾	18 V	
V_{CC-}	Supply voltage, negative ⁽²⁾		-18 V
V_{ID}	Differential input voltage ⁽³⁾	±30 V	
VI	Input voltage ⁽²⁾⁽⁴⁾	±15 V	
	Duration of output short circuit ⁽⁵⁾		Unlimited
	Continuous total power dissipation		(6)
H		TL082I	-40°C to 85°C
T _A	Operating free-air temperature range	TL082Q	-40°C to 125°C
θ_{JA}	Package thermal impedance, junction to free air ⁽⁷⁾	I	97°C/W
		Human-Body Model	1.5 kV (H1C)
	ESD rating ⁽⁸⁾	Charged-Device Model	1.5 kV (C5)
		Machine Model	200 V (M3)
	Operating virtual junction temperature	150°C	
T _{stg}	Storage temperature range	–65°C to 150°C	

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values, except differential voltages, are with respect to the midpoint between V_{CC+} and V_{CC-} .

(3) Differential voltages are at IN+ with respect to IN-.

(4) The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 V, whichever is less.

(5) The output may be shorted to ground or to either supply. Temperature and/or supply voltages must be limited to ensure that the dissipation rating is not exceeded.

(6) Maximum power dissipation is a function of $T_J(max)$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is PD = $(T_J(max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.

(7) The package thermal impedance is calculated in accordance with JESD 51-7.

(8) ESD protection level per JEDEC classifications JESD22-A114 (HBM), JESD22-A115 (MM), and JESD22-C101 (CDM).

TL082-Q1 JFET-INPUT OPERATIONAL AMPLIFIER

SLOS548-SEPTEMBER 2007



ELECTRICAL CHARACTERISTICS⁽¹⁾

 $V_{CC+} = \pm 15 V$ (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	T _A ⁽²⁾	MIN	TYP	MAX	UNIT
V _{IO} Input offset voltage		$V_{2} = 0$ $P_{2} = 50.0$	25°C		3	6	mV
		$V_{O} = 0, R_{S} = 50 \Omega$	Full range			9	mv
α_{VIO}	Temperature coefficient of input offset voltage	$V_O = 0, R_S = 50 \ \Omega$	Full range		18		µV/∘C
1	Input offset current ⁽³⁾	V = 0	25°C		5	100	pА
I _{IO}	input onset current of	$V_{O} = 0$	Full range			20	nA
	Input bias current ⁽³⁾	$V_{\Omega} = 0$	25°C		30	200	pА
I _{IB}		V _O = 0	Full range			50	nA
V _{ICR}	Common-mode input voltage range		25°C	±11	–12 to 15		V
		$R_L = 10 \text{ k}\Omega$	25°C	±12	±13.5		
V _{OM}	Maximum peak output voltage swing	R _L ≥ 10 kΩ	Full range	±12			V
		$R_L \ge 2 k\Omega$	Fuil lange	±10	±12		
٨	Large-signal differential voltage	$V_{\Omega} = \pm 10 \text{ V}, \text{ R}_{1} \geq 2 \text{ k}\Omega$	25°C	50 200			V/mV
A _{VD}	amplification	$v_0 = \pm 10 v, R_1 \ge 2 R_{22}$	Full range	15			V/IIIV
B1	Unity-gain bandwidth		25°C		3		MHz
r _i	Input resistance		25°C		10 ¹²		Ω
CMRR	Common-mode rejection ratio	$V_{IC} = V_{ICR}(min), V_O = 0, R_S = 50 \ \Omega$	25°C	75	86		dB
k _{SVR}	Supply-voltage rejection ratio $(\Delta V_{CC\pm}/\Delta V_{IO})$	$\begin{array}{l} V_{CC} = \pm 15 \text{ V to } \pm 9 \text{ V}, \\ V_O = 0, \text{ R}_S = 50 \Omega \end{array}$	25°C	80	86		dB
I _{CC}	Supply current (per amplifier)	$V_{O} = 0$, No load	25°C		1.4	2.8	mA
V ₀₁ /V ₀₂	Crosstalk attenuation	A _{VD} = 100	25°C		120		dB

(1) All characteristics are measured under open-loop conditions with zero common-mode voltage, unless otherwise specified. (2) Full range for T_A is -40°C to 85°C for I-suffix devices and -40°C to 125°C for Q-suffix devices.

(2) (3) Input bias currents of an FET-input operational amplifier are normal junction reverse currents, which are temperature sensitive, as shown in Figure 14. Pulse techniques must be used that maintain the junction temperature as close to the ambient temperature as possible.


OPERATING CHARACTERISTICS

 $V_{CC\pm} = \pm 15 \text{ V}, \text{ T}_{\text{A}} = 25^{\circ}\text{C}$ (unless otherwise noted)

	PARAMETER	TEST CO	MIN	TYP	MAX	UNIT	
SR	Slew rate at unity gain	$V_{I} = 10 \text{ V}, \text{ R}_{L} = 2 \text{ k}\Omega, \text{ C}_{L} =$	100 pF, See Figure 1	8	13		V/µs
t _r	Rise time	V_{I} = 20 mV, R_{L} = 2 k Ω , C_{L}	= 100 pF, See Figure 1		0.05		μs
	Overshoot factor	V_{I} = 20 mV, R_{L} = 2 k Ω , C_{L}		20		%	
V		D 20 O	f = 1 kHz		18		nV/√Hz
Vn	Equivalent input noise voltage	$R_{\rm S} = 20 \ \Omega$ f = 10 Hz to 10 kHz			4		μV
I _n	Equivalent input noise current	$R_S = 20 \Omega$, f = 1 kHz		0.01		pA/√ Hz	
THD	Total harmonic distortion	V _{Irms} = 6 V, f = 1 kHz, AVD	= 1, $R_S \le 1 \text{ k}\Omega$, $R_L \ge 2 \text{ k}\Omega$		0.003		%



PARAMETER MEASUREMENT INFORMATION








Figure 2.

TL082-Q1 JFET-INPUT OPERATIONAL AMPLIFIER




SLOS548-SEPTEMBER 2007

TYPICAL CHARACTERISTICS

Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the devices.

Table	of	Graphs
-------	----	--------

			FIGURE
		vs Frequency	3, 4, 5
V _{OM}		vs Free-air temperature	6
	Maximum peak output voltage	vs Load resistance	7
		vs Supply voltage	8
A _{VD}		vs Free-air temperature	9
	Large-signal differential voltage amplification	vs Frequency	10
PD	Total power dissipation	vs Free-air temperature	11
	Currentu current	vs Free-air temperature	12
ICC	Supply current	vs Supply voltage	13
I _{IB}	Input bias current	vs Free-air temperature	14
	Large-signal pulse response	vs Time	15
Vo	Output voltage	vs Elapsed time	16
CMRR	Common-mode rejection ratio	vs Free-air temperature	17
V _n	Equivalent input noise voltage	vs Frequency	18
THD	Total harmonic distortion	vs Frequency	19




6

10M


1M




SLOS548-SEPTEMBER 2007













TL082-Q1 JFET-INPUT OPERATIONAL AMPLIFIER SLOS548-SEPTEMBER 2007








APPLICATION INFORMATION













Figure 22. Audio-Distribution Amplifier


TL082-Q1 JFET-INPUT OPERATIONAL AMPLIFIER SLOS548-SEPTEMBER 2007






A. These resistor values may be adjusted for a symmetrical output.









10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TL082IDRQ1	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TL082I	Samples
TL082QDRQ1	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TL082Q	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

10-Dec-2020

OTHER QUALIFIED VERSIONS OF TL082-Q1 :

Catalog: TL082

Military: TL082M

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications



www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensio	ns are nominal												
De	evice	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TL08	2IDRQ1	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TL082	2QDRQ1	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

25-Sep-2024



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TL082IDRQ1	SOIC	D	8	2500	356.0	356.0	35.0
TL082QDRQ1	SOIC	D	8	2500	356.0	356.0	35.0

D0008A



PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.

- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



D0008A

EXAMPLE BOARD LAYOUT

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



D0008A

EXAMPLE STENCIL DESIGN

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated