



SLLS008E - JUNE 1986 - REVISED OCTOBER 2023

Support &

training

SN75ALS193 Quadruple Differential Line Receiver

Technical

documentation

9 Design &

development

1 Features

- Meets or exceeds ANSI standard EIA/TIA-422-B and EIA/TIA-423-A and ITU recommendations V.10 and V.11
- Designed for multipoint bus transmission on long bus lines in noisy environments
- 3-state outputs
- Common-mode input voltage range: -7 V to 7 V
- Input sensitivity: ±200 mV
- Input hysteresis: 120-mV typical
- High input impedance: 12-kΩ minimum
- Operates from single 5-V supply
- Low supply current requirement 35-mA maximum
- Improved speed and power version of the AM26LS32A

2 Applications

- Motor drives
- Factory automation and control

3 Description

The SN75ALS193 is a monolithic quadruple line receiver with 3-state outputs designed using advanced low-power Schottky technology. This technology provides combined improvements in bar design, tooling production, and wafer fabrication. This, in turn, provides significantly lower power requirements and permits much higher data throughput than other designs. This device meets the specifications of ANSI Standards EIA/TIA-422-B and EIA/TIA-423-A and ITU Recommendations V.10 and V.11. It features 3-state outputs that permit direct connection to a bus-organized system with a fail-safe design that ensures the outputs will always be high if the inputs are open.

The device is optimized for balanced multipoint bus transmission at rates up to 20 megabits per second. The input features high input impedance, input hysteresis for increased noise immunity, and an input sensitivity of \pm 200 mV over a common-mode input voltage range of -7 to 7 V. It also features active-high and active-low enable functions that are common to the four channels. The SN75ALS193 is designed for optimum performance when used with the 'ALS192 quadruple differential line driver.


The SN75ALS193 is characterized for operation from 0° C to 70° C.


Package	Information
---------	-------------

PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾					
SN75ALS193	N (PDIP, 16)	19.3 mm × 9.4 mm					
SINT SALO 195	D (SOIC, 16)	9.9 mm × 6 mm					

(1) For more information, see Section 10.

(2) The package size (length × width) is a nominal value and includes pins, where applicable.





Logic Diagram (Positive Logic)

[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.



Table of Contents

1 Features	1
2 Applications	1
3 Description	
4 Pin Configuration and Functions	
5 Specifications	4
5.1 Absolute Maximum Ratings	
5.2 Dissipation Rating	
5.3 Recommended Operating Conditions	
5.4 Thermal Information	
5.5 Electrical Characteristics	5
5.6 Switching Characteristics	5
5.7 Typical Characteristics	

6 Parameter Measurement Information	10
7 Detailed Description	. 12
7.1 Device Functional Modes	12
8 Device and Documentation Support	13
8.1 Receiving Notification of Documentation Updates.	13
8.2 Support Resources	13
8.3 Trademarks	13
8.4 Electrostatic Discharge Caution	13
8.5 Glossary	13
9 Revision History	13
10 Mechanical, Packaging, and Orderable	
Information	13



4 Pin Configuration and Functions

1B [1A [1Y [G [2Y [1 2 3 4 5	1 1 1	6 5 4 3	V _{CC} 4B 4A 4Y G
2Y [4 5	1	2] <u>G</u>
2 T L 2A [6		11	1 3Y
				E
2B [7	1	0] 3A
GND [8		9] 3B

Figure 4-1. D or N Package (Top View)

Table 4-1. Pin Functions

PIN			DESCRIPTION			
NAME	NO.		DESCRIPTION			
1B	1	I	Channel 1 Differential Receiver Inverting Input			
1A	2	I	Channel 1 Differential Receiver Non-Inverting Input			
1Y	3	0	Channel 1 Single Ended Output			
G	4	I	Active High Enable			
2Y	5	0	Channel 2 Single Ended Output			
2A	6	I	Channel 2 Differential Receiver Non-Inverting Input			
2B	7	I	Channel 2 Differential Receiver Inverting Input			
GND	8	GND	Device GND			
3B	9	I	Channel 3 Differential Receiver Inverting Input			
3A	10	I	Channel 3 Differential Receiver Non-Inverting Input			
3Y	11	0	Channel 3 Single Ended Output			
G	12	I	Active Low Enable			
4Y	13	0	Channel 4 Single Ended Output			
4A	14	I	Channel 4 Differential Receiver Non-Inverting Input			
4B	15	I	Channel 4 Differential Receiver Inverting Input			
V _{CC}	16	PWR	Device VCC (4.75V to 5.25V)			

(1) Signal Types: I = Input, O = Output, I/O = Input or Output.



5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN MAX	UNIT
V _{CC}	Supply voltage, see ⁽²⁾	7	V
VI	Input voltage, A or B	±15	V
V _{ID}	Differential input voltage, see ⁽³⁾	±15	V
VI	Enable input voltage	7	V
I _{OL}	Low-level output current	50	mA
	Continuous total dissipation	See Dissipation Rating table	
T _A	Operating free-air temperature range	0 70	°C
	Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds	300	°C
T _{stg}	Storage temperature range	-65 150	°C

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values, except differential input voltage, are with respect to network ground terminal.

(3) Differential-input voltage is measured at the noninverting input with respect to the corresponding inverting input.

5.2 Dissipation Rating

PACKAGE	PACKAGE $T_A \leq 25^{\circ}C$ POWER RATING		T _A = 70°C POWER RATING	
Ν	1150 mW	9.2 mW/°C	736 mW	

5.3 Recommended Operating Conditions

	MIN	NOM	MAX	UNIT
Supply voltage, V _{CC}	4.75	5	5.25	V
Common-mode input voltage, V _{IC}			±7	V
Differential input voltage, V _{ID}			±12	V
High-level input voltage, V _{IH}	2			V
Low-level input voltage, V _{IL}			0.8	V
High-level output current, I _{OH}			-400	μA
Low-level output current, I _{OL}		·	16	mA
Operating free-air temperature, T _A	0	70		°C

5.4 Thermal Information

THERMAL METRIC ⁽¹⁾		SN75		
		N (PDIP)	D (SOIC)	UNIT
	-	16 Pins	16 Pins	
R _{θJA}	Junction-to-ambient thermal resistance	60.6	84.6	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	48.1	43.5	°C/W
R _{θJB}	Junction-to-board thermal resistance	40.6	43.2	°C/W
ΨJT	Junction-to-top characterization parameter	27.5	10.4	°C/W
Ψ _{JB}	Junction-to-board characterization parameter	40.3	42.8	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC package thermal metrics application report.



5.5 Electrical Characteristics

over recommended range of common-mode input voltage, supply voltage, and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST C	ONDITIONS ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
V _{IT+}	Positive-going input threshold voltage					200	mV
V _{IT-}	Negative-going input threshold voltage			-200 ⁽³⁾			mV
V _{hys}	Hysteresis voltage (V _{IT+} -V _{IT-})				120		mV
V _{IK}	Enable-input clamp voltage	V _{CC} = MIN,	I _I = -18 mA			-1.5	V
V _{OH}	High-level output voltage	V _{CC} = MIN, I _{OH} = – 400 μA,	V _{ID} = 200 mV, See Figure 1	2.5	1.6		V
		$V_{CC} = MIN, V_{ID} = -$	I _{OL} = 8 mA			0.45	
V _{OL}	Low-level output voltage	200 mV, See Figure 1	I _{OL} = 16 mA			0.5	V
	Lligh impedance state sutput surrent		V _O = 2.4 V			20	
I _{OZ}	High-impedance-state output current	V _{CC} = MAX	V _O = 0.4 V			-20	μA
	Line input ourrent	Other input at 0, See	V _{CC} = MIN, V _I = 15 V		0.7	1.2	mA
I _I	Line input current	(4)	V _{CC} = MIN, V _I = -15 V		-1.0	-1.7	mA
	Lligh lovel enable input current		V _{IH} = 2.7 V			20	
IIH	High-level enable-input current	V _{CC} = MAX	V _{IH} = MAX			100	μA
IIL	Low-level enable-input current	V _{CC} = MAX,	V _{IL} = 0.4 V			-100	μA
	Input resistance			12	18		kΩ
I _{OS}	Short-circuit output current	$V_{\rm CC}$ = MAX, $V_{\rm O}$ = 0,	V _{ID} = 3 V, See ⁽⁵⁾	-15	-78	-130	mA
I _{CC}	Supply current	V _{CC} = MAX,	Outputs disabled		22	35	mA

(1) For conditions shown as MIN or MAX, use the appropriate values specified under recommended operating conditions.

(2) All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

(3) The algebraic convention, in which the less positive limit is designated minimum, is used in this data sheet for threshold voltage levels only.

(4) Refer to ANSI Standard EIA/TIA-422-B and EIA/TIA-423-A for exact conditions.

(5) Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.


5.6 Switching Characteristics

 $V_{CC} = 5 V, T_A = 25^{\circ}C$

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
t _{PLH}	Propagation delay time, low-to-high-level output	V _{ID} = -2.5 '	V _{ID} = -2.5 V to 2.5 V		15	22	
t _{PHL}	Propagation delay time, high-to-low-level output	C _L = 15 pF	See Figure 6-1		15	22	
	Output enable time to high lovel	C _L =15 pF See	=15 pF See Figure 6-2		13	25	20
t _{PZH}	Output enable time to high level				11	25	ns
	Output disable time from high load	C _L = 5 pF See Figure 6-2	See Figure 6.2		13	25	
t _{PHZ}	Output disable time from high level			15	22		




5.7 Typical Characteristics






5.7 Typical Characteristics (continued)






5.7 Typical Characteristics (continued)






5.7 Typical Characteristics (continued)





6 Parameter Measurement Information




TEST CIRCUIT

VOLTAGE WAVEFORMS


- A. The input pulse is supplied by a generator having the following characteristics: PRR \leq 1 MHz, duty cycle \leq 50%, Z_O = 50 Ω , t_r \leq 6 ns, t_f \leq 6 ns.
- B. C_L includes probe and jig capacitance.

Figure 6-2. Test Circuit and Voltage Waveforms










A. C_L includes probe and jig capacitance.

B. All diodes are 1N3064 or equivalent.

C. Enable G is tested with \overline{G} high; \overline{G} is tested with G low.





7 Detailed Description

7.1 Device Functional Modes

DIFFERENTIAL INPUTS A – B ⁽¹⁾	EN	OUTPUT Y		
DIFFERENTIAL INFOTS A - B	G	G	COIPOILI	
V _{ID} ≥ 0.2 V	Н	Х	Н	
VID = 0.2 V	Х	L	Н	
–0.2 V _{ID} < V _{ID} < 0.2 V	Н	Х	?	
$-0.2 V_{ID} < V_{ID} < 0.2 V$	Х	L	?	
V _{ID} ≤ -0.2 V	Н	Х	L	
$V_{\text{ID}} = -0.2$ V	Х	L	L	
Х	L	Н	Z	
Open	Н	Х	Н	
Open	Х	L	Н	

Table 7-1. Function Table (Each Receiver)

(1) H = high level, L = low level, X = irrelevant, ? = indeterminate, Z = high impedance (off)




Figure 7-1. Schematics of Inputs and Outputs



8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

8.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.2 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.3 Trademarks

TI E2E[™] is a trademark of Texas Instruments. All trademarks are the property of their respective owners.

8.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.5 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (May 1995) to Revision E (October 2023)

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Page



PACKAGING INFORMATION

Orderable Device	Status	Package Type	•	Pins	•	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
SN75ALS193D	OBSOLETE	SOIC	D	16		TBD	Call TI	Call TI	0 to 70	75ALS193	
SN75ALS193DR	ACTIVE	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	75ALS193	Samples
SN75ALS193N	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	0 to 70	(SN75ALS193N, SN7A LS193N)	Samples
SN75ALS193NE4	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	0 to 70	(SN75ALS193N, SN7A LS193N)	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



www.ti.com

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal	

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN75ALS193DR	SOIC	D	16	2500	330.0	16.4	6.5	10.3	2.1	8.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

25-Sep-2024



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN75ALS193DR	SOIC	D	16	2500	353.0	353.0	32.0

TEXAS INSTRUMENTS

www.ti.com

25-Sep-2024

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
SN75ALS193N	N	PDIP	16	25	506	13.97	11230	4.32
SN75ALS193NE4	N	PDIP	16	25	506	13.97	11230	4.32

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- \triangle The 20 pin end lead shoulder width is a vendor option, either half or full width.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated