





LP2981-N

SNOS7730 - MARCH 2000 - REVISED DECEMBER 2023

# LP2981-N 100-mA, Low-Dropout Regulator in SOT-23 Package

### 1 Features

Texas


Input Voltage (V<sub>IN</sub>) Range:

INSTRUMENTS

- Legacy chip: 2.1 V to 16 V
- New chip: 2.5 V to 16 V
- Output Voltage (V<sub>OUT</sub>) Range: 1.2 V to 5.0 V
- Output Voltage (V<sub>OUT</sub>) Accuracy:
  - ±0.75% for A-Grade legacy chip
  - ±1.25% for standard-grade legacy chip
  - ±0.5% for new chip (A grade and standard grade)
- Output Voltage (V<sub>OUT</sub>) accuracy over load, and temperature: ±1% (new chip)
- Output current: Up to 100 mA
- Low  $I_Q$  (new chip): 69  $\mu$ A at  $I_{LOAD}$  = 0 mA •
- Low  $I_Q$  (new chip): 620  $\mu$ A at  $I_{LOAD}$  = 100 mA •
- Shutdown current over temperature:
  - $< 1 \,\mu A$  (legacy chip)
  - $\leq 1.75 \,\mu\text{A} \text{ (new chip)}$
- Output current limiting and thermal protection
- Stable with 2.2-µF ceramic capacitors (new chip)
- High PSRR (new chip):
  - 75 dB at 1 kHz, 45 dB at 1 MHz
- Operating junction temperature: -40°C to +125°C
- Package: 5-pin SOT-23 (DBV) •

## 2 Applications

- **Electricity meters**
- Micro inverters
- Server PSU (12-V output)
- **Residential breakers**



### **3 Description**

The LP2981-N is a fixed-output, low-dropout (LDO) voltage regulator supporting an input voltage range from 2.5 V to 16 V (for new chip only) and up to 100 mA of load current. The LP2981-N supports an output range of 1.2 V to 5.0 V (new chip).

Additionally, the LP2981-N (new chip) has a 1% output accuracy across load and temperature that can meet the needs of low-voltage microcontrollers (MCUs) and processors.

In the new chip, wide bandwidth PSRR performance is 75 dB at 1 kHz and 45 dB at 1 MHz to help attenuate the switching frequency of an upstream DC/DC converter and minimize post regulator filtering.


The internal soft-start time and current-limit protection reduce inrush current during start up, thus minimizing input capacitance. Standard protection features, such as overcurrent and overtemperature protection, are included.

### Package Information

PART NUMBER	PACKAGE <sup>(1)</sup>	BODY SIZE (NOM) (2)
LP2981-N	SOT-23 (5)	2.90 mm × 2.80 mm

For all available packages, see the orderable addendum at (1) the end of the data sheet.

The package size (length × width) is a nominal value and (2) includes pins, where applicable.



Dropout Voltage versus Temperature (New Chip)




## **Table of Contents**

1 Features	I
2 Applications	I
3 Description	I
4 Pin Configuration and Functions	3
5 Specifications	1
5.1 Absolute Maximum Ratings	1
5.2 ESD Ratings	
5.3 Recommended Operating Conditions	1
5.4 Thermal Information	5
5.5 Electrical Characteristics	5
5.6 Typical Characteristics	3
6 Detailed Description18	
6.1 Overview	3
6.2 Functional Block Diagram18	3
6.3 Feature Description18	3
6.4 Device Functional Modes20	)
7 Application and Implementation2	I
7.1 Application Information2	I

7.2 Typical Application	. 24
8 Power Supply Recommendations	
9 Layout	.28
9.1 Layout Guidelines	
9.2 Layout Example	
10 Device and Documentation Support	.29
10.1 Device Nomenclature	.29
10.2 Third-Party Products Disclaimer	. 29
10.3 Receiving Notification of Documentation Updates.	.29
10.4 Related Documentation	29
10.5 Support Resources	. 29
10.6 Trademarks	.29
10.7 Electrostatic Discharge Caution	.29
10.8 Glossary	
11 Revision History	30
12 Mechanical, Packaging, and Orderable	
Information	. 30



## **4** Pin Configuration and Functions



### Figure 4-1. DBV Package, 5-Pin SOT-23 (Top View)

### Table 4-1. Pin Functions

PIN		TYPE	DESCRIPTION		
NO.	NAME		DESCRIPTION		
1	IN	I	Input supply pin. Use a capacitor with a value of 1 $\mu$ F or larger from this pin to ground. See the Section 7.1.2 section for more information.		
2	GND	_	Common ground (device substrate).		
3	ON/OFF	I	Enable pin for the LDO. Driving the ON/ $\overline{\text{OFF}}$ pin high enables the device. Driving this pin low disables the device. High and low thresholds are listed in the Section 5.5 table. Tie this pin to $V_{\text{IN}}$ if unused.		
4	NC	_	For new chip: Not internally connected. This pin can be left open or tied to ground for improved thermal performance. For legacy chip: DO NOT CONNECT. Device pin 4 is reserved for post packaging test and calibration of the LP2981-N $V_{OUT}$ accuracy. Device pin 4 must be left floating. Do not connect to any potential. Do not connect to ground. Any attempt to do pin continuity testing on device pin 4 is discouraged. Continuity test results will be variable depending on the actions of the factory calibration. Aggressive pin continuity testing (high voltage, or high current) on device pin 4 can activate the trim circuitry forcing $V_{OUT}$ to move out of tolerance.		
5	OUT	0	Output of the regulator. Use a capacitor with a value of 2.2 $\mu$ F or larger from this pin to ground. See the <i>Section 7.1.2</i> section for more information.		

### **5** Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V	Continuous input voltage range (for legacy chip)	-0.3	16	
V <sub>IN</sub>	Continuous input voltage range(for new chip)	-0.3	18	
	Output voltage range (for legacy chip)       Output voltage range(for new chip)       ON/OFF pin voltage range (for legacy chip)	-0.3	9	
V <sub>OUT</sub>	Output voltage range(for new chip)	-0.3	V <sub>IN</sub> + 0.3 or 9 (whichever is smaller)	V
V	ON/OFF pin voltage range (for legacy chip)	-0.3	16	
V <sub>ON/OFF</sub>	ON/OFF pin voltage range (for new chip)	-0.3	18	
	Input-output voltage (for legacy chip)	-0.3	16	
VIN - VOUT	Input-output voltage (for new chip)	-0.3	18	
Current	Maximum output current	Internally	Internally limited	
Tomporatura	Operating junction, T <sub>J</sub>	-55	150	°C
Temperature	Storage, T <sub>stg</sub>	-65	150	U

### 5.2 ESD Ratings

			VALUE (Legacy Chip)	VALUE (New Chip)	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (Pin 1,2 and 5) $^{(1)}$	±2000	±3000	
V <sub>(ESD)</sub>	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (Pin 3 and 4) <sup>(1)</sup>	±1000	13000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	N/A	±1000	

(1) JEDEC document JEP155 states that 2-kV HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 500-V CDM allows safe manufacturing with a standard ESD control process.

### **5.3 Recommended Operating Conditions**

		MIN	NOM	MAX	UNIT
V	Supply input voltage (for legacy chip)	2.1		16	
V <sub>IN</sub>	Supply input voltage (for new chip)	2.5		16	
	Input-output differential (for legacy chip)	0.7		11	
V <sub>IN</sub> – V <sub>OUT</sub>	Input-output differential (for new chip)	0		16	V
V <sub>OUT</sub>	Output voltage (for new chip)	1.2		5	
M	Enable voltage (for legacy chip)	0		V <sub>IN</sub> 16	
V <sub>ON/OFF</sub>	Enable voltage (for new chip)	0		16	
I <sub>OUT</sub>	Output current	0		100	mA
C <sub>IN</sub> <sup>(1)</sup>	Input capacitor		1		
0	Output capacitor (for legacy chip)	2.2	4.7		μF
C <sub>OUT</sub>	Output capacitance (for new chip) <sup>(1)</sup>	1	2.2	16 100 1 4.7	
TJ	Operating junction temperature	-40		125	°C

All capacitor values are assumed to derate to 50% of the nominal capacitor value. Maintain an effective output capacitance of 1 µF minimum for stability.



### 5.4 Thermal Information

		Legacy Chip <sup>(2)</sup>	New Chip <sup>(2)</sup>	
	THERMAL METRIC <sup>(1)</sup>	DBV (SOT23-5)	DBV (SOT23-5)	UNIT
		5 PINS	5 PINS	
R <sub>0JA</sub>	Junction-to-ambient thermal resistance	175.7	178.6	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	78.0	77.9	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	30.8	47.2	°C/W
Ψյт	Junction-to-top characterization parameter	2.8	15.9	°C/W
Ψјв	Junction-to-board characterization parameter	30.3	46.9	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application note.

(2) Thermal performance results are based on the JEDEC standard of 2s2p PCB configuration. These thermal metric parameters can be further improved by 35-55% based on thermally optimized PCB layout designs. See the analysis of the *Impact of board layout on LDO thermal performance* application report.

### **5.5 Electrical Characteristics**

specified at  $T_J = 25^{\circ}C$ ,  $V_{IN} = V_{OUT(nom)} + 1.0$  V or VIN = 2.5 V (whichever is greater),  $I_{OUT} = 1$  mA,  $V_{ON/OFF} = 2$  V,  $C_{IN} = 1.0$   $\mu$ F, and  $C_{OUT} = 2.2$   $\mu$ F (unless otherwise noted)

	PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
			Legacy chip (Standard grade)	-1.25		1.25	%
		I <sub>L</sub> = 1 mA	Legacy chip (A grade)	-0.75		0.75	%
			New chip	-0.5		0.5	%
			Legacy chip (Standard grade)	-2.0		2.0	%
ΔV <sub>OUT</sub>	Output voltage tolerance	1 mA < I <sub>L</sub> < 100 mA	Legacy chip (A grade)	-1.0		1.0	%
			New chip	-0.5		0.5	%
		1 mA < I <sub>L</sub> < 100 mA, –40°C ≤ T <sub>J</sub> ≤ 125°C	Legacy chip (Standard grade)	-3.5		3.5	%
			Legacy chip (A grade)	-2.5		2.5	%
			New chip	-1		1	%
			Legacy chip		0.007	0.014	%/V
A\/	Line regulation	$V_{O(NOM)}$ + 1 V ≤ $V_{IN}$ ≤ 16 V	New chip		0.002	0.014	
ΔV <sub>OUT(ΔVIN)</sub>		$V_{O(NOM)}$ + 1 V ≤ $V_{IN}$ ≤ 16 V, -40°C ≤ $T_J$ ≤ 125°C	Legacy chip		0.007	0.032	
		VO(NOM) · · · · · · · · · · · · · · · · · · ·	New chip		0.002	0.032	
$\Delta V_{OUT(\Delta)}$ Iload)	Load regulation	1 mA < I <sub>L</sub> < 100 mA, -40°C ≤ T <sub>J</sub> ≤ 125°C, V <sub>IN</sub> = $V_{O(NOM)}$ +0.5 V	New chip		0.1	0.5	%/A



specified at  $T_J = 25^{\circ}C$ ,  $V_{IN} = V_{OUT(nom)} + 1.0$  V or VIN = 2.5 V (whichever is greater),  $I_{OUT} = 1$  mA,  $V_{ON/OFF} = 2$  V,  $C_{IN} = 1.0$   $\mu$ F, and  $C_{OUT} = 2.2$   $\mu$ F (unless otherwise noted)

	PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNI
		I <sub>OUT</sub> = 0 mA	Legacy chip		1 3		
			New chip		1	2.75	
		$1 = 0 = 0 = 0$ $40^{\circ} C < T < 125^{\circ} C$	Legacy chip			5	
		$I_{OUT} = 0 \text{ mA}, -40^{\circ}\text{C} \le T_{\text{J}} \le 125^{\circ}\text{C}$	New chip			3	
Vin - Vout		I <sub>OUT</sub> = 1 mA	Legacy chip		7	10	
			New chip		11.5	14	
			Legacy chip			15	
	- (1)	$I_{OUT} = 1 \text{ mA}, -40^{\circ}\text{C} \le T_{\text{J}} \le 125^{\circ}\text{C}$	New chip			17	
V <sub>IN</sub> - V <sub>OUT</sub>	Dropout voltage <sup>(1)</sup>		Legacy chip		70	100	m۱
		I <sub>OUT</sub> = 25 mA	New chip		110	132	
			Legacy chip			150	
		I <sub>OUT</sub> = 25 mA, –40°C ≤ T <sub>J</sub> ≤ 125°C	New chip			167	
			Legacy chip		200	250	
		I <sub>OUT</sub> = 100 mA	New chip		160	175	
			Legacy chip			375	-
		$I_{OUT}$ = 100 mA, -40°C ≤ $T_{J}$ ≤ 125°C	New chip			218	
			Legacy chip		65	95	
		I <sub>OUT</sub> = 0 mA	New chip			95	
		$I_{OUT} = 0 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$ $I_{OUT} = 1 \text{ mA}$	-		69		
			Legacy chip			125	
			New chip			123	
			Legacy chip		80	110	
			New chip		78	110	
		$I_{OUT} = 1 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$	Legacy chip			170	
			New chip			140	
		I <sub>OUT</sub> = 25 mA	Legacy chip		200	300	
GND	GND pin current		New chip		225	295	μА
GND		I <sub>OUT</sub> = 25 mA, –40°C ≤ T <sub>J</sub> ≤ 125°C	Legacy chip			550	-
			New chip			345	
		I <sub>OUT</sub> = 100 mA	Legacy chip		600	800	
			New chip		620	790	
			Legacy chip			1500	
		I <sub>OUT</sub> = 100 mA, –40°C ≤ T <sub>J</sub> ≤ 125°C	New chip			950	
			Legacy chip		0.01	0.8	
		V <sub>ON/OFF</sub> < 0.3 V, V <sub>IN</sub> = 16 V	New chip		1.25	1.75	-
			Legacy chip		0.05	2	
		$V_{ON/OFF} < 0.15 \text{ V}, V_{IN} = 16 \text{ V}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$	New chip		1.12	2.75	
V <sub>UVLO+</sub>	Rising bias supply UVLO	V <sub>IN</sub> rising, –40°C ≤ T <sub>J</sub> ≤ 125°C	· ·		2.2	2.4	
V <sub>UVLO-</sub>	Falling bias supply UVLO	$V_{IN}$ falling, $-40^{\circ}C \le T_{I} \le 125^{\circ}C$	New chip	1.9			v
VUVLO(HYST)	UVLO hysteresis	$-40^{\circ}C \le T_{J} \le 125^{\circ}C$			.130		-
			1	0			
VUVLO(HYST)			Legacy chip		150		



specified at $T_J = 25^{\circ}C$ , $V_{IN} = V_{OUT(nom)} + 1.0 V$	or VIN = 2.5 V (whichever is greater), $I_{OUT}$ = 1 mA, $V_{ON/OFF}$ = 2 V, $C_{IN}$ = 1.0
$\mu$ F, and C <sub>OUT</sub> = 2.2 $\mu$ F (unless otherwise noted)	


	PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
			Legacy chip		0.5		
		Low = Output OFF	New chip		0.72		
V <sub>ON/OFF</sub>		Low = Output OFF, $V_{OUT}$ + 1 ≤ $V_{IN}$ ≤ 16 V, -40°C ≤ $T_J$	Legacy chip			0.15	1
	ON/OFF input voltage	≤ 125°C	New chip			0.15	
VON/OFF	ON/OFF input voltage	Llich - Output ON	Legacy chip		1.4		V
		High = Output ON	New chip		0.85		
		High = Output ON, $V_{OUT}$ + 1 ≤ $V_{IN}$ ≤ 16 V, -40°C ≤ $T_J$ ≤	Legacy chip	1.6			
		125°C	New chip	1.6			
			Legacy chip		0.01		
I <sub>ON/OFF</sub>		V <sub>ON/OFF</sub> = 0 V	New chip		0.42		
		$V_{ON/OFF} = 0 \text{ V}, V_{OUT} + 1 \le V_{IN} \le 16 \text{ V}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$	Legacy chip			-1	
	ON/OFF input current		New chip			-0.9	
		$V_{ON/OFF} = 5 V$ $V_{ON/OFF} = 5 V, V_{OUT} + 1 \le V_{IN} \le 16 V, -40^{\circ}C \le T_{J} \le 125^{\circ}C$	Legacy chip		5		μA
			New chip		0.011		
			Legacy chip			15	
			New chip			2.20	
			Legacy chip (A version)	150	400		
IO(PK)	Peak output current	Peak output current $V_{OUT} \ge V_{O(NOM)} -5\%$ (steady state)	Legacy chip (Standard version)		150		mA
			New chip		350		
ΔV <sub>O</sub> /ΔV <sub>IN</sub>	Ripple Rejection	f = 1 kHz, C <sub>OUT</sub> = 10 μF	Legacy chip		63		dB
		$1 - 1 \text{ km}^2, \text{ C}_{00T} - 10 \mu$	New chip		75		
V <sub>n</sub> Output noise voltage	Bandwidth = 300 Hz to 50 kHz, $C_{OUT}$ = 2.2 µF, $V_{OUT}$ = 3.3 V, I <sub>LOAD</sub> = 150 mA	Legacy chip		160		μ <sub>VRM</sub>	
	Calput noise voitage	Bandwidth = 300 Hz to 50 kHz, $C_{OUT}$ = 2.2 µF, $V_{OUT}$ = 3.3 V, I <sub>LOAD</sub> = 150 mA	New chip		140		S
T <sub>sd+</sub>	Thermal shutdown	Shutdown, temperature increasing	New chip		170		°C
T <sub>sd-</sub>	threshold	Reset, temperature decreasing			150		

(1) Dropout voltage ( $V_{DO}$ ) is defined as the input-to-output differential at which the output voltage drops 100 mV below the value measured with a 1-V differential.  $V_{DO}$  is measured with  $V_{IN} = V_{OUT(nom)} - 100$  mV for fixed output devices.




### **5.6 Typical Characteristics**


Unless otherwise specified:  $T_A = 25^{\circ}C$ ,  $V_{IN} = V_{O(NOM)} + 1$  V,  $C_{OUT} = 4.7 \ \mu\text{F}$ ,  $C_{IN} = 1 \ \mu\text{F}$  all voltage options, ON/ OFF pin tied to  $V_{IN}$ .




















LP2981-N SNOS7730 – MARCH 2000 – REVISED DECEMBER 2023






LP2981-N SNOS7730 – MARCH 2000 – REVISED DECEMBER 2023












LP2981-N SNOS7730 – MARCH 2000 – REVISED DECEMBER 2023














### 6 Detailed Description

### 6.1 Overview

The LP2981-N is a fixed-output, high PSRR, low-dropout regulator that offers exceptional, cost-effective performance for both portable and non-portable applications. The LP2981-N has an output tolerance of 1% across line, load, and temperature variation (for the new chip) and is capable of delivering 100 mA of continuous load current.

This device features integrated overcurrent protection, thermal shutdown, output enable, and internal output pulldown and has a built-in soft-start mechanism for controlled inrush current. This device delivers excellent line and load transient performance. The operating ambient temperature range of the device is  $-40^{\circ}$ C to  $+125^{\circ}$ C.

### 6.2 Functional Block Diagram



### 6.3 Feature Description

### 6.3.1 Output Enable

The ON/OFF pin for the device is an active-high pin. The output voltage is enabled when the voltage of the ON/OFF pin is greater than the high-level input voltage of the ON/OFF pin and disabled when the ON/OFF pin voltage is less than the low-level input voltage of the ON/OFF pin. If independent control of the output voltage is not needed, connect the ON/OFF pin to the input of the device.

For the new chip, the device has an internal pulldown circuit that activates when the device is disabled by pulling the ON/OFF pin voltage lower than the low-level input voltage of the ON/OFF pin to actively discharge the output voltage.

### 6.3.2 Dropout Voltage

Dropout voltage ( $V_{DO}$ ) is defined as the input voltage minus the output voltage ( $V_{IN} - V_{OUT}$ ) at the rated output current ( $I_{RATED}$ ), where the pass transistor is fully on.  $I_{RATED}$  is the maximum  $I_{OUT}$  listed in the *Section 5.3* table. The pass transistor is in the ohmic or triode region of operation, and acts as a switch. The dropout voltage indirectly specifies a minimum input voltage greater than the nominal programmed output voltage at which the output voltage is expected to stay in regulation. If the input voltage falls to less than the nominal output regulation, then the output voltage falls as well.

For a CMOS regulator, the dropout voltage is determined by the drain-source on-state resistance ( $R_{DS(ON)}$ ) of the pass transistor. Therefore, if the linear regulator operates at less than the rated current, the dropout voltage for that current scales accordingly. The following equation calculates the  $R_{DS(ON)}$  of the device.



$$R_{\rm DS(ON)} = \frac{V_{\rm DO}}{I_{\rm RATED}}$$

(1)

#### 6.3.3 Current Limit

The device has an internal current limit circuit that protects the regulator during transient high-load current faults or shorting events. The current limit is a brick-wall scheme. In a high-load current fault, the brick-wall scheme limits the output current to the current limit ( $I_{CL}$ ).  $I_{CL}$  is listed in the *Electrical Characteristics* table.

The output voltage is not regulated when the device is in current limit. When a current limit event occurs, the device begins to heat up because of the increase in power dissipation. When the device is in brick-wall current limit, the pass transistor dissipates power  $[(V_{IN} - V_{OUT}) \times I_{CL}]$ . If thermal shutdown is triggered, the device turns off. After the device cools down, the internal thermal shutdown circuit turns the device back on. If the output current fault condition continues, the device cycles between current limit and thermal shutdown. For more information on current limits, see the *Know Your Limits* application note.

*Figure 6-1* shows a diagram of the current limit.




Figure 6-1. Current Limit

#### 6.3.4 Undervoltage Lockout (UVLO)

For the new chip, the device has an independent undervoltage lockout (UVLO) circuit that monitors the input voltage, allowing a controlled and consistent turn on and off of the output voltage. To prevent the device from turning off if the input drops during turn on, the UVLO has hysteresis as specified in the Section 5.5 table.

#### 6.3.5 Thermal Shutdown

The device contains a thermal shutdown protection circuit to disable the device when the junction temperature  $(T_J)$  of the pass transistor rises to  $T_{SD(shutdown)}$  (typical). Thermal shutdown hysteresis makes sure that the device resets (turns on) when the temperature falls to  $T_{SD(reset)}$  (typical). Limits for Thermal shutdown circuit are defined in *Section 5.5*.

The thermal time-constant of the semiconductor die is fairly short, thus the device can cycle on and off when thermal shutdown is reached until power dissipation is reduced. Power dissipation during start up can be high from large  $V_{IN} - V_{OUT}$  voltage drops across the device or from high inrush currents charging large output capacitors. Under some conditions, the thermal shutdown protection disables the device before start-up completes.



For reliable operation, limit the junction temperature to the maximum listed in the *Section 5.3* table. Operation above this maximum temperature causes the device to exceed operational specifications. Although the internal protection circuitry of the device is designed to protect against thermal overall conditions, this circuitry is not intended to replace proper heat sinking. Continuously running the device into thermal shutdown or above the maximum recommended junction temperature reduces long-term reliability.

### 6.3.6 Output Pulldown

The new chip has an output pulldown circuit. The output pulldown activates in the following conditions:

- When the device is disabled (V<sub>ON/OFF</sub> < V<sub>ON/OFF(LOW)</sub>)
- If 1.0 V < V<sub>IN</sub> < V<sub>UVLO</sub>

Do not rely on the output pulldown circuit for discharging a large amount of output capacitance after the input supply has collapsed because reverse current can flow from the output to the input. This reverse current flow can cause damage to the device. See the *Section 7.1.5* section for more details.

### 6.4 Device Functional Modes

### 6.4.1 Device Functional Mode Comparison

Table 6-1 shows the conditions that lead to the different modes of operation. See the Section 5.5 table for parameter values.

OPERATING MODE	PARAMETER										
OPERATING MODE	V <sub>IN</sub>	V <sub>ON/OFF</sub>	I <sub>OUT</sub>	TJ							
Normal operation	$V_{IN} > V_{OUT(nom)} + V_{DO}$ and $V_{IN} > V_{IN(min)}$	$V_{ON/\overline{OFF}} > V_{ON/\overline{OFF}(HI)}$	$I_{OUT} < I_{OUT(max)}$	T <sub>J</sub> < T <sub>SD(shutdown)</sub>							
Dropout operation	$V_{IN(min)} < V_{IN} < V_{OUT(nom)} + V_{DO}$	$V_{ON/\overline{OFF}} > V_{ON/\overline{OFF}(HI)}$	$I_{OUT} < I_{OUT(max)}$	$T_J < T_{SD(shutdown)}$							
Disabled (any true condition disables the device)	V <sub>IN</sub> < V <sub>UVLO</sub>	V <sub>ON/OFF</sub> < V <sub>ON/</sub> OFF(LOW)	Not applicable	T <sub>J</sub> > T <sub>SD(shutdown)</sub>							

#### Table 6-1. Device Functional Mode Comparison

### 6.4.2 Normal Operation

The device regulates to the nominal output voltage when the following conditions are met:

- The input voltage is greater than the nominal output voltage plus the dropout voltage (V<sub>OUT(nom)</sub> + V<sub>DO</sub>)
- The output current is less than the current limit (I<sub>OUT</sub> < I<sub>CL</sub>)
- The device junction temperature is less than the thermal shutdown temperature (T<sub>J</sub> < T<sub>SD</sub>)
- The ON/OFF voltage has previously exceeded the ON/OFF rising threshold voltage and has not yet
  decreased to less than the enable falling threshold

#### 6.4.3 Dropout Operation

If the input voltage is lower than the nominal output voltage plus the specified dropout voltage, but all other conditions are met for normal operation, the device operates in dropout mode. In this mode, the output voltage tracks the input voltage. During this mode, the transient performance of the device becomes significantly degraded because the pass transistor is in the ohmic or triode region, and acts as a switch. Line or load transients in dropout can result in large output-voltage deviations.

When the device is in a steady dropout state (defined as when the device is in dropout,  $V_{IN} < V_{OUT(NOM)} + V_{DO}$ , directly after being in a normal regulation state, but *not* during start up), the pass transistor is driven into the ohmic or triode region. When the input voltage returns to a value greater than or equal to the nominal output voltage plus the dropout voltage ( $V_{OUT(NOM)} + V_{DO}$ ), the output voltage can overshoot for a short period of time while the device pulls the pass transistor back into the linear region.

### 6.4.4 Disabled

The output of the device can be shutdown by forcing the voltage of the ON/OFF pin to less than the maximum ON/OFF pin low-level input voltage (see the *Section 5.5* table). When disabled, the pass transistor is turned off,



internal circuits are shutdown, and the output voltage is actively discharged to ground by an internal discharge circuit from the output to ground.

### 7 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 7.1 Application Information

The LP2981-N is a linear voltage regulator operating from 2.5 V to 16 V (for new chip) on the input and regulates voltages between 1.2 V to 5 V with ±1% accuracy (across line, load and temperature) and 100-mA maximum output current.

Successfully implementing an LDO in an application depends on the application requirements. If the requirements are simply input voltage and output voltage, compliance specifications (such as internal power dissipation or stability) must be verified for a solid design. If timing, start-up, noise, power supply rejection ratio (PSRR), or any other transient specification is required, then the design becomes more challenging.

#### 7.1.1 Recommended Capacitor Types

### 7.1.1.1 Recommended Capacitors for the Legacy Chip

**Tantalum Capacitors:** For the legacy chip LP2981-N, tantalum capacitors are the best choice for use at the output of the LDO. Most good quality tantalums can be used with the LP2981-N, but check the manufacturer's data sheet to be sure the ESR is in range. At lower temperatures, as ESR increases, a capacitor with ESR, near the upper limit for stability at room temperature can cause instability. For very low temperature applications, output tantalum capacitors can be used in parallel configuration to prevent the ESR from going up too high.

**Ceramic Capacitors:** For the legacy chip LP2981-N, ceramic capacitors are not recommended for use at the output of the LDO. This is because the ESR of a ceramic can be low enough to go below the minimum stable value for the LP2981-N. A 2.2- $\mu$ F ceramic was measured and found to have an ESR of about 15 m $\Omega$ , which is low enough to cause oscillations. If a ceramic capacitor is used on the output, a 1- $\Omega$  resistor is required be placed in series with the capacitor.

**Aluminum Capacitors:** For the legacy chip LP2981-N, aluminum electrolytics are not typically used with the LDO, because of the large physical size. These aluminimum capacitors must meet the same ESR requirements over the operating temperature range, more difficult because of their steep increase at cold temperature. An aluminum electrolytic can exhibit an ESR increase of as much as 50x when going from 20°C to  $-40^{\circ}$ C. Also, some aluminum electrolytics are not operational below  $-25^{\circ}$ C because the electrolyte can freeze.

#### 7.1.1.2 Recommended Capacitors for the New Chip

The new chip is designed to be stable using low equivalent series resistance (ESR) ceramic capacitors at the input and output. Multilayer ceramic capacitors have become the industry standard for these types of applications and are recommended, but must be used with good judgment. Ceramic capacitors that employ X7R-, X5R-, and C0G-rated dielectric materials provide relatively good capacitive stability across temperature, whereas using Y5V-rated capacitors is discouraged because of large variations in capacitance.

Regardless of the ceramic capacitor type selected, the effective capacitance varies with operating voltage and temperature. Generally, expect the effective capacitance to decrease by as much as 50%. The input and output capacitors listed in the *Section 5.3* table account for an effective capacitance of approximately 50% of the nominal value.

Copyright © 2023 Texas Instruments Incorporated



### 7.1.2 Input and Output Capacitor Requirements

#### Input capacitor:

For the legacy chip, an input capacitor  $(C_{IN}) \ge 1 \ \mu F$  is required (the amount of capacitance can be increased without limit). Any good-quality tantalum or ceramic capacitor can be used. The capacitor must be located no more than half an inch from the input pin and returned to a clean analog ground.

For the new chip, although an input capacitor is not required for stability, good analog design practice is to connect a capacitor from IN to GND. This capacitor counteracts reactive input sources and improves transient response, input ripple, and PSRR. Use an input capacitor if the source impedance is more than 0.5  $\Omega$ . A higher value capacitor can be necessary if large, fast rise-time load or line transients are anticipated or if the device is located several inches from the input power source.

### Output capacitor:

For the legacy chip, The output capacitor must meet both the requirement for minimum amount of capacitance and equivalent series resistance (ESR) value. Curves are provided which show the allowable ESR range as a function of load current for various output voltages and capacitor values (refer to Figure 7-3, Figure 7-4, Figure 7-5, and Figure 7-6).

For the new chip, Dynamic performance of the device is improved with the use of an output capacitor. Use an output capacitor, preferably ceramic capacitors, within the range specified in the *Section 5.3* table for stability.

### 7.1.3 Estimating Junction Temperature

The JEDEC standard now recommends the use of psi ( $\Psi$ ) thermal metrics to estimate the junction temperatures of the linear regulator when in-circuit on a typical PCB board application. These metrics are not thermal resistance parameters and instead offer a practical and relative way to estimate junction temperature. These psi metrics are determined to be significantly independent of the copper area available for heat-spreading. The *Thermal Information* table lists the primary thermal metrics, which are the junction-to-top characterization parameter ( $\psi_{JT}$ ) and junction-to-board characterization parameter ( $\psi_{JB}$ ). These parameters provide two methods for calculating the junction temperature ( $T_J$ ), as described in the following equations. Use the junction-to-top characterization parameter ( $\psi_{JT}$ ) with the temperature at the center-top of device package ( $T_T$ ) to calculate the junction temperature. Use the junction-to-board characterization parameter ( $\psi_{JB}$ ) with the PCB surface temperature 1 mm from the device package ( $T_B$ ) to calculate the junction temperature.

$$T_{J} = T_{T} + \psi_{JT} \times P_{D}$$
<sup>(2)</sup>

where:

- P<sub>D</sub> is the dissipated power
- T<sub>T</sub> is the temperature at the center-top of the device package

$$T_J = T_B + \psi_{JB} \times P_D$$

where:

 T<sub>B</sub> is the PCB surface temperature measured 1 mm from the device package and centered on the package edge

For detailed information on the thermal metrics and how to use them, see the *Semiconductor and IC Package Thermal Metrics* application note.

### 7.1.4 Power Dissipation (P<sub>D</sub>)

Circuit reliability requires consideration of the device power dissipation, location of the circuit on the printed circuit board (PCB), and correct sizing of the thermal plane. The PCB area around the regulator must have few or no other heat-generating devices that cause added thermal stress.

To first-order approximation, power dissipation in the regulator depends on the input-to-output voltage difference and load conditions. The following equation calculates power dissipation (P<sub>D</sub>).

(3)



#### $P_D = (V_{IN} - V_{OUT}) \times I_{OUT}$

(4)

#### Note

Power dissipation can be minimized, and therefore greater efficiency can be achieved, by correct selection of the system voltage rails. For the lowest power dissipation use the minimum input voltage required for correct output regulation.

For devices with a thermal pad, the primary heat conduction path for the device package is through the thermal pad to the PCB. Solder the thermal pad to a copper pad area under the device. This pad area must contain an array of plated vias that conduct heat to additional copper planes for increased heat dissipation.

The maximum power dissipation determines the maximum allowable ambient temperature ( $T_A$ ) for the device. According to the following equation, power dissipation and junction temperature are most often related by the junction-to-ambient thermal resistance ( $R_{\theta JA}$ ) of the combined PCB and device package and the temperature of the ambient air ( $T_A$ ).

$$T_{J} = T_{A} + (R_{\theta JA} \times P_{D})$$
(5)

Thermal resistance ( $R_{\theta JA}$ ) is highly dependent on the heat-spreading capability built into the particular PCB design, and therefore varies according to the total copper area, copper weight, and location of the planes. The junction-to-ambient thermal resistance listed in the *Thermal Information* table is determined by the JEDEC standard PCB and copper-spreading area, and is used as a relative measure of package thermal performance. As mentioned in the *An empirical analysis of the impact of board layout on LDO thermal performance* application note,  $R_{\theta JA}$  can be improved by 35% to 55% compared to the *Thermal Information* table value with the PCB board layout optimization.

### 7.1.5 Reverse Current

Excessive reverse current can damage this device. Reverse current flows through the intrinsic body diode of the pass transistor instead of the normal conducting channel. At high magnitudes, this current flow degrades the long-term reliability of the device.

Conditions where reverse current can occur are outlined in this section, all of which can exceed the absolute maximum rating of  $V_{OUT} \le V_{IN} + 0.3 \text{ V}$ .

- If the device has a large C<sub>OUT</sub> and the input supply collapses with little or no load current
- The output is biased when the input supply is not established
- The output is biased above the input supply

If reverse current flow is expected in the application, use external protection to protect the device. Reverse current is not limited in the device, so external limiting is required if extended reverse voltage operation is anticipated.

*Figure 7-1* shows one approach for protecting the device.





Figure 7-1. Example Circuit for Reverse Current Protection Using a Schottky Diode



### 7.2 Typical Application



\*ON/  $\overline{\text{OFF}}$  input must be actively terminated. Tie to V<sub>IN</sub> if this function is not to be used. Minimum output capacitance is shown to insure stability over full load current range. More capacitance provides superior dynamic performance and additional stability margin (see Section 7.1.1).

### Figure 7-2. LP2981-N Typical Application

### 7.2.1 Design Requirements

PARAMETER	DESIGN REQUIREMENT
Input voltage	12 V ±10%, provided by the DC-DC converter switching at 1 MHz
Output voltage	3.3 V ±1%
Output current	100 mA (maximum), 1 mA (minimum)
RMS noise, 300 Hz to 50 kHz	< 1 mV <sub>RMS</sub>
PSRR at 1 kHz	> 40 dB

### 7.2.2 Detailed Design Procedure

#### 7.2.2.1 ON and OFF Input Operation

The LP2981-N is shut off by pulling the ON/  $\overline{OFF}$  input low, and turned on by driving the input high. If this feature is not to be used, the ON/OFF input is required to be tied to V<sub>IN</sub> to keep the regulator on at all times (the ON/  $\overline{OFF}$  input must **not** be left floating).


For proper operation of the LDO, the signal source used to drive the ON/ OFF input must be able to swing above and below the specified turnon/turnoff voltage thresholds which specify an ON or OFF state (see Section 5.5).

The ON/ OFF signal can come from either a totem-pole output, or an open-collector output with pullup resistor to the LP2981-N input voltage or another logic supply. The high-level voltage can exceed the LP2981-N input voltage, but must remain within the Section 5.1 for the ON/ OFF pin.

For the legacy chip only, it is also important that the turnon/turnoff voltage signals applied to the ON/  $\overline{OFF}$  input have a slew rate which is greater than 40 mV/µs.




### 7.2.3 Application Curves




LP2981-N SNOS7730 – MARCH 2000 – REVISED DECEMBER 2023











### 8 Power Supply Recommendations

The LP2981-N is designed to operate from an input voltage supply range between 2.5 V and 16 V (for the new chip). The input voltage range provides adequate headroom for the device to have a regulated output. This input supply must be well regulated. If the input supply is noisy, additional input capacitors with low ESR can help improve the output noise performance.

### 9 Layout

### 9.1 Layout Guidelines

For best overall performance, place all circuit components on the same side of the circuit board and as near as practical to the respective LDO pin connections. Place ground return connections to the input and output capacitors, and to the LDO ground pin as close to each other as possible, connected by a wide, component-side, copper surface. The use of vias and long traces to create LDO circuit connections is strongly discouraged and negatively affects system performance. This grounding and layout scheme minimizes inductive parasitics, and thereby reduces load-current transients, minimizes noise, and increases circuit stability. A ground reference plane is also recommended and is either embedded in the PCB itself or located on the bottom side of the PCB opposite the components. This reference plane serves for the accuracy of the output voltage, shield noise, and behaves similar to a thermal plane to spread (or sink) heat from the LDO device. In most applications, this ground plane is necessary to meet thermal requirements.

### 9.2 Layout Example




Figure 9-1. LP2981-N Layout Example



## **10 Device and Documentation Support**

### 10.1 Device Nomenclature

PRODUCT	V <sub>OUT</sub>								
	<ul> <li>c is the accuracy specification. xxx is the package designator. z is the package quantity.</li> <li>X is for a large-quantity reel and non-X is for a small-quantity reel.</li> <li>y.y is the nominal output voltage (for example, 3.3 = 3.3 V; 5.0 = 5.0 V).</li> </ul>								
New chip	<ul> <li>A is for higher accuracy and non-A is for standard grade.</li> <li>xxx is the package designator. z is the package quantity.</li> <li>X is for a large-quantity reel and non-X is for a small-quantity reel</li> <li>y.y is the nominal output voltage (for example, 3.3 = 3.3 V; 5.0 = 5.0 V).</li> <li>M3 is a suffix designator for newer chip redesigns, fabricated on the latest TI process technology.</li> </ul>								

## Table 10-1. Available Options

### **10.2 Third-Party Products Disclaimer**

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

#### **10.3 Receiving Notification of Documentation Updates**

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### **10.4 Related Documentation**

For related documentation see the following:

- Texas Instruments, LDO Noise Demystified, application note
- Texas Instruments, LDO PSRR Measurement Simplified, application note
- Texas Instruments, A Topical Index of TI LDO Application Notes, application note

#### **10.5 Support Resources**

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 10.6 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments. All trademarks are the property of their respective owners.

#### **10.7 Electrostatic Discharge Caution**



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 10.8 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

Copyright © 2023 Texas Instruments Incorporated



### 11 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

anges from , to , (from Revision N (April 2016) to Revision O (December 2023))	Page
Updated the numbering format for tables, figures, and cross-references throughout the docume	ent 1
Changed entire document to align with current family format	1
Added M3 devices to document	1
Changed "Nine" to "Assorted"	1
Added Pin Configuration and Functions section, ESD Ratings table, Feature Description section Functional Modes, Application and Implementation section, Power Supply Recommendations s section, Device and Documentation Support section, and Mechanical, Packaging, and Orderab section	ection, <i>Layout</i> <i>le Information</i>
Changed update typical application drawing and change pin names from Vin, Vout to IN and Ol	UT1
Changed layout of National Data Sheet to TI format	
Added Device Nomenclature section	
Added three references to Related Documentation	29
anges from Revision M (September 2015) to Revision N (April 2016)	Page

#### Changed update typical application drawing and change pin names from Vin, Vout to IN and OUT ......1

### 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



### **PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
LP2981AIM5-2.5/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	LOCA	Samples
LP2981AIM5-3.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L05A	Samples
LP2981AIM5-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L04A	Samples
LP2981AIM5-3.6/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	LOJA	Samples
LP2981AIM5-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L03A	Samples
LP2981AIM5X-3.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L05A	Samples
LP2981AIM5X-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	L04A	Samples
LP2981AIM5X-3.6/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	LOJA	Samples
LP2981AIM5X-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L03A	Samples
LP2981IM5-2.5/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	LOCB	Samples
LP2981IM5-3.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L05B	Samples
LP2981IM5-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	L04B	Samples
LP2981IM5-3.6/NOPB	ACTIVE	SOT-23	DBV	5	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L0JB	Samples
LP2981IM5-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L03B	Samples
LP2981IM5X-3.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L05B	Samples
LP2981IM5X-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	L04B	Samples
LP2981IM5X-3.6/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	L0JB	Samples
LP2981IM5X-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	L03B	Samples

(1) The marketing status values are defined as follows:
 ACTIVE: Product device recommended for new designs.
 LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.



# PACKAGE OPTION ADDENDUM

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design. **PREVIEW:** Device has been announced but is not in production. Samples may or may not be available. **OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

Texas

STRUMENTS

### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter	Reel Width	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
	Туре	Drawing			(mm)	W1 (mm)	· /	(,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	(1111)	(,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	(1111)	Quadrant
LP2981AIM5-2.5/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5-3.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5-3.3/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5-3.6/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5-5.0/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5X-3.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5X-3.3/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5X-3.6/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981AIM5X-5.0/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5-2.5/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5-3.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5-3.3/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5-3.6/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5-5.0/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5X-3.0/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5X-3.3/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3




13-Oct-2024

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LP2981IM5X-3.6/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LP2981IM5X-5.0/NOPB	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3



# PACKAGE MATERIALS INFORMATION

13-Oct-2024



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LP2981AIM5-2.5/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981AIM5-3.0/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981AIM5-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981AIM5-3.6/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981AIM5-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981AIM5X-3.0/NOPB	SOT-23	DBV	5	3000	208.0	191.0	35.0
LP2981AIM5X-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981AIM5X-3.6/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981AIM5X-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5-2.5/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981IM5-3.0/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981IM5-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5-3.6/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LP2981IM5-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5X-3.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5X-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5X-3.6/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LP2981IM5X-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0

# **DBV0005A**



# **PACKAGE OUTLINE**

# SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
   This drawing is subject to change without notice.
   Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.



# DBV0005A

# **EXAMPLE BOARD LAYOUT**

## SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



# DBV0005A

# **EXAMPLE STENCIL DESIGN**

## SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated