







MAX3221F SLLS686D - OCTOBER 2005 - REVISED JULY 2024

# MAX3221E 3V to 5.5V Single-Channel RS-232 Line Driver and Receiver With ±15kV **IEC ESD Protection**

#### 1 Features

- ESD protection for RS-232 pins
  - ±15kV Human-body model (HBM)
  - ±8kV (IEC 61000-4-2, Contact discharge)
  - ±15kV (IEC 61000-4-2, Air-gap discharge)
- Meets or exceeds the requirements of TIA/ EIA-232-F and ITU v.28 standards
- Operates with 3V to 5.5V V<sub>CC</sub> supply
- Operates up to 250kbit/s
- One driver and one receiver
- Low standby current: 1µA typical
- Accepts 5V logic input with 3.3V supply
- Auto-power-down feature automatically disables drivers for power savings
- Alternative high-speed device (1Mbit/s)
  - SN75C3221E and SN65C3221E

## 2 Applications

- **Industrial PCs**
- Wired networking
- Data center and enterprise computing
- Battery-powered systems
- **PDAs**
- **Notebooks**
- Laptops
- Palmtop PCs
- Hand-held equipment

## 3 Description


The MAX3221E is a single driver, single receiver RS-232 solution operating from a single  $V_{CC}$  supply. The RS-232 pins provide IEC 61000-4-2 ESD protection. The device meets the requirements of TIA/EIA-232-F and provides the electrical interface between an asynchronous communication controller and the serial-port connector. The charge pump and four small external capacitors allow operation from a single 3V to 5.5V supply. These devices operate at data signaling rates up to 250kbit/s and a maximum of 30V/µs driver output slew rate.

Flexible control options for power management are available. Auto-power down disables driver and charge pump when the receiver is disconnected or the remote driver is power down. The drivers can be manually enabled or disabled. INVALID output goes low when receiver input is unconnected or power off.

#### **Package Information**

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE <sup>(2)</sup>
MAX3221E	SSOP (DB, 16)	6.2mm × 7.8mm
	TSSOP (PW, 16)	5mm × 6.4mm

- (1) For more information, see Section 11.
- The package size (length × width) is a nominal value and (2)includes pins, where applicable.



Copyright © 2016, Texas Instruments Incorporated

**Block Diagram** 



# **Table of Contents**

1 Features1	7 Detailed Description12
2 Applications1	7.1 Overview12
3 Description1	7.2 Functional Block Diagram12
4 Pin Configuration and Functions3	7.3 Feature Description12
5 Specifications4	7.4 Device Functional Modes1
5.1 Absolute Maximum Ratings4	8 Application and Implementation14
5.2 ESD Ratings4	8.1 Application Information14
5.3 ESD Ratings - IEC Specifications4	8.2 Typical Application14
5.4 Recommended Operating Conditions5	8.3 Power Supply Recommendations15
5.5 Thermal Information5	8.4 Layout16
5.6 Electrical Characteristics5	9 Device and Documentation Support17
5.7 Electrical Characteristics: Driver6	9.1 Receiving Notification of Documentation Updates17
5.8 Electrical Characteristics: Receiver6	9.2 Support Resources17
5.9 Electrical Characteristics: Auto-Power Down6	9.3 Trademarks17
5.10 Switching Characteristics: Driver7	9.4 Electrostatic Discharge Caution17
5.11 Switching Characteristics: Receiver7	9.5 Glossary17
5.12 Switching Characteristics: Auto-Power Down7	10 Revision History17
5.13 Typical Characteristics8	11 Mechanical, Packaging, and Orderable
6 Parameter Measurement Information9	Information18



# **4 Pin Configuration and Functions**




Figure 4-1. DB or PW Package 16-Pin SSOP or TSSOP (Top View)

**Table 4-1. Pin Functions** 

PIN		I/O	DESCRIPTION
NAME	NO.	1/0	DESCRIPTION
C1+	2		Positive terminals of the voltage-doubler charge pump capacitors
C2+	5	_	Prositive terminals of the voltage-doubler charge pump capacitors
C1-	4		Negative terminals of the voltage-doubler charge pump capacitors
C2-	6		Negative terminals of the voltage-doubler charge pump capacitors
DIN	11	I	Driver input
DOUT	13	0	RS-232 driver output
EN	1	I	Low input enables receiver ROUT output. High input sets ROUT to high impedance.
FORCEOFF	16	I	Automatic power-down control input
FORCEON	12	1	Automatic power-down control input
GND	14	_	Ground
INVALID	10	0	Invalid output pin. Output low when RIN input is unpowered.
RIN	8	I	RS-232 receiver input
ROUT	9	0	Receiver output
V <sub>CC</sub>	15	_	3V to 5.5V supply voltage
V+	3	0	5.5V supply generated by the charge pump
V-	7	0	-5.5V supply generated by the charge pump



## **5 Specifications**

## 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage <sup>(2)</sup>		-0.3	6	V
V+	Positive output supply voltage <sup>(2)</sup>		-0.3	7	V
V-	Negative output supply voltage <sup>(2)</sup>		0.3	<b>–</b> 7	V
V+ - V-	Supply voltage difference <sup>(2)</sup>			13	V
V	Input voltage	DIN, FORCEOFF, FORCEON, EN	-0.3	6	V
V <sub>I</sub>	Input voltage	RIN	-25	25	V
.,	Output valtage	DOUT	-13.2	13.2	V
Vo	Output voltage ROUT, INVALID			V <sub>CC</sub> + 0.3	v
TJ	Operating virtual junction temperature			150	°C
T <sub>stg</sub>	Storage temperature			150	°C

<sup>(1)</sup> Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

## 5.2 ESD Ratings

				VALUE	UNIT
		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	Pins 8 and 13	±15000	
V <sub>(ESD)</sub>	Electrostatic discharge	Truman-body model (HBM), per ANGI/EGDA/JEDEC 33-00 TV	All other pins	±2000	V
		Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	All pins	±1500	

<sup>(1)</sup> JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.

## 5.3 ESD Ratings - IEC Specifications

				VALUE	UNIT
V (ESD) Electrostatic discharge	IEC 61000-4-2 Contact Discharge, DOUT and RIN <sup>(1)</sup>	- Pins 8 and 13	±8000	V	
V (ESD)	Electrostatic discharge	IEC 61000-4-2 Air-Gap Discharge, DOUT and RIN <sup>(1)</sup>	THIS O AND 13	±15000	V

(1) A minimum of 1µF capacitor is required between VCC and GND to meet the specified IEC-ESD level.

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

<sup>(2)</sup> All voltages are with respect to network GND.

<sup>(2)</sup> JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.



## **5.4 Recommended Operating Conditions**

See Figure 8-1 (1)

				MIN	NOM	MAX	UNIT
	Supply voltage	V <sub>CC</sub> = 3.3V	3	3.3	3.6	V	
	Supply voltage			4.5	5	5.5	V
V <sub>IH</sub>	Driver and control high-level input voltage	DIN, FORCEOFF, FORCEON, EN	V <sub>CC</sub> = 3.3V	2			V
		DIN, FORCEOFF, FORCEON, EN	V <sub>CC</sub> = 5V	2.4			V
$V_{IL}$	Driver and control low-level input voltage	DIN, FORCEOFF, FORCEON, EN				0.8	V
VI	Driver and control input voltage	DIN, FORCEOFF, FORCEON		0		5.5	V
VI	Receiver input voltage			-25		25	V
T <sub>A</sub>	Operating free air temperature	MAX3221EC		0		70	°C
	Operating free-air temperature	MAX3221EI		-40		85	C

<sup>(1)</sup> Test conditions are C1–C4 =  $0.1\mu F$  at  $V_{CC}$  =  $3.3V \pm 0.3V$ ; C1 =  $0.047\mu F$ , C2–C4 =  $0.33\mu F$  at  $V_{CC}$  =  $5V \pm 0.5V$ .

#### 5.5 Thermal Information

		MAX	MAX3221E			
	THERMAL METRIC(1)	DB (SSOP)	PW (TSSOP)	UNIT		
		16 PINS	16 PINS			
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	105.8	110.9	°C/W		
R <sub>θJC(top)</sub>	Junction-to-case (top) thermal resistance	51.9	41.7	°C/W		
$R_{\theta JB}$	Junction-to-board thermal resistance	57.6	57.2	°C/W		
ΨЈТ	Junction-to-top characterization parameter	14.1	4.2	°C/W		
ΨЈВ	Junction-to-board characterization parameter	56.8	56.6	°C/W		

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application

## 5.6 Electrical Characteristics

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)(2)

PARAMETER			TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
II	Input leakage current	FORCEOFF, FORCEON, EN				±0.01	±1	μΑ
		Auto-power down disabled		No load, FORCEOFF and FORCEON at V <sub>CC</sub>		0.3	1	mA
I <sub>CC</sub>	Supply current	Powered off	V <sub>CC</sub> = 3.3V or 5V, T <sub>A</sub> = 25°C	No load, FORCEOFF at GND		1	10	
		Auto-power down enabled		No load, FORCEOFF at V <sub>CC</sub> , FORCEON at GND, All RIN are open or grounded		1	10	μΑ

Copyright © 2024 Texas Instruments Incorporated

Submit Document Feedback

All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C. Test conditions are C1–C4 = 0.1 $\mu$ F at  $V_{CC}$  = 3.3V  $\pm$  0.3V; C1 = 0.047 $\mu$ F, C2–C4 = 0.33 $\mu$ F at  $V_{CC}$  = 5V  $\pm$  0.5V.



#### 5.7 Electrical Characteristics: Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)<sup>(3)</sup>

	PARAMETER	TEST CONDITIONS			MIN	TYP <sup>(1)</sup>	MAX	UNIT
V <sub>OH</sub>	High-level output voltage	DOUT at $R_L = 3k\Omega$ to GND,	DIN = GND		5	5.4		V
V <sub>OL</sub>	Low-level output voltage	DOUT at $R_L = 3k\Omega$ to GND,	DIN = V <sub>CC</sub>		<b>-</b> 5	-5.4		V
I <sub>IH</sub>	High-level input current	V <sub>I</sub> = V <sub>CC</sub>				±0.01	±1	μΑ
I <sub>IL</sub>	Low-level input current	V <sub>I</sub> = GND				±0.01	±1	μΑ
	Short-circuit	V <sub>CC</sub> = 3.6V,	V <sub>O</sub> = 0V			±35	±60	mA
los	output current <sup>(2)</sup>	V <sub>CC</sub> = 5.5V,	V <sub>O</sub> = 0V			±35	±60	ША
r <sub>o</sub>	Output resistance	V <sub>CC</sub> , V+, and V- = 0V,	V <sub>O</sub> = ±2V		300	10M		Ω
1	Output leakage current	FORCEOFF = GND	$V_{O} = \pm 12V$ ,	V <sub>CC</sub> = 3V to 3.6V			±25	
I <sub>off</sub>	Output leakage current	PORCEOUT - GND	$V_0 = \pm 10V$ ,	V <sub>CC</sub> = 4.5V to 5.5V			±25	μA

- (1) All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C.
- (2) Short-circuit durations should be controlled to prevent exceeding the device absolute power-dissipation ratings, and not more than one output should be shorted at a time.
- (3) Test conditions are C1–C4 =  $0.1\mu F$  at  $V_{CC} = 3.3V \pm 0.3V$ ; C1 =  $0.047\mu F$ , C2–C4 =  $0.33\mu F$  at  $V_{CC} = 5V \pm 0.5V$ .

#### 5.8 Electrical Characteristics: Receiver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)(2)

	PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
V <sub>OH</sub>	High-level output voltage	I <sub>OH</sub> = -1mA	V <sub>CC</sub> - 0.6	$V_{CC} - 0.1$		V
V <sub>OL</sub>	Low-level output voltage	I <sub>OL</sub> = 1.6mA			0.4	V
V <sub>IT+</sub>	Positive-going input threshold voltage	V <sub>CC</sub> = 3.3V		1.6	2.4	V
	Fositive-going input till estiblic voltage	V <sub>CC</sub> = 5V		1.9	2.4	V
V <sub>IT</sub> _	Negative-going input threshold voltage	V <sub>CC</sub> = 3.3V	0.6	1.1		V
VII-	rvegative-going input timeshold voltage	V <sub>CC</sub> = 5V	0.8	1.4		V
V <sub>hys</sub>	Input hysteresis (V <sub>IT+</sub> - V <sub>IT-</sub> )			0.5		V
I <sub>off</sub>	Output leakage current	EN = V <sub>CC</sub>		±0.05	±10	μΑ
ri	Input resistance	V <sub>I</sub> = ±3V to ±25V	3	5	7	kΩ

- (1) All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C.
- (2) Test conditions are C1–C4 =  $0.1\mu$ F at  $V_{CC}$  =  $3.3V \pm 0.3V$ ; C1 =  $0.047\mu$ F, C2–C4 =  $0.33\mu$ F at  $V_{CC}$  =  $5V \pm 0.5V$ .

#### 5.9 Electrical Characteristics: Auto-Power Down

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST C	TEST CONDITIONS			UNIT
V <sub>T+(valid)</sub>	Receiver input threshold for INVALID high-level output voltage	FORCEON = GND,	FORCEOFF = V <sub>CC</sub>		2.7	V
V <sub>T-(valid)</sub>	Receiver input threshold for INVALID high-level output voltage	FORCEON = GND,	FORCEOFF = V <sub>CC</sub>	-2.7		V
V <sub>T(invalid)</sub>	Receiver input threshold for I NVALID low-level output voltage	FORCEON = GND,	FORCEOFF = V <sub>CC</sub>	-0.3	0.3	V
V <sub>OH</sub>	INVALID high-level output voltage	I <sub>OH</sub> = -1mA, FORCEON = GND, FORCEOFF = V <sub>CC</sub>		V <sub>CC</sub> - 0.6		V
V <sub>OL</sub>	INVALID low-level output voltage	I <sub>OL</sub> = 1.6mA, FORCEO FORCEOFF = V <sub>CC</sub>	N = GND,		0.4	V

Product Folder Links: MAX3221E



#### 5.10 Switching Characteristics: Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)(3)

	PARAMETER	TE	MIN	TYP <sup>(1)</sup>	MAX	UNIT	
	Maximum data rate	C <sub>L</sub> = 1000pF,	$R_L = 3k\Omega$ ,	150	250		kbit/s
t <sub>sk(p)</sub>	Pulse skew <sup>(2)</sup>	C <sub>L</sub> = 150pF to 2500pF,	$R_L$ = 3kΩ to 7kΩ, See Figure 6-2		100		ns
0.7(1)	Slew rate,	V <sub>CC</sub> = 3.3V,	C <sub>L</sub> = 150pF to 1000pF	6		30	
SR(tr)	transition region (see Figure 6-1)	D 0101 710	C <sub>L</sub> = 150pF to 2500pF	4		30	V/µs

- (1) All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C.
- Pulse skew is defined as  $|t_{PLH}-t_{PHL}|$  of each channel of the same device. Test conditions are C1–C4 = 0.1 $\mu$ F at V<sub>CC</sub> = 3.3V  $\pm$  0.3V; C1 = 0.047 $\mu$ F, C2–C4 = 0.33 $\mu$ F at V<sub>CC</sub> = 5V  $\pm$  0.5V.

#### **5.11 Switching Characteristics: Receiver**

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)(3)

	PARAMETER	TEST CONDITIONS	TYP <sup>(1)</sup>	UNIT
t <sub>PLH</sub>	Propagation delay time, low- to high-level output	C <sub>L</sub> = 150pF, See Figure 6-3	150	ns
t <sub>PHL</sub>	Propagation delay time, high- to low-level output	C <sub>L</sub> = 150pF, See Figure 6-3	150	ns
t <sub>en</sub>	Output enable time	$C_L = 150 \text{pF}, R_L = 3 \text{k}\Omega, \text{ See Figure 6-4}$	200	ns
t <sub>dis</sub>	Output disable time	$C_L$ = 150pF, $R_L$ = 3k $\Omega$ , See Figure 6-4	200	ns
t <sub>sk(p)</sub>	Pulse skew <sup>(2)</sup>	See Figure 6-3	50	ns

- All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C.
- (2)
- Pulse skew is defined as  $|t_{PLH}-t_{PHL}|$  of each channel of the same device. Test conditions are C1–C4 = 0.1 $\mu$ F at V<sub>CC</sub> = 3.3V  $\pm$  0.3V; C1 = 0.047 $\mu$ F, C2–C4 = 0.33 $\mu$ F at V<sub>CC</sub> = 5V  $\pm$  0.5V.

## 5.12 Switching Characteristics: Auto-Power Down

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)


	PARAMETER	TYP <sup>(1)</sup>	UNIT
t <sub>valid</sub>	Propagation delay time, low- to high-level output	1	μs
t <sub>invalid</sub>	Propagation delay time, high- to low-level output	30	μs
t <sub>en</sub>	Supply enable time	100	μs

All typical values are at  $V_{CC}$  = 3.3V or  $V_{CC}$  = 5V, and  $T_A$  = 25°C.




## **5.13 Typical Characteristics**

 $T_A = 25$ °C;  $V_{CC} = 3.3V$ 






## **6 Parameter Measurement Information**




- A. C<sub>L</sub> includes probe and jig capacitance.
- B. The pulse generator has the following characteristics: PRR = 250kbps,  $Z_0 = 50\Omega$ , 50% duty cycle,  $t_f \le 10$ ns,  $t_f \le 10$ ns.

Figure 6-1. Driver Slew Rate



- A. C<sub>L</sub> includes probe and jig capacitance.
- B. The pulse generator has the following characteristics: PRR = 250kbps,  $Z_0 = 50\Omega$ , 50% duty cycle,  $t_f \le 10$ ns,  $t_f \le 10$ ns.


Figure 6-2. Driver Pulse Skew



- A. C<sub>L</sub> includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $Z_0 = 50\Omega$ , 50% duty cycle,  $t_r \le 10$ ns,  $t_f \le 10$ ns.

Figure 6-3. Receiver Propagation Delay Times





- A. C<sub>L</sub> includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $Z_0 = 50\Omega$ , 50% duty cycle,  $t_r \le 10$ ns,  $t_f \le 10$ ns.
- C.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
- D.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .

Figure 6-4. Receiver Enable and Disable Times

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated






Figure 6-5. INVALID Propagation Delay Times and Driver Enabling Time

current to 1  $\mu$ A.

## 7 Detailed Description

#### 7.1 Overview

The MAX3221E is a single driver, single receiver RS-232 solution operating from a single  $V_{CC}$  supply. The RS-232 pins provide IEC 61000-4-2 ESD protection. The device meets the requirements of TIA/EIA-232-F and provides the electrical interface between an asynchronous communication controller and the serial-port connector. The charge pump and four small external capacitors allow operation from a single 3V to 5.5V supply. These devices operate at data signaling rates up to 250kbit/s and a maximum of 30V/ $\mu$ s driver output slew rate.

Flexible control options for power management are available when the serial port is inactive. The auto-power-down feature functions when FORCEON is low and  $\overline{\text{FORCEOFF}}$  is high. During this mode of operation, if the device does not sense a valid RS-232 signal on the receiver input, the driver output is disabled. If  $\overline{\text{FORCEOFF}}$  is set low and  $\overline{\text{EN}}$  is high, both the driver and receiver are shut off, and the supply current is reduced to 1  $\mu$ A. Disconnecting the serial port or turning off the peripheral drivers causes the auto-power-down condition to occur. Auto-power down can be disabled when FORCEON and  $\overline{\text{FORCEOFF}}$  are high. With auto-power down enabled, the device is activated automatically when a valid signal is applied to the receiver input. The  $\overline{\text{INVALID}}$  output notifies the user if an RS-232 signal is present at the receiver input.  $\overline{\text{INVALID}}$  is high (valid data) if the receiver input voltage is greater than 2.7V or less than -2.7V, or has been between -0.3V and 0.3V for less than 30 $\mu$ s.  $\overline{\text{INVALID}}$  is low (invalid data) if the receiver input voltage is between -0.3V and 0.3V for more than 30 $\mu$ s. See Figure 6-1 for receiver input levels.

#### 7.2 Functional Block Diagram




Figure 7-1. Logic Diagram (Positive Logic)

## 7.3 Feature Description

#### 7.3.1 Power

The power block increases, inverts, and regulates voltage at V+ and V- pins using a charge pump that requires four external capacitors. Auto-power-down feature for driver is controlled by FORCEON and  $\overline{\text{FORCEOFF}}$  inputs. Receiver is controlled by  $\overline{\text{EN}}$  input. When unpowered, the MAX3221E can be safely connected to an active remote RS-232 device.

#### 7.3.2 RS-232 Driver

One driver interfaces standard logic levels to RS-232 levels. DIN input must be valid high or low.

Product Folder Links: MAX3221E

#### 7.3.3 RS-232 Receiver

One receiver interfaces RS-232 levels to standard logic levels. An open input results in a high output on ROUT. RIN input includes an internal standard RS-232 load. A logic high input on the  $\overline{\text{EN}}$  pin shuts down the receiver output.

#### 7.3.4 RS-232 Status

The  $\overline{\text{INVALID}}$  output goes low when RIN input is unpowered for more than 30µs. The  $\overline{\text{INVALID}}$  output goes high when receiver has a valid input. The  $\overline{\text{INVALID}}$  output is active when  $V_{CC}$  is powered irregardless of FORCEON and  $\overline{\text{FORCEOFF}}$  inputs (see Table 7-3).

#### 7.4 Device Functional Modes

Table 7-1, Table 7-2, and Table 7-3 show the behavior of the driver, receiver, and INVALID features under all possible relevant combinations of inputs.

**INPUTS** OUTPUT **DRIVER STATUS VALID RIN DOUT FORCEON FORCEOFF** DIN RS-232 LEVEL Χ Ζ Х Х Powered off L Н Χ Н Normal operation with auto-power down disabled Н Н Н Χ L L Yes Н L Η Normal operation with auto-power down enabled Н L Н Yes L Ζ L Powered off by auto-power down feature Н L 7 Nο

Table 7-1. Function Tables Each Driver<sup>(1)</sup>

(1) H = high level, L = low level, X = irrelevant, Z = high impedance

Table	7-2.	Each	Recei	iver <sup>(1</sup>	)
INI	PIITS				

	OUTPUT		
RIN	EN	VALID RIN RS-232 LEVEL	ROUT
L	L	Х	Н
Н	L	Х	L
X	Н	Х	Z
Open	L	No	Н

 H = high level, L = low level, X = irrelevant, Z = high impedance (off), Open = disconnected input or connected driver off

Table 7-3. INVALID (1)

INPUTS	ОИТРИТ			
RIN	FORCEON	FORCEOFF	EN	INVALID
L	X	X	X	Н
Н	X	X	X	Н
Open	X	X	X	L

(1) H = high level, L = low level, X = irrelevant, Z = high impedance (off), Open = input disconnected or connected driver off

## 8 Application and Implementation

#### Note


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 8.1 Application Information

The MAX3221E line driver and receiver is a specialized device for 3V to 5.5V RS-232 communication applications. This application is a generic implementation of this device with all required external components. For proper operation, add capacitors as shown in Figure 8-1.

#### 8.2 Typical Application

ROUT and DIN connect to UART or general purpose logic lines. FORCEON and  $\overline{FORCEOFF}$  may be connected general purpose logic lines or tied to ground or  $V_{CC}$ .  $\overline{INVALID}$  may be connected to a general purpose logic line or left unconnected. RIN and DOUT lines connect to a RS-232 connector or cable. DIN, FORCEON, and  $\overline{FORCEOFF}$  inputs must not be left unconnected.



(1) C3 can be connected to V<sub>CC</sub> or GND.

NOTES: A. Resistor values shown are nominal.

B. Nonpolarized ceramic capacitors are acceptable. If polarized tantalum or electrolytic capacitors are used, they should be connected as shown

V<sub>CC</sub> vs CAPACITOR VALUES

V <sub>CC</sub>	C1	C2, C3, and C4
3.3 V ± 0.3 V	0.1 μF	0.1 μF
5 V ± 0.5 V	0.047 μF	0.33 μF
3 V to 5.5 V	0.1 μF	0.47 μF

Copyright © 2016, Texas Instruments Incorporated

Figure 8-1. Typical Operating Circuit and Capacitor Values

Product Folder Links: MAX3221E




## 8.2.1 Design Requirements

- Recommended  $V_{CC}$  is 3.3V or 5V.
  - 3V to 5.5V is also possible
- Maximum recommended bit rate is 250kbps.
- Use capacitors as shown in Figure 8-1.

## 8.2.2 Detailed Design Procedure

- DIN, FORCEOFF and FORCEON inputs must be connected to valid low or high logic levels.
- · Select capacitor values based on VCC level for best performance.

## 8.2.3 Application Curves



## 8.3 Power Supply Recommendations

TI recommends a  $0.1\mu\text{F}$  capacitor to filter noise on the power supply pin. For additional filter capability, a  $0.01\mu\text{F}$  capacitor may be added in parallel as well. Power supply input voltage is recommended to be any valid level in Section 5.4.



#### 8.4 Layout

## 8.4.1 Layout Guidelines

Keep the external capacitor traces short. This is more important on C1 and C2 nodes that have the fastest rise and fall times. Make the impedance from MAX3221E ground pin and the circuit board ground plane as low as possible for best ESD performance. Use wide metal and multiple vias on both sides of ground pin.

## 8.4.2 Layout Example




Figure 8-4. MAX3221E Layout Example

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

## 9 Device and Documentation Support

## 9.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 9.2 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 9.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

## 9.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 9.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

#### 10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision C (July 2021) to Revision D (July 2024)	Page
Changed the Device Information table to the Package Information table	1
Changed Pins 8 and 11 to Pins 8 and 13 in the ESD Ratings	4
Changed Pins 8 and 11 to Pins 8 and 13 in the ESD ratings IEC Specifications	
Changes from Revision B (March 2016) to Revision C (July 2021)	Page
Changed the Applications list	1
<ul> <li>Added ESD ratings IEC Specifications table and added a table note for the minimum requiremental IEC ESD level</li></ul>	ent to meet the
Changed values in the <i>Thermal Information</i> table for DB and PW packages	
Changes from Revision A (May 2006) to Revision B (March 2016)	Page
<ul> <li>Added ESD Ratings table, Feature Description section, Device Functional Modes, Application a Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section</li> <li>Deleted Ordering Information table; see the POA at the end of the data sheet</li></ul>	and1
• Changed R <sub>θJA</sub> thermal values: 82 to 92 for DB package and 108 to 100.3 for PW Package	



# 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Product Folder Links: MAX3221E



www.ti.com 28-Aug-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
MAX3221ECDBR	ACTIVE	SSOP	DB	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	MP221EC	Samples
MAX3221ECDBRG4	ACTIVE	SSOP	DB	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	MP221EC	Samples
MAX3221ECPWR	ACTIVE	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	MP221EC	Samples
MAX3221EIDBR	ACTIVE	SSOP	DB	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MP221EI	Samples
MAX3221EIDBRG4	ACTIVE	SSOP	DB	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MP221EI	Samples
MAX3221EIPW	OBSOLETE	TSSOP	PW	16		TBD	Call TI	Call TI	-40 to 85	MP221EI	
MAX3221EIPWR	ACTIVE	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MP221EI	Samples
MAX3221EIPWRG4	ACTIVE	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MP221EI	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



## **PACKAGE OPTION ADDENDUM**

www.ti.com 28-Aug-2024

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 18-Jun-2024

## TAPE AND REEL INFORMATION



# TAPE DIMENSIONS KO P1 BO W Cavity A0

A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
MAX3221ECDBR	SSOP	DB	16	2000	330.0	16.4	8.35	6.6	2.4	12.0	16.0	Q1
MAX3221ECPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
MAX3221EIDBR	SSOP	DB	16	2000	330.0	16.4	8.35	6.6	2.4	12.0	16.0	Q1
MAX3221EIPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
MAX3221EIPWRG4	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
MAX3221EIPWRG4	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1



www.ti.com 18-Jun-2024



## \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
MAX3221ECDBR	SSOP	DB	16	2000	356.0	356.0	35.0
MAX3221ECPWR	TSSOP	PW	16	2000	356.0	356.0	35.0
MAX3221EIDBR	SSOP	DB	16	2000	356.0	356.0	35.0
MAX3221EIPWR	TSSOP	PW	16	2000	356.0	356.0	35.0
MAX3221EIPWRG4	TSSOP	PW	16	2000	356.0	356.0	35.0
MAX3221EIPWRG4	TSSOP	PW	16	2000	356.0	356.0	35.0





#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
  4. Reference JEDEC registration MO-150.





NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated